

# 2243QW

SAMSUNG

## 22" Widescreen LCD Multi-Display Monitor



### Features:

- UbiSync technology lets you add up to six 2243QW monitors via USB interface
- No special graphic cards or software required, just plug and play
- Compatible with Windows 2000, XP, Vista and Mac OS X (Intel CPUs)
- Included software adds GUI for easy monitor management
- Ultra-high 20,000:1 dynamic contrast ratio for detailed images
- Fast 5 ms response for blur-free motion graphics
- Exclusive MagicColor™ and MagicBright™ 3 picture technologies for rich, natural color



2243QW

How much more efficient could you be with twice as much monitor space? The Samsung 2243QW 22" widescreen LCD monitor gives you the ability to add up to six high-definition monitors to your current system. With revolutionary Samsung UbiSync technology, you can connect one or more 2243QW monitors via USB, without having to add any graphic cards or software. It's an innovative, simple, cost-effective, plug and play solution. And 20,000:1 dynamic contrast ratio, 5 ms response time and Samsung Magic picture technologies ensure sharp, blur-free, natural-looking images. Increase your productivity up to six-fold. The Samsung 2243QW 22" widescreen LCD monitor.

# 2243QW



## 22" Widescreen LCD Multi-Display Monitor

### Features

#### Easily Add Monitors to Your Current System Via USB

UbiSync technology allows you to connect up to six 2243QW high-resolution monitors to your current system via USB.

#### Plug and Play

The UbiSync connection is truly plug and play. No additional graphic cards or software required.

#### Greater Flexibility and Productivity

Refer to several documents at once. Easily compare images. Watch real-time graphics on three monitors while you work on the fourth. The possibilities are limitless.

#### GUI Monitor Management

Included software adds a simple GUI that makes managing your monitors simple.


#### High Dynamic Contrast Ratio

Dynamic contrast ratio of 20,000:1 continually optimizes picture for detailed whites and blacks.

#### Exclusive Magic Picture Technologies

MagicColor™ features Full mode to enhance overall color, and Intelligent mode to enhance color without affecting delicate skin tones. And MagicBright™ 3 gives you preset modes including Text, Internet, Game, Sports and Movie.

#### 2243QW Dimensions



### Specifications

### 2243QW

Display	Screen Size	22" Wide
	Brightness (Typical)	300 cd/m <sup>2</sup>
	Contrast Ratio (Typical/Dynamic)	1000:1/20,000:1
	Resolution	1680 x 1050
	Response Time (Typical)	5 ms
	Viewing Angle (Horizontal/Vertical)	170°/160° (CR>10)
	Color Supported	16.7M
Signal Input	Video Signal	Analog RGB, DVI, USB
	Sync. Signal	Separate H/V, Composite, SOG
	Connector	15-pin D-Sub, DVI-D, USB
Power	Power Consumption	45 Watts (Max.)
	Stand by Power (DPMS)	Analog RGB, DVI < 2.5 Watt
	Type	Built-in
Features	Plug & Play	DDC 1/2B, DDC-CI
	USB Powered Hub	■
	PC Compatibility	Windows 2000, XP, Vista
	Mac Compatibility	■ OS X (Intel CPU)
	Wall Mount	VESA 100mm
	TCO	TCO '03
	Cabinet Color	Black
	Accessories Included	DVI-D Cable, VGA Cable, USB Cable, Power Cable
	Special Features	UbiSync Technology (USB Graphic Interface), USB Hub (1-up 2-down), MagicBright 3, Image Size Color Effect, Customized Key, Windows Vista Premium, DVI with HDCP, Pivot Function, Safe Mode (Downscaling in UXGA)
Dimension	Product Dimension (With Stand, W x H x D)	19.9" x 14.8" x 7.9"
	Product Dimension (Without Stand, W x H x D)	19.9" x 13.1" x 2.7"
	Shipment Dimension (W x H x D)	23.0" x 8.0" x 16.3"
Weight	Product Weight	14.0 lbs.
	Shipment Weight	18.1 lbs.
Stand	Type	HAS (80mm)
	Function	Height Adjustable, Pivot, Swivel, Tilt
Green Management	Emission Standard	EMC
	RoHS Compliant	■
	EPEAT	Silver
	Product Recyclability	CCFL panel contains mercury, please dispose of properly
	Packaging Recyclability	Packing materials recyclable



Product Information: 1-866-542-7214 [samsung.com/monitor](http://samsung.com/monitor)

Product Support: 1-800-SAMSUNG



©2009 Samsung Electronics America, Inc. Samsung is a registered mark of Samsung Electronics Corp., Ltd. Specifications and design are subject to change without notice. See [www.samsung.com](http://www.samsung.com) for detailed information. Printed in USA. MON-2243QWDSHT-May09T