

5-Port Gigabit GREENnet Switch

TEG-S50g (v5.0R)

- · Plug and play installation
- 5 x Gigabit ports
- · 10Gbps switching capacity
- Up to 70% energy savings with GREENnet technology*
- · Sturdy metal switch
- · Limited Lifetime Warranty


The 5-Port Gigabit GREENnet Switch, model TEG-S50g, provides high bandwidth performance, ease of use, and reliability, all while reducing power consumption by up to 70%*. GREENnet technology automatically adjusts power consumption as needed, resulting in substantial energy savings. Embedded GREENnet technology works right out of the box with no management requirement.

Boost office network efficiency and eliminate network congestion with gigabit speeds and a total switching capacity of 10Gbps with full-duplex mode. Integrate this sturdy metal switch for reliable high speed network connectivity.

TRENDIET







Energy Savings

Embedded GREENnet technology provides cost savings and reduces power consumption by up to 70%, by limiting port power consumption during periods of low link utilization.


Gigabit Speeds

5 gigabit ports provide high-speed network connections to devices and a 10Gbps switching capacity allows data traffic to flow smoothly, reducing traffic bottlenecks.

Compact Design

With a compact and lightweight metal housing design, this switch is well-suited for desktop installations. Its fanless design is perfect for quiet environments that require silent operation.

Networking Solution





Easy Setup

Simply power up the switch and plug in connected devices



Jumbo Frame

Sends larger packets, or Jumbo Frames (up to 9KB), for increased performance



Housing Design

Compact and lightweight metal housing



Ports

5 x Gigabit Ethernet ports



Fanless

Fanless design lowers energy consumption and eliminates operating



LED Indicators

LEDs convey power, link, and activity



Switching Capacity

10Gbps switching capacity



Specifications

Standards	• IEEE 802.3 • IEEE 802.3u • IEEE 802.3x • IEEE 802.3ab • IEEE 802.3az
Device Interface	• 5 x Gigabit ports • LED indicators
Data Transfer Rate	Ethernet: 10Mbps (half duplex), 20Mbps (full duplex) Fast Ethernet: 100Mbps (half duplex), 200Mbps (full duplex) Gigabit: 2000Mbps (full duplex)
Performance	Data RAM buffer: 128KB Switch fabric: 10Gbps MAC address table: 2K Forwarding rate: 7.44Mpps (64-byte packet size) Jumbo frame: 9KB
Special Features	GREENnet energy saving technology Metal enclosure Wall Mountable
Power	Input: 100 – 240V AC, 50/60Hz, 0.15A Output: 5V DC, 1A external power adapter Max. consumption: 2.75W

Fan/Acoustics	Fanless design
MTBF	• 2,152,216 Hours
Operating Temperature	• 0° – 40° C (32° – 104° F)
Operating Humidity	Max. 90% non-condensing
Dimensions	• 116 x 70 x 25mm (4.6 x 2.8 x 1 in.)
Weight	• 192g (6.8 oz.)
Certifications	• CE • FCC
Warranty	Lifetime

PACKAGE CONTENTS

- TEG-S50g
- Quick Installation Guide
- Power adapter (5V DC, 1A)

TRENDnet offers a limited lifetime warranty for all of its metal-enclosed network switches that have been purchased in the United States/Canada on or after 1/1/2015. Cooling fan and internal power supply carry a one-year warranty.

^{*} Max power savings compared with standard TRENDnet switches.