


Printer and Network Connectors

- Printer Connector
HP EIO
- Network Connection (logical)
IEEE 802.3 (1000BaseSX)
- Network Connection (physical)
SC (Type MMF 62,5/125)



Configuration and Management

- InterCon-NetTool
Microsoft Windows (95, 98, Me, NT 4.x, 2000, XP, Server 2003, Vista)
Linux (RPM based installation)
Macintosh (MAC OS 10.x)
- Printer Wizard (Printer Installation Assistant)
Microsoft Windows (95, 98, Me, NT 4.x, 2000, XP, Server 2003, Vista)
Microsoft Windows (XP, Vista, Windows7)
- Internal Printserver WEB (Monitoring, Configuration, Administration, Firmware Update)
Minimum Browser Requirement: Frame compatible
- HP Tools (Compatibility / Support)
HP WebJetAdmin
HP JetAdmin
HP Install Network Printer Wizard
- FTP
- SNMP
SNMP-MIB II compatible, SEH private enterprise MIB
- Apple virtual printer
- Bonjour

Supported Operating Systems

- Microsoft Windows
95
98
Me
NT 3.x
NT 4.x
XP
2003 Server
2008 Server
Vista
Windows 7
- Apple Macintosh
Mac OS 7.x
MAC OS 8.x
MAC OS 9.x
MAC OS 10.x
- Novell NetWare
NetWare 3.x
NetWare 4.x
NetWare 5.x
NetWare 6.x
- Systems with TCP/IP Support
Linux Systems
System V Systems (SCO, SunOS 5, IBM AIX, HP-UX, Reliant UNIX 5.x, ...)
BSD Systems (BSD 4.x, SunOS4, ...)
IBM Systems (OS390/400, ...)

Supported Protocols

- TCP/IP
IPSec, DHCP, BootP, ARP, RARP, IPv4, IPv6, IPv6 / TCP, IPv6 / ICMP, IPv6 / FTP, IPv6 / FTPs, IPv6 / TFTP, IPv6 / HTTP, HTTPs, IPv6 / SSL, TLS, TCP, IPv6 / Raw TCP, UDP, ICMP, IGMP, FTP, FTPs, TFTP, LPD, HTTP, HTTPs, ZeroConf, DNS, SLP, SNMPv1, SNMP, SMTP, POP3, SSL/TLS, IPPv1.0, IPPv1.1, Raw TCP, Apple Bonjour
- AppleTalk (EtherTalk/TokenTalk)
AARP, RTMP, ADSP, ATP, NBP, ZIP, ATSP, PAP, DDP, BCP1, BCP2, TBCP
- NetWare
IPX, SPX, SPX2, SAP, SNAP, NCP, NCP Burst Mode, NDS, NDPS, PureIP, RIP, Bindery, R/N Printer
- Windows
SMB/CIFS (NetBIOS over TCP/IP), WINS

Printing Protocols and Methods

- Socketprinting / Raw TCP
- LPR/LPD printing
- IPP v1.1 printing
- AppleTalk printing
- HTTP printing (encrypted and un-encrypted)
- HTTP printing (beyond Proxy Server / Internet printing)
- ThinPrint printing
ThinPrint SSL printing
- FTP printing
- NetBIOS printing
- Novell iPrint (LPR and IPP)
- NDPS printing (IP/IPX)
- Bindery printing
- R/N printing
- POP3 printing
- Bonjour printing service

Security

- IPSec
- SSL 3.0
- TLS 1.0
- HTTPs
- 802.1X
EAP-MD5 Authentication
EAP-TLS Authentication
EAP-TTLS Authentication

- EAP-FAST Authentication
- EAP-PEAP Authentication
- Cisco EAP (LEAP) Authentication
- IPsender protection ("user access list")
- Access control
- Certificate Management
 - Self signed Certificate
 - Certificate request
 - Root Certificate
- Password Protection
- NetWare Packet Signature Level 1,2,3

Supported Languages

- English
- German
- French
- Spanish
- Italian
- Portuguese
- Japanese
- Korean
- Chinese (traditional)
- Chinese (simplified)

Technical Data

- Printer Connector
 - HP EIO
- Network Connection (logical)
 - IEEE 802.3 (1000BaseSX)
- Network Connection (physical)
 - SC (Type MMF 62,5/125)
- Tests (Notifications)
 - CE: EN55022 Class A, EN55024
 - FCC Class A
 - WEEE
 - RoHS
- Operating Environment
 - Ambient temperature 5 - 40 °C
 - Relative humidity: 20 - 80 %
 - Indoor use only
- Hardware
 - 4MB Flash
 - 16MB RAM
 - ISA based RISC Processor / 100 Mhz
- Power Supply
 - internal (via Printer)
- Dimensions (Depth, Width, Height)
 - 135 x 90 x 32 mm
- Weight
 - 85 g

Package

- PS1126 Print Server
- Installation Manual
- Software Quick Reference
- Product CD

Order Numbers

- M04630 (Euro)
- M04632 (US)