

Lexmark C780n/C782n

Leverage the power of
colour affordably

Simplify
the way you
work.



 **Fast!** Up to 38 ppm
mono & 33 ppm colour

 **Professional** 4800 Colour
Quality and 1200 x 1200
dpi giving you sharp, vivid,
high quality results

 **Affordable** Low cost colour and
mono printing at the same TCO
as a mono only printer

 **Versatile** Customise to meet the
specific needs of your business,
including upgrading it to a full
colour MFP

Colour Laser Printer

LEXMARK

Welcome to the future of workgroup printing

Colour is the future of office printing, and now Lexmark has provided the key to the future. Two new laser printers, that deliver the performance, functionality and cost advantages of a workgroup mono laser printer, with the added advantage of colour. From memos and business reports to eye-catching catalogues, Lexmark's C780n and C782n laser printers give you everything you need to leverage the many benefits that colour can bring to the office. So now you can combine your mono and colour printers into one, versatile and reliable device.

Serious performance for high-volume printing

Robust and reliable, the Lexmark C780n and C782n come network-ready and integrate seamlessly into your existing network environment. In virtually no time at all you'll be set up and running through your heaviest print jobs at record speeds! Besides their competitive time to first page, both printers are incredibly fast. In fact, the C782n can reach up to 38 ppm in mono and 33 ppm in colour. So you can reduce the wait and get your documents in your hands faster.

Leverage the power of colour

And while performance is crucial for the workgroup printer of the future, it's quality colour that demands the attention and produces the results. With our newly enhanced toner and long-term colour-science expertise, the results speak for themselves: crisp, professional-looking text, rich flesh tones and consistent images every time, from first page to last. Ensure the Lexmark C780n and C782n provide you with the power to communicate the key messages and represent your business in the best light.

Easier than ever to manage

What better way to boost productivity than by offering your employees a simple and secure new way of working? These printers are remarkably simple at every level, from set-up to maintenance. The front-loading consumables take just seconds to replace, while the intuitive operator panel coaches your end-users through printing and maintenance tasks with ease. And thanks to the cutting-edge security features with convenient numeric pad, you're always ensured true confidential printing.

No worries – colour costs are under control!

The benefits of colour are widely recognised, however until now, they have come at price. However, the Lexmark C780n and C782n were designed to put you in total control of colour costs. In addition to high-yield cartridges and a low cost per page, both printers come equipped with Lexmark's unique ColorCare technology, a complete range of colour-cost-control tools. This includes convenient budget-friendly features, such as user-specific colour-print-permission settings, which let you limit which users can print in colour based on their specific job functions.

Getting the 'right fit'

In addition to ensuring you keep the costs of printing in colour to a minimum, Lexmark has also focused on making sure productivity is maximised. Lexmark's Right Fit range of product options gives you the ability to customise the Lexmark C782n to meet the specific requirements of every individual workgroup in your organisation. You can choose from document stapling, high capacity envelope feeding, separated output for individual users to minimise wastage, or a full upgrade to print, copy, fax and scan multifunction, using Lexmark's X4600 MFP option. Further to this, the Lexmark C780 series supports printing on UV and water resistant media (ideal for outdoor or 'wet area' signage and mapping), long-life vinyl labels, multi-part forms, pharmaceutical labels and for medical imaging purposes.

Lexmark's guarantee to you

At Lexmark, the goal is to ensure you achieve maximum productivity, and minimum downtime and cost of ownership. The Lexmark C780 and C782 are supported by Lexmark's comprehensive on-site warranty. In addition to the standard on-site support, you can choose from a wide range of flexible service options built specifically to meet your business's unique needs.

Part numbers for other options

C782 Paper Handling Options		Part Number
Lexmark C772/C780/C782 500-Sheet Drawer		20B2300
Lexmark C772/C780/C782 500-Sheet Tray		20B2373
Lexmark C772/C780 2000-Sheet Drawer		20B2700
Lexmark C772/C780 Envelope Drawer		20B3100
Lexmark C772/C780/C782 Duplex Unit		20B2400
Lexmark C772/C780 Output Expander		20B3050
Lexmark C772/C780 5-Bin Mailbox		20B3000
Lexmark C772/C780 Banner Tray		20B5000
Lexmark C772 Outdoor Media Drawer		20B3340
Lexmark C772/C780 StapleSmart Finisher		20B3060
MFP Upgrade		
Lexmark X4600 MFP Option + Installation for C782n		10D1788
Furniture		Part Number
Lexmark X4600 scanner stand (Required for finishing options)		10D1632
Lexmark C782 printer stand		16N1708
Lexmark X4600 scanner shelf		21J0055

Technical Specifications

Print technology	Colour Laser
Print speed	C780n: Mono 33ppm, Colour 29ppm C782n: Mono 38ppm, Colour 33ppm
Time to first page	Mono: <11 seconds, Colour: 13 seconds
Processor	800 MHz
Memory	Standard: 256 MB, Maximum: 768 MB
Resolution	Black: 1200 x 1200 dpi, 2400 Colour Quality
Duty cycle	120,000 pages per month
Expandable memory options	256 MB, 512 MB
Emulation	PostScript Level 3 Emulation, PCL 6 Emulation, PDF v1.5
Operating Systems Supported	Microsoft Windows: 2000, NT, ME, XP, Server 2003, 98 2nd Edition, XP Professional x64 Novell Netware: 3.2, 4.2, 5.x and 6.x, Microsoft Vista UNIX: Sun Solaris 7, 8, 9, 10, HP-UX 11.00, 11.11, IBM AIX 5.1, 5.2, 5.3 Linux: Red Hat Linux 7.3, 8.0, 9.0, other systems Mac OS: 9.x, X IBM: AS/400 Systems
Paper Handling	Standard: 500-Sheet Input Tray, 100-Sheet MPF, 250-Sheet Output Bin, Optional: 500-Sheet Drawer, 2000-Sheet Drawer
Paper Input Capacity	Standard: 500 pages, Maximum: 2100 pages
Paper Output Capacity	Standard: 250 pages, Maximum: 1000 pages
Finishing Option	5-Bin Mailbox, Lexmark StapleSmart Finisher, Output Expander *Supported on the C782n only
Number of Paper Inputs	Standard: 2, Maximum: 5
Media Supported	Banner paper, Transparencies, Glossy Paper, labels, Plain Paper, Envelopes, Card Stock
Media Sizes Supported	A4, A5, Executive, Folio, JIS-B5, Legal, Letter, Universal, Envelope, 10, B5, DL
Media weights Supported	60 - 300 g/m ² Vinyl labels. *Refer to CardStock and Label guide for full reference
Standard ports	Ethernet 10/100, USB 2.0
Optional network ports	Ethernet 10/100/1000, FibreOptic, Wireless G, USB 2.0
Optional adapter	Coax/Twinax Adapter for SCS, External Ethernet 10/100BaseTX, External Token-Ring, Internal Ethernet 10/100BaseTX, Internal Fiber 100Basefx, Lexmark N4000e for Ethernet 10/100BaseTX, Lexmark N4050e 802.11g Wireless Print Server, Internal Gigabit Ethernet, Internal 802.11g Wireless
Security Features	Secure Management with MarkVision Professional, Secure Network Communications, Confidential Print, PrintCrypton, Digitally Signed Firmware Update Files, Encryption for Optional Internal Hard Disk Drives, Operator Panel Menu Lockout, Printing Lockout, Secure Socket Layer
Product guarantee	Two Years OnSite Warranty ¹
Size (H x W x D)	528 x 604 x 470 mm
Weight	68 kg
Acoustics	30 dB(A) ready, 53 dB(A) printing
Product certifications	FCC Class B, UL 60950-1, U.S. FDA, IEC 60320-1, CAN/CSA-C22.2 60950-00, ICES Class B, CE Class B, CB IEC 60320, IEC 60825-1, GS (TÜV), SEMKO, UL AR, CS, TÜV R, ACA C-tick mark Class B, BSMI Class B, CCC Class B, EK, MIC
Specified operating environment	Temperature: 15.6 to 32.2° C (60 to 90° F), Humidity: 8 to 80% Relative Humidity, Altitude: 0 - 3048 meters (10,000 ft.)
Part numbers	C780n - 10Z0286, C780dn - 10Z0287 & C780dtn - 10Z0288 C782n - 10Z0186, C782dn - 10Z0187 & C782dtn 10Z0188
Supplies	C780n - Ships with 6K pages CMYK C782n - Ships with 10K pages CMYK - 6K pages CMYK standard yield print cartridges – C-C780A1CG, M-C780A1MG, Y-C780A1YG, K-C780A1KG - 10 K pages CMYK high yield print cartridges – C-C780H1CG, M-C780H1MG, Y-C780H1YG, K-C780H1KG - 15 K pages CMYK extra high yield print cartridges – C-C782X1CG, M-C782X1MG, Y-C782X1YG, K-C782X1YG - 180K Mono/50K Colour Waste Toner Bottle - 10B3100

Lexmark supports the environment by reducing paper wastage. As one of the many environmental initiatives Lexmark does not pre-print brochures.



¹Local warranty conditions apply. For further details please contact your nearest Lexmark office.



Lexmark and Lexmark with diamond design are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. Operating speeds may vary according to document complexity, software application & system configuration.

www.lexmark.com.au

LEXMARK
TM