

lyriQ Flush Mount Single Source Input, Black

AU1004-BK



Distributes high quality audio to multiple locations throughout the home with the similar functionality as the AU7398, plus additional features.

features & benefits

- Automatically overrides the remote source
- For use with the lyriQ Audio System

specifications

General Info

Color: Black
Product Series: Studio

Construction Information

Installation Location: In-Wall

Cord Information

Pinning:

1. Green/White L- (PreGND)
2. Green L+
3. Orange/White Audio R- (PreGND)
4. Blue IR_IN (IR TX)
5. Blue/White Status_Out (IR RX)

- 6. Orange Audio R+
- 7. Ground
- Brown/White
- 8. Brown Power (+24 Vdc)

Technical Information

Frequency Response: 20 - 100Hz \pm 4dB; 100 - 20,000Hz \pm 2dB

Humidity: Up to 90% RH (non-condensing)

IR Receive Frequency: 10 KHz \pm 5 KHz to 110 KHz \pm 5 KHz

Operating Temperature Fahrenheit: 0 to 55 Degrees Celsius

Power Requirements: +24Vdc supplied by the Distribution Module

Storage Temperature: -25 to +75 Degrees Celsius