



Philips 5000 series
LCD TV with Pixel Plus 3
HD

42" class

Full HD 1080p digital TV

42PFL5704D



Brilliant design, powerful performance.

Save energy with this Eco TV™

Experience leading-edge style, performance and energy efficiency. Combining a full HD 1080p display, Pixel Plus 3 HD engine and fantastic invisible sound, this eco-friendly TV delivers powerful performance while conserving our future.

See vivid and razor sharp pictures

- Pixel Plus 3 HD for most sharp and clear pictures
- 120Hz Clear LCD, 2ms performance for superb motion sharpness
- Full HD LCD display, with a 1920x1080p resolution
- HD Natural Motion for ultra smooth motion in Full HD movies

Hear pure and powerful sound

- 30W RMS high audio power
- Dolby Digital output for connection to a home theatre system
- Invisible speakers with incredible surround

Easy to connect and enjoy

- Settings assistant for effortless personalized TV settings
- 4 HDMI inputs with Easylink for a full HD connection
- USB for fantastic photo and music playback

Ready for digital

- ATSC & QAM tuner receives over the air and unscrambled cable



PHILIPS

sense and simplicity

Specifications

Picture/Display

- **Aspect ratio:** Widescreen
- **Viewing angle:** 178° (H) / 178° (V)
- **Brightness:** 500 cd/m²
- **Panel resolution:** 1920x1080p
- **Dynamic screen contrast:** 29000:1
- **Response time (typical):** 2 ms
- **Picture enhancement:** Pixel Plus 3 HD, 120Hz LCD, HD Natural Motion, 3/2 - 2/2 motion pull down, 3D Combfilter, Active Control + Light sensor, Dynamic contrast enhancement, Progressive Scan
- **Diagonal screen size:** 42 inch / 107 cm
- **Visible screen diagonal (inch):** 42.02 inch

Supported Display Resolution

- **Computer formats**

Resolution	Refresh rate
640 x 480	60Hz
800 x 600	60Hz
1024 x 768	60Hz
1280 x 768	60Hz
1280 x 1024	60Hz
1360 x 768	60Hz
1920 x 1080	60Hz
- **Video formats**

Resolution	Refresh rate
480i	60Hz
480p	60Hz
720p	60Hz
1080i	60Hz
1080p	60Hz

Sound

- **Equalizer:** 5-bands
- **Sound Enhancement:** Incredible Surround
- **Output power (RMS):** 30W
- **Sound System:** Dolby Digital (AC-3), Stereo, SAP

Loudspeakers

- **Built-in speakers:** 4

Convenience

- **Child Protection:** Child Lock+Parental Control
- **Clock:** On main display, Sleep Timer
- **Ease of Installation:** Autostore
- **Ease of Use:** 4 favorite lists, Auto Volume Leveller (AVL), Channel list, Settings assistant Wizard, Side Control
- **Remote Control:** TV
- **Screen Format Adjustments:** 4:3, Auto Format,

Movie expand 14:9, Movie expand 16:9, Super Zoom, Widescreen, unscaled (1080p dot by dot)

Multimedia Applications

- **Multimedia connections:** USB memory class device
- **Playback Formats:** MP3, Slideshow files (.alb), JPEG Still pictures

Tuner/Reception/Transmission

- **Aerial Input:** 75 ohm F-type
- **TV system:** ATSC, NTSC
- **Video Playback:** NTSC
- **Cable:** Unscrambled Digital Cable -QAM
- **Tuner bands:** Hyperband, S-Channel, UHF, VHF

Connectivity

- **AV 1:** Audio L/R in, YPbPr
- **AV 2:** Audio L/R in, YPbPr
- **AV 3:** CVBS in, S-Video in
- **HDMI 1:** HDMI v1.3
- **HDMI 2:** HDMI v1.3
- **HDMI 3:** Analog audio L/R in, HDMI v1.3
- **Audio Output - Digital:** Coaxial (cinch)
- **Front / Side connections:** HDMI v1.3, S-video in, CVBS in, Audio L/R in, Headphone out, USB
- **EasyLink (HDMI-CEC):** One touch play, Power status, System info (menu language), System audio control, System standby

Power


- **Ambient temperature:** 5 °C to 40 °C
- **Mains power:** 110-240V, 50-60Hz
- **Power consumption:** 210 W
- **Standby power consumption:** < 0.15 W

Dimensions

- **Set dimensions in inch (W x H x D):** 41.18 x 25.39 x 3.48 inch
- **VESA wall mount compatible:** 400 x 400 mm
- **Set dimensions with stand in inch (W x H x D):** 41.18 x 28.19 x 10.31 inch
- **Weight incl. Packaging (lb):** 66.25
- **Product weight (lb):** 44.53
- **Product weight (+stand) (lb):** 54.01 lb
- **Box dimensions in inch (W x H x D):** 45.31 x 31.22 x 13.11 inch

Accessories

- **Included Accessories:** Tabletop swivel stand, Power cord, Quick start guide, User Manual, Registration card, Remote Control



LCD TV with Pixel Plus 3 HD
42" class Full HD 1080p digital TV



42PFL5704D/F7

Product highlights

Pixel Plus 3 HD

Pixel Plus 3 HD offers the unique combination of ultimate sharpness, natural detail, vivid colors and smooth natural motion on all qualities of HD, standard TV signals and multimedia content, for high definition displays. Each pixel of the incoming picture is enhanced to better match the surrounding pixels, resulting in a more natural picture. Artifacts and noise in all sources from multimedia to standard TV and also in highly compressed HD are detected and reduced ensuring that the picture is clean and razor sharp.

120Hz Clear LCD (2ms)

120Hz Clear LCD creates extreme motion sharpness for clear and vibrant images even with fast on-screen motion. The Double Frame Rate Insertion works with a high 120Hz refresh rate. It increases the sharpness of motion reproduction to more than twice that of conventional LCD, resulting in a response time of 2 milliseconds (measured in Perceived Blur-Edge-Width; BEW). This unique Philips technology brings motion sharpness of LCD displays to an unprecedented level.

Full HD LCD display 1920x1080p

The Full HD screen has the widescreen resolution of 1920 x 1080p. This is the highest resolution of HD sources for the best possible picture quality. It is fully future proof as it supports 1080p signals from all sources, including the most recent like Blu-ray and advanced HD game consoles. The signal processing is extensively upgraded to support this much higher signal quality and resolution. It produces brilliant flicker-free progressive scan pictures with superb brightness and colors.

HD Natural Motion

Philips invented HD Natural Motion to eliminate juddering effects that are visible with movie based picture content. HD Natural Motion estimates motion in the picture and corrects juddering movements in both broadcast and recorded movie material (such as DVD and Blu-ray Disc). The resulting smooth motion reproduction and excellent sharpness take the viewing experience to a higher level. HD Natural Motion removes judder from SD and HD pictures, including 1080p, for a motion performance that surpasses the cinema!

Invisible speakers

An invisible sound system that blends perfectly with the design of the cabinet. The Incredible Surround allows you to experience total surround with greater depth and width of sound. It gives a clear and spacious sound stage complementary to the rich viewing experience.

4 HDMI inputs with EasyLink

EasyLink uses the HDMI CEC industry standard protocol to share functionality between connected devices and the TV. With Easylink only one remote control is needed to operate main functionalities on your TV and connected devices. HDMI makes an uncompressed digital RGB connection from the source to the screen for the ultimate picture quality. HDMI uses HDCP copy protection. With 3 HDMI inputs on the back and 1 HDMI on the side of the TV you can connect multiple HD sources, for instance an HD settop box, a Blu-ray player, and Game Console or Digital Camcorder.

USB for photo & music playback

The USB connector allows access to jpeg photos and mp3 music of most USB-sticks (USB memory-class device). Plug the USB into the slot at the side of the TV and access your photos or music files. You can easily view and share your photos and music.



Issue date 2009-03-02

Version: 2.5.5

12 NC: 8670 000 47552
UPC: 6 09585 16271 6

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com