

Computer Power Cord, NEMA 5-15P to C13 - Heavy-Duty, 15A, 125V, 14 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P007-002









Computer power cord connects a server, computer, monitor, printer or other device with a C14 inlet to an AC outlet on a PDU.

Features

5-15P to C13 Power Cable for Network Devices That Require a Heavy-Gauge ConnectionThis computer power supply cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. You can use it to connect a computer, server, monitor, laser printer or drive to a PDU, UPS, surge protector or AC wall outlet. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering larger servers, laser printers and other network devices
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- Computer power cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, large servers and laser printers to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source in a rack

Package Includes

P007-002 Desktop Computer
Power Cord, 5-15P to C13, 2-ft.
(0.61 m), Black

Specifications

| OVERVIEW | | |
|----------------------|---|--|
| UPC Code | 037332150011 | |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU | |
| Country/Region | North America | |
| INPUT | | |
| | | |
| Maximum Input Amps | 15 | |





| Voltage Compatibility (VAC) | 125 |
|--|---------------------------|
| PHYSICAL | |
| Color | Black |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 14 |
| Wire Gauge (OD - mm²) | 2.08 |
| Cable Length (ft.) | 2 |
| Cable Length (m) | 0.6 |
| Power Cord Jacket Type | SJT |
| Shipping Dimensions (hwd / cm) | 25.40 x 18.03 x 1.27 |
| Shipping Dimensions (hwd / in.) | 10.00 x 7.10 x 0.50 |
| Shipping Weight (kg) | 0.15 |
| Shipping Weight (lbs.) | 0.33 |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA 5-15P |
| Side B - Connector 1 | IEC-320-C13 |
| SPECIAL FEATURES | |
| High Voltage | No |
| Locking Plug | No |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies