

45U 3300lb High Capacity 4 Post Open Server Equipment Rack - Flat Pack

Product ID: 4POSTRACKHD



This 45U 4 Post Open Frame Server Equipment Rack offers a solid, reliable solution for mounting servers, UPSs, and other heavy rack-mountable equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Supporting a total weight capacity of up to 3300lbs - nearly double the capacity of competitive models, this full size (45U) rack features an open frame design with heavy gauge mounting rails that ensure exceptional structural stability.

Built to meet EIA standards for 19in racks, the 4-post open frame rack is compatible with equipment and accessories from most popular manufacturers.

A durable, cost-effective server room storage solution, StarTech.com's DuraRak 45U 4 Post Open Frame Server Equipment Rack is backed by 2-year warranty.

Certifications, Reports and Compatibility



Applications

- Ideal mounting option for heavy equipment like UPSs and storage servers in environments such as server farms, factory and other industrial applications
- Equipped to support servers, KVM switches, networking equipment and cabinet consoles
- Suitable for rack mount equipment where security at the rack level is not required

Features

- Fixed heavy duty rails with front/rear and side mounting options
- Easily route, manage and access your equipment cables without any obstruction
- TAA compliant for GSA Schedule purchases
- Heavy-duty design supporting a maximum weight load of 3300 lb. (1493.21 kg.) with Pre-drilled holes allowing the rack to be secured directly to the floor for additional stability
- Open frame design with heavy gauge mounting rails provides exceptional structural stability
- Provides ample ventilation and unobstructed air flow keeping your rack mount equipment at room temperature
- Meets ANSI/EIA RS-310-D standards
- Package includes all necessary hardware to assemble the rack with a **free** pack of 50 cage screws and nuts for immediate hardware installation
- Flat-pack packaging for easier handling and reduced shipping expenses. Assembles in minutes.

	Warranty	Lifetime
Hardware	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	G-Shape
	Rack Type	4-Post
	Special Features	Base Plate with Floor-Anchoring Holes Built-in Cable Management Easy Assembly U-Markings
Performance	U Height	45U
	Wallmountable	No
Physical Characteristics	Weight Capacity	3300 lb [1493.2 kg]
Product Measurements	Color	Black
	Construction Material	Steel
Packaging Information	Maximum Mounting Depth	35.9 in [91.3 cm]
	Product Height	84.1 in [213.5 cm]
	Product Length	35.9 in [91.3 cm]
	Product Width	24 in [61 cm]
	Weight of Product	112.3 lb [50.8 kg]
What's in the Box	Flat Pack (Assembly Required)	Yes
	Package Height	3.5 in [90 mm]
	Package Length	7.1 ft [2.2 m]
	Package Width	19.9 in [50.5 cm]
	Shipping (Package) Weight	122.3 lb [55.3 kg]
Included in Package		
1 - 4 Post Heavy Duty Rack Assembly Kit		
50 - #10-32 Screws		
50 - #10-32 Cage Nuts		
1 - Assembly instructions		

Product appearance and specifications are subject to change without notice.