



HP Designjet 815mfp

Large-format multi-functional printer

Fully integrated standalone solution
High performance
Ease-of-use

Now, your office can truly enjoy the benefits of an integrated large-format multi-function solution.

Digitise and archive your large-format originals by scanning directly to CD, file or network in photo-realistic colours, high quality grayscale and crisp black-and-white. Print and copy high quality outputs at ease with the user-friendly software via touch-screen graphical display and keyboard. The HP Designjet 815mfp handles CAD output, GIS, graphics, large-format originals effectively and professionally.



HP Designjet 815mfp

1. Colour copy and print up to 42-inch wide straight from the HP Designjet 815mfp. You can also remote print to other HP Designjet large-format printers (HP Designjet 500, 800, 1000 plus, 5000 and 5500 series) on the network.

2. Fully operable from panel PC. Access scan, copy and print functions straight from the user-friendly graphical touch-screen display and keyboard.


3. Convenient archival functions. Scan directly to CD via CD writer (8x 8x 32x) built into the panel PC. Scan direct to file or network using intuitive software.

4. Bigger hard disk space for faster processing and bigger storage (6 GB—printer, 14 GB—control panel)



Fully integrated multi-function capability —A complete standalone solution

The HP Designjet 815mfp is a complete, self-contained solution that puts a printer, scanner, front-panel PC, keyboard, and software all in a single footprint that fits your workspace. Manage large-format documents from scan through print or archive seamlessly and efficiently.



Intelligent high performance features

The HP Designjet 815mfp delivers outstanding print, scan and copy features that are intelligent and user-friendly. You can achieve professional quality by using advanced colour-management, image-enhancement, and calibration features built into HP Designjet 815mfp.

Excellent print quality

HP Designjet 815mfp create scans and prints at a level of detail that is comparable to the originals. Scan or print at a resolution of up to 2400 dpi enhanced, up to 42 inches wide. Achieve vivid, colour accurate prints and copies consistently with 2400 x 1200 dpi resolution, HP's Color Layering Technology and automatic closed-loop colour calibration.

Remote printing capable

Batch and network printing for greater productivity. The HP Designjet 815mfp includes a print-list feature that you can use to print your scanned jobs in unattended batches. You can also set up additional HP Designjet printers on your network and then print these files remotely through these HP Designjet printers from the HP Designjet 815mfp touch screen.

Key print features

- Print technology—HP Thermal Inkjet with HP Color Layering Technology and automatic closed-loop colour calibration
- Print resolution—2400 x 1200 dpi
- Line accuracy— $\pm 0.2\%$
- Print speed—economic quality (colour) 7.9 m²/h (85 ft²/h)
—normal quality 3.3 m²/h (36 ft²/h)
—photo quality 2 m²/h (21 ft²/h)
- Ink—4 ink with pigment-based black and dye-based colour
- Scan file formats—PDF, TIFF, JPEG, CALSG4





Flexible scanning

Built-in scanner accepts originals up to 43 inches (42-inch scan width—1092 mm) wide, and up to 15 mm (0.6-inch) thick, so you can even scan oversized and heavyweight originals into common file formats—PDF, TIFF, JPEG and CALSG4

Advanced scan features

Perfect your image by using the colour correction and 2D-filters for colour sharpening, image softening, and blurring. The monochrome dual 2D-adaptive enhancement technology produces clean and crisp scans even from poor-quality originals. Together with the calibration wizard, you can ensure that your scans, copies, and prints consistently show HP quality and consistency.

Key scan features

- Technology—double tri-linear colour CCDs; 21 360 pixels (RGB triplets); 36 bits of data capture; all-digital cameras
- Resolution—optical: 424 dpi; enhanced: 2400 dpi
- Line accuracy— $\pm 0.15\%$
- Image digital processing—dual 2D-adaptive enhancement, dual 2D-adaptive gray, ADL+ error diffusion halftoning, 2D-sharpening, 2D-softening and 2D-blur filter; 2D-adaptive thresholding
- Scan speed—colour: 3.8 cm/sec (1.5-inch/sec); black and white: 7.6 cm/sec (3-inch/sec)
- Scan modes—24-bit colour, 8-bit gray tone, copy modes with gray shades, 1-bit black-and-white, black-and-white dual 2D-adaptive modes
- Scan file formats—PDF, TIFF, JPEG, CALSG4

User-friendly copy functions

The advanced copy functions of the HP Designjet 815mfp help you make copies quickly and easily. Skew is never a problem when you use the auto-alignment option to load and preview your original. Enlarge or reduce images (1 to 10000%) and adjust margins to create the ideal image.

Use the nesting option to save media, and make extra-large enlargements easily with the panelling option. You can also track your output by using the integrated accounting features.



2D-adaptive threshold



Ease-of-use

The HP Designjet 815mfp is easy to learn, operate and master even for users who are not literate in large-format printing, scanning or copying.

After the plug-and-play installation, operation is intuitive, even untrained users can produce great copy, scan, and print results from the intuitive touch-screen display.

User-friendly

Intuitive software meets all your print, scan and copy needs at your finger tips. The friendly, graphical touch-screen display gives you clear, hassle-free operation.

The graphical interface walks the user through the appropriate procedure to produce the type of document or file that you need.

Convenience

Offer your customers, clients, and co-workers the convenience of having scanned documents available on compact discs (CDs) or floppy disks. Save your scanned files in the most common file formats (PDF, TIFF, JPEG and CALSG4) directly to CD, via built-in CD writer, or to file or network.

The HP Designjet 815mfp fits seamlessly into your network. Using universal network standards, you can communicate easily across a network by using the keyboard that comes standard.

HP Designjet 815mfp at-a-glance

1. Receive data:

- Access stored files
- Access network
- Read from CD or floppy

2. Scan:

- Small and large-format originals (up to 43 inches wide)
- Thick or rigid media (up to 15 mm)
- Scan width up to 42 inches wide

3. Store:

- Store in the hard disk
- Store in the network
- Save to a CD or floppy
- Multiple formats

4. Remote print:

- Print file via other network printer
- HP Remote printing (US only)

5. Print:

- Batch printing
- Multiple copies
- And sets panelling, nesting

6. Copy:

- Single or multiple copies
- Enlarge/reduce
- Colour or black and white
- Panelling, nesting

7. Edit/enhance:

- Background cleaning
- Sharpen/blur
- Colour/light adjustment



HP Designjet 815mfp shown

HP Designjet 815mfp

Technical Specifications

Print Features

Technology	HP Color Thermal Inkjet
Max resolution	Print resolution 2400 x 1200 dpi
Print languages	Adobe PostScript® 3™, HP-GL/2, HP RTL, CALSG4
Print speed	Economic quality (colour) 7.9 m ² /h (85 ft ² /h) Normal quality 3.3 m ² /h (36 ft ² /h) Photo quality 2 m ² /h (21 ft ² /h)
Line accuracy	+/- 0.2 % (printer)

Scan Features

Technology	Double tri-linear colour CCDs; 21360 pixels (RGB triplets); 36 bits of data capture; all-digital cameras
Resolution	Optical: 424 dpi; enhanced: 2400 dpi
Scanner image digital processing	Dual 2D-adaptive enhancement, dual 2D-adaptive gray, ADL+ error diffusion halftoning, 2D-sharpening, 2D-softening and 2D-blur filter; 2D-adaptive thresholding
Scan speed	Colour: 3.8 cm/sec (1.5-inch/sec) Black and white: 7.6 cm/sec (3-inch/sec)
Scan modes	24-bit colour, 8-bit gray tone, copy modes with gray shades, 1-bit black-and-white, black-and-white dual 2D-adaptive modes
Line accuracy	+/- 0.15%
Reduce/enlarge	1 to 10000%

Media

Roll	Core diameter: 6.35 cm (2.5-inch) Max roll length: 45 m (150 ft) Media sizes: 8.3 to 42-inch wide sheets; 24, 36 and 42-inch rolls
Media length	1897 mm
Media width	Printer: 42-inch; scanner: 43-inch
Max scan width	42-inch
Media weight	Up to 210 g/m ² (up to 56 lb)
Media thickness	Up to 15 mm (0.6-inch)
Media sizes	Metric: ISO AO, ISO A1, ISO A2, ISO A3, ISO A4, JIS B4, JIS B3, JIS B2, JIS B1 US: ANSI A, ANSI B, ANSI C, ANSI D, ANSI E, ARCH A, ARCH B, ARCH C, ARCH D, ARCH E, ARCH E1
Media types	HP Bright White Inkjet Paper (bond), Translucent Bond, Natural Tracing Paper, Vellum, Clear Film, Matte Film, Coated Paper, Heavyweight Coated Paper, High-Gloss Photo Paper, Semi-Gloss Photo Paper, Paper-Based Semi-Gloss, Satin Poster Paper, Studio Canvas, Banners with Tyvek, Colorfast Adhesive Vinyl
Paper handling	Printer: single-sheet feed, roll feed, automatic cutter, standard bin; Scanner: straight-through scan paper path for sheet and cardboard originals, all-wheel drive (contour adjustment, precision rollers)

Interface

User interface	Touch-screen and keyboard
Front panel/control panel	Print/scan/copy operation controlled through an easy-to-use LCD colour touch-screen and intuitive software.
CD drive type	CDRW (8x 8x 32x)

System

Processor	Intel Pentium III—850 MHz
Compatible network operating system	Printer: Novell NetWare v. 3.11, 3.12, 4.X, 5.0; NDS (IPX/SPX); NDPS (TCP/IP, IPX/SPX); Microsoft® Windows® 95, 98; (TCP/IP, IPX/SPX); Microsoft Windows NT® 4.0, XP; (TCP/IP, IPX/SPX, DLC/LLC); Microsoft Windows 2000; IBM OS/2 WARP v. 3.0, 4.0; (TCP/IP, DLC/LLC); HP-UX v. 10.X, 11.X; Sun Solaris 2.5X, 2.6; IBM AIX v. 3.2.5 and later; MPE-IX v. 5.5 (TCP/IP); Line printer Daemon (LPD); Mac OS 9.X (TCP/IP, Apple talk); Mac OS X (TCP/IP); Artisoft LANtastic v. 7.0 (DLC/LLC); Internet printing protocol Scanner: NDPS (TCP/IP); Microsoft Windows 95, 98; (TCP/IP); Microsoft Windows NT 4.0, XP; (TCP/IP); Microsoft Windows 2000; IBM OS/2 WARP v. 3.0, 4.0; (TCP/IP); HP-UX v. 10.X, 11.X; Sun Solaris 2.5X, 2.6; IBM AIX v. 3.2.5 and later; MPE-IX v. 5.5 (TCP/IP); Mac OS 9.X and X (TCP/IP)
Compatible operating system	Printer: Microsoft® Windows® (95, 98, Me, NT 4.0, 2000, XP), Mac OS 9.X, Mac OS X, ZEHRaster for UNIX®; scanner: Microsoft Windows (95, 98, Me, NT 4.0, 2000, XP) through Windows domain or FTP service, Mac OS 9.X and Mac OS X through FTP service, UNIX/Linux through FTP service
Memory	Standard memory 256 MB 6 GB for printed jobs (in the printer) 14 GB for scanned jobs (in the control panel)
Connectivity	External I/O ports: 1 Centronics parallel IEEE 1284-compliant (ECP), 1 HP Jetdirect 615n (EIO) 10/100Base-TX, 1 Fast Ethernet 10/100Base-TX network card for scan to file Connectivity, Std Printer—Centronics parallel IEEE 1284-compliant (ECP), HP Jetdirect 615n EIO internal print server for Fast Ethernet 10/100Base-TX; scanner: additional Fast Ethernet 10/100Base-TX network card
Remote network printer windows	Windows®—Microsoft® Windows® 95, 98, NT, 2000, XP Mac—Mac 9.1 or later
Printer drivers included	Printer: Microsoft® Windows® 95, 98, Me, NT 4.0, 2000, Macintosh OS 8.1 or later, AutoCAD™ 2000, R 13, R 14, for Windows Scanner: Microsoft Windows drivers for HP Designjet 500, 800, 1000 plus, 5000 and 5500 Printer Series

HP Designjet 815mfp

Technical Specifications

Software included	PostScript® drivers for Microsoft® Windows® (95, 98, Me NT 4.0 and 2000), Macintosh (OS 8.1 or later); HPGL/2-RTL drivers for Microsoft Windows (95, 98, Me, NT 4.0, 2000); drivers for AutoCAD™ (2000, R 13, R 14, for Windows); for UNIX®, TIFF and JPEG files are accepted via ZEHRRaster Plus software, supplied with the printer; system recovery software for the scanning system including HP Macroinstaller with Microsoft Windows drivers for HP Designjet 500, 800, 1000 plus, 5000 and 5500 Printer Series
Dimensions and Weight	
Volume (w x h x d)	2020 x 840 x 1500 mm (79.5 x 33 x 59-inch)
Weight	180 kg (396.8 lb)
Power	
Power consumption	330 W
Power supply	100 to 240 VAC (+/-10%) auto-ranging, 50/60 Hz, 8 amp maximum
Operating sound pressure	54 dB
Safety and Compatibility	
Electromagnetic compatibility	Compliant with the requirements for Class A ITE products: EU (EMC Directive), USA (FCC Rules), Canada (DoC), Australia (ACA), New Zealand (MoC), Japan (VCCI), Taiwan (BSMII)
Safety	ITE product compliance, EU IVD, UL Certified for US and Canada, Mexico NOM-1-NYCE, Argentina: IRAM, Russia: GOST, Poland PCBC, and others
Others	
Warranty	One-year, next-business-day, on-site warranty Warranty varies according to countries. Please check with your local Hewlett-Packard sales offices or your nearest HP authorised dealer for details.
What's in the box	HP Designjet 815mfp including HP Designjet 800ps printer, scanner, touch-screen, keyboard, built-in HP Jetdirect 615n for Fast Ethernet 10/100 Base-TX network card, additional Fast Ethernet 10/100 Base-TX network card, printer and scanner stands, media bin, spindle, power cords, ink cartridges, printheads, roll of media, print/scan/copy software, HP Macroinstaller with Microsoft Windows drivers for HP Designjet 500, 800, 1000 plus, 5000 and 5500 series printers HP-GL/2, AutoCAD™ and PostScript® drivers for Windows®, PostScript driver for Macintosh, ZEHRRaster Plus for UNIX®, system recovery software CD, quick reference guide, setup poster, user documentation CD, (interface cables must be ordered separately)
Accessories	HP spindle C2389A, IEEE 1284-compliant bidirectional parallel cable (3 m) C2951A, memory module (128 MB) C2388A, HP Jetdirect (EIO 10Base-T) J3110A, HP Jetdirect (10Base2, 10Base-T, LocalTalk) J3111A, HP Jetdirect (Token Ring) J4167A, power cords; 8120-1369 (Australia), 8120-1689 (Korea), 8120-1378 (Taiwan), 8120-8705 (Hong Kong), 8120-8376 (China (English)), 8120-6798 (Japan) 8120-8871 (Philippines), 5080-3149 (Japan converter)

For more information, visit our website at <http://www.designjet.hp.com>, or call your local Hewlett-Packard sales office or your nearest HP authorised dealer:

HP customer information centre (for product information)

Australia	132347
China	+86 21 2898 2255
Hong Kong	+852 800 938 833
India	+9628 123 123 (Del/Mum/Blr) +1600 444 999 (other cities)
Indonesia	+0800 1111 222
Korea	+080 703 0700
Malaysia	+1800 88 4848
New Zealand	+0800 733 547
Philippines	+1800 1331 4488
Singapore	+1800 278 8100
Taiwan	+0800 236 686
Thailand	+662 353 9000
Vietnam	+848 823 6215

For the following countries, please fax your queries to: +65 6 275 6707
• Bangladesh • Brunei • Cambodia • Pakistan • Sri Lanka

HP customer care centre (for post-sales service)

Australia	+61 3 8877 8000
China	+86 10 6564 5959
Hong Kong	+852 800 96 7729
India	+91 11 682 6035
Indonesia	+62 21 350 3408
Korea	+82 2 3270 0700
Malaysia	+60 3 2695 2566
New Zealand	+64 9 356 6640
Philippines	+63 2 867 3551
Singapore	+65 6 272 5300
Taiwan	+886 2 2717 0055
Thailand	+662 353 9000
Vietnam	+848 823 4530

Ordering information

Number	Description
Q1279A	HP Designjet 815mfp
Service and support	
H4518A/E	Installation for 1 network configuration for HP Designjet network printer
U2006A/E	Next business day onsite, HW support, 3 year
U3535PA/E	Post warranty service, next business day onsite, HW support, 1 year
Supplies and accessories	
C2389A	HP Spindle
HP ink cartridges	
C4844A	HP no. 10 black ink cartridge
C4911A	HP no. 82 cyan ink cartridge
C4912A	HP no. 82 magenta ink cartridge
C4913A	HP no. 82 yellow ink cartridge
HP printheads	
C4810A	HP no. 11 black printhead
C4811A	HP no. 11 cyan printhead
C4812A	HP no. 11 magenta printhead
C4813A	HP no. 11 yellow printhead
Media	
C7923A/C7924A	HP Basic Heavyweight Coated Paper, 24"/36" roll
C7925A	HP Basic Heavyweight Coated Paper, 42" roll
C8281A/C8282A	HP Basic Coated Paper, 24"/36" roll
C8315A/C8316A	HP Basic High-gloss Photo Paper, 24"/36" roll
C8317A	HP Basic High-gloss Photo Paper, 42" roll
C8310A/C8311A	HP Basic Photo Satin Paper, 24"/36" roll
C8312A	HP Basic Photo Satin Paper, 42" roll
C6035A/C6036A	HP Bright White Paper, 24"/36" roll
C6019B/C6020B	HP Coated Paper, 24"/36" roll
C6559B	HP Coated Paper, 42" roll
C6029C/C6030C	HP Heavyweight Coated Paper, 24"/36" roll
C6569C	HP Heavyweight Coated Paper, 42" roll
C6031A/C6032A	HP Semi-gloss Photo Paper, 24"/36" roll
C6571A	HP Semi-gloss Photo Paper, 42" roll
C6813A/C6814A	HP High-gloss Photo Paper, 24"/36" roll
C6787A	HP Banners with Tyvek®, 36" roll
C6775A	HP Colorfast Adhesive Vinyl, 36" roll
C6771A	HP Studio Canvas
51642A	HP Matte Film, 24" roll
51642B	HP Matte Film, 36" roll
C3876A/C3875A	HP Clear Film, 24"/36" roll
C3862A/C3861A	HP Vellum, 24"/36" roll
C3869A/C3868A	HP Natural Tracing Paper, 24"/36" roll
C3860A/C3859A	HP Translucent Bond, 24"/36" roll
Interface and cables	
C2951A	IEEE-1284 compliant parallel A-B cable, 3 m
Network	
J3111A	HP Jetdirect 600n EIO (10Base2, 10Base-T, LocalTalk)
J4167A	HP Jetdirect 610n EIO (Token Ring)

For more information on HP Care Pack, visit:
<http://www.hp.com/apac/hpservices/carepack>
HP Instant Support Professional Edition (ISPE),
visit: <http://instantsupport.asiapac.hp.com>

For specific warranty details, please check with your local country resellers.



Microsoft



www.designjet.hp.com

© 2003 Hewlett-Packard Development Company, L.P.

The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Printed in Singapore, 5981-7391EEP, 09/2003



i n v e n t