

42U Adjustable 4 Post Open Server Equipment Rack Cabinet

Product ID: 4POSTRACKBK



StarTech.com's DuraRak 42U Adjustable 4 Post Open Server Rack offers a solid, versatile solution for mounting servers and other networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This full size (42U) rack offers adjustable posts for maximum flexibility, and an open frame design with heavy gauge mounting rails to ensure exceptional structural stability.

To ensure broad compatibility, the 42U rack features an industry standard design for compatibility with equipment from popular manufacturers.

A cost-effective solution, the rack is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty, plus the rack is flat-packed for easier handling and assembly.

For even more versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed to the bottom of the 42U server rack.

Certifications, Reports and Compatibility



Applications

- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles
- Suitable for rack mount equipment where security at the rack level is not required

Features

- Open frame design with heavy gauge mounting rails provides exceptional structural stability
- Provides ample ventilation and unobstructed air flow keeping your rack mount equipment at room temperature
- TAA compliant for GSA Schedule purchases
- Easily route, manage and access your equipment cables without any obstruction
- Adjustable mounting rails ensure compatibility with many rack mount equipment
- Heavy-duty base with holes allow you to bolt the server rack to the floor when mounting heavy rack mount equipment

	Warranty	Lifetime
Hardware	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	C-Shape
	Rack Type	4-Post
	Special Features	Adjustable Mounting Rails Base Plate with Floor-Anchoring Holes Casters (Optional) Easy Assembly
	U Height	42U
	Wallmountable	No
Performance	Weight Capacity	994.5 lb [450 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Maximum Mounting Depth	39.2 in [99.5 cm]
	Minimum Mounting Depth	22.9 in [58.2 cm]
	Product Height	78 in [198 cm]
	Product Length	39.2 in [99.5 cm]
	Product Width	22.4 in [57 cm]
	Weight of Product	102.2 lb [46.3 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Package Height	6.8 in [17.2 cm]
	Package Length	6.9 ft [2.1 m]
	Package Width	25.8 in [65.5 cm]
	Shipping (Package) Weight	112.3 lb [50.8 kg]
What's in the Box	Included in Package	2 - Front/Rear Frame 2 - Floor Plates 6 - Adjustable Horizontal Arm 2 - Floor Mounting Brackets

- 1 - M8 Hex (Allen) key
- 8 - M8x25 Hex Socket Screws
- 42 - M5x15 Truss Head Screws
- 16 - Bushing Caps
- 50 - M5 Screws
- 92 - M5 Cage Nuts

Product appearance and specifications are subject to change without notice.