



PICO USB Drives

Super Talent's patented PICO USB drives pack huge capacities into a tiny case. Half the size of an SD card, each PICO drive is smaller than the plug at the end of a USB cable! But tiny does not have to mean fragile or slow. Encased in a sleek and solid metal housing, no-compromise PICO drives are shock- and water-resistant to hold up under harsh conditions. And we didn't forget to include zippy transfer speeds up to 200x. Our line of PICO USB drives have won over 80 awards to date including being featured on the cover of Popular Science magazine.

Features

- **Handy:** Extremely small and lightweight for easy portability
- **Stylish:** Available in five unique styles
- **Durable:** Shock resistant and water resistant
- **Hot Plug & Play:** Available

Specifications

- **Capacities:** 2GB – 32GB*
- **Speed:** 2GB - 4GB: Up to 133X
8GB - 32GB: Up to 200X
- **Dimensions:** A = 38.7mm x 12.4mm x 3.9mm
C = 31.3mm x 12.4mm x 3.4mm
D = 39.7mm x 13.5mm x 4.9mm
E = 34.8mm x 15.8mm x 5.2mm
- **Package:** Steel
- **Temperature:** Storage = -20°C to 85°C
Operating = 0°C to 60°C
- **USB:** USB 2.0 and 1.1 compatible
- **O/S Support:** Windows-Windows 98 and above
Mac- Mac 10.x and above
Linux

PICO A



Swivel Model

PICO C



Capless Model
(Chrome)

PICO C



Capless Model
(Gold)

PICO C



Capless Model
(Nickel Plated)

PICO D



Swivel Model

PICO E



Sliding Lid (Chrome)

PICO E



Sliding Lid (Gold)



■ PICO USB Drives

Packaging Options



Deluxe Gift Box



Standard Clam Shell



Jewelry Box

How much can my drive store?

	Format	2GB	4GB	8GB	16GB	32GB
Photos	JPEG (6 Megapixels)	672 photos	1,344 photos	2,688 photos	5,376 photos	10,752 photos
Music	MP3 (128 kbps)	480 songs	960 songs	1,920 songs	3,840 songs	7,680 songs
Video	MPEG-4 (384kbps-15fps)	9 hours	18 hours	35 hours	70 hours	140 hours

*approximate capacity based on average file sizes.

Ordering Information

	2GB	4GB	8GB	16GB	32GB	32GB w/Encryption
A chrome	STU2GPAS	STU4GPAS	STU8PAS	STU16PAS	-	-
C chrome	STU2GPCS	STU4GPCS	STU8GPCS	STU16GPCS	-	-
C gold	-	STU4GPCG	STU8GPCG	STU16GPCG	STU32GPCG	STU32GPCGE
C nickel	STU2GPCN	STU4GPCN	STU8GPCN	STU16GPCN	STU32GPCN	-
C 3-in-1	-	STU12GC3	STU24GC3	-	-	-
D chrome	STU2GPDS	STU4GPDS	STU8GPDS	STU16GPDS	-	-
E chrome	STU2GPES	STU4GPES	STU8GPES	STU16GPES	-	-
E gold	-	STU4GPEG	STU8GPEG	STU16GPEG	STU32GPEG	STU32GPEGE



Truly Water Resistant!



Mighty Small, Yet Impressively Big!