



Mobile Performance Meets Style and Versatility

The Vivitek D530 and D535 digital projectors are distinctive in design, lightweight and packed with user-friendly features. Connectivity options for the D530/D535 including HDMI v1.3 and both projectors are 3D-ready, make them ready for the latest multimedia applications. With a high brightness level of 3200 lumens and a weight of only 4.2 lbs, the Vivitek D530 and D535 are the portable solutions to deliver sharp, vibrant pictures and presentations.

Features

- 3200 lumens of brightness with a 3000:1 contrast
- Native SVGA/XGA Resolution and displays up to UXGA
- 3D-ready via DLP® Link™
- DLP and BrilliantColor™ technologies by Texas Instruments
- High-efficiency lamps that last up to 4000 hours (in economy mode)
- Keypad lock feature to avoid accidental change to the setting
- Closed caption and rapid on/off feature
- Enhanced color and display adjustments

Specifications	
Brightness	3200 Lumens
Native Resolution	D530: SVGA (800 x 600), D535: XGA (1024 x 768)
Max. Resolution	UXGA (1600 x 1200)
Contrast Ratio	3000:1 (Full On/Off)
Lamp Life and Type	≈3000/4000 Hours (Standard/Economy Mode), 240W
Lamp Part #	5811116310-S
Display Type	Single 0.55" DLP® Technology by Texas Instruments
Throw Ratio (±3%)	1.92 to 2.14:1 (Distance/Width)
Image Size (Diagonal)	40" to 300" (1.0 to 7.6 m)
Projection Distance	5.1' to 42.8' (1.6 to 13.0 m)
Projection Lens	F = 2.52-2.73, f = 24.34-25.95 mm
Zoom Ratio	1.1:1 Manual Zoom/Focus
Aspect Ratio	4:3 Native, 16:9 Compatible
Offset	128%
Keystone Correction	±30° Vertical
Color Spectrum	1.07 Billion
Horizontal Scan Rate	15, 30 to 90 KHz
Vertical Scan Rate	43 to 85 Hz
Speaker	2 Watt Mono
Remote Control	Card Type IR Remote
Projection Method	Table Top or Ceiling Mount (Front or Rear)
Uniformity	85%
Computer Compatibility	UXGA, WXGA, SXGA+, SXGA, XGA, SVGA, VGA Resized; VESA Standards; PC and Macintosh Compatible
Video Compatibility	SDTV(480i, 576i), EDTV (480p), HDTV (720p, 1080i), NTSC/NTSC 4.43, PAL B/G/H/I/M/N 60, SECAM
I/O Connection Ports	HDMI v1.3, VGA-In, Composite Video, S-Video, RCA Stereo-In, Mini-Jack Audio-In, RS-232c
Security	Kensington® Lock Port
Weight	4.2 lbs (1.9 Kg)
Dimensions (W x H x D)	10.3" x 3.1" x 7.5" (261 x 76.2 x 190 mm)
Noise Level	35dB/29dB (Standard/Economy Mode)
Power	Supply: AC 100-240V Consumption: 230W (Economy Mode), 300W (Standard Mode), <1W (Standby Mode)
Operating Temperature	41 to 104°F (5 to 40°C)
Warranty	1-Year Limited Parts/Labor, 90-Day Lamp
Standard Accessories	AC Power Cord, VGA Cable, Remote Control, Batteries for Remote, Carrying Case, User's Manual(CD), Lens Cap, Warranty Card
UPC	8 14964 33466 4/8 14964 33467 1 (D530/D535)

