

VA705b

17" ECO FRIENDLY LCD

WITH ONLY 21W OF POWER USAGE

Reliable, eco-friendly performer.

Using only 21W of power, the ViewSonic® 17" VA705b LCD delivers impressive front-of-screen performance thanks to fast 5MS VIDEO RESPONSE, 280 nits of brightness (typ) and a 1000:1 contrast ratio (typ). The VA705b delivers crystal-clear graphics and SMOOTH, FULL-MOTION VIDEO IN BRILLIANT COLOR. The OSD power lock secures your screen settings and the Kensington® security port provides theft deterrence. The stylish, slim bezel makes the VA705b an easy fit with any desktop décor while saving valuable desktop real estate. Home users, small office, education and government users will find that the elegant, affordable and energy saving VA705b is an ideal fit.



HIGH STYLE HIGH PERFORMANCE

- > **Low energy consumption**
Uses only 21w of power for a greener solution.
- > **Full 17" viewable screen**
Displays a full, flat 17" viewable area with crisp detail and fully saturated color.
- > **1280x1024 native resolution**
Incredible image detail for sharp text and graphics.
- > **Fast 5ms video response delivers superior picture clarity**
- > **Stylish slim-bezel design**
An ultra-thin bezel lets you see more without taking up valuable desktop real estate.
- > **OSD/power lock secures your settings**
Prevents changes to monitor settings and maintains an optimized image.
- > **OnView® controls for superior screen adjustability**
Screen adjustments are precisely made via an easy-to-use on-screen menu.
- > **Windows Vista approved**
- > **ViewSonic Wizard included**
User-friendly Wizard software automates the setup process to deliver optimized screen performance.
- > **PC and Mac® compatible**
- > **TCO'03 and ENERGY STAR® qualified**



VIEWSONIC
PRODUCTS, PROGRAMS,
AND SERVICES

ViewSonic®
See the difference® 

VA705b

17" VALUE SERIES LCD WITH 5MS VIDEO RESPONSE



ViewSonic Corporation's QMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by the British Standards Institution.

LCD	Type	17" color TFT active matrix SXGA LCD
	Display Area	13.3" horizontal x 10.6" vertical; 17.0" diagonal
	Optimum Resolution	1280x1024
	Contrast Ratio	1000:1 (typ)
	Viewing Angles	160° horizontal, 160° vertical @ contrast ratio > 5:1
	Response Time	5ms (typ)
	Light Source	Long life, 50,000 hrs. (typ)
	Brightness	250 cd/m2 (typ)
VIDEO INPUT	Panel Surface	Anti-glare
	Analog	RGB analog (75 ohms, 0.7 Vp-p)
	Frequency	F _H : 24~82kHz, F _V : 50~75Hz
COMPATIBILITY	Sync	H/V separated (TTL)
	PC	VGA up to 1280x1024 non-interlaced
	Mac®*	Power Mac™ G3/G4/G5 up to 1280x1024
CONNECTOR	Analog	15-pin mini D-sub
	Power	3-pin AC plug (CEE22)
POWER	Voltage	AC 100~240V (universal), 50/60Hz (auto switch)
	Consumption	21W (typ)
CONTROLS	Basic	Power, 1, down, up, 2
	OnView®	Auto image adjust, contrast, brightness, ViewMatch® color adjust (sRGB, 9300K, 6500K – default, 5400K, RGB), information (resolution, H-freq, V-freq, pixel clock, model number, serial number, web site), manual image adjust (H. size, H. position, V. position, fine tune, sharpness), setup menu (language, resolution notice, OSD position, OSD timeout, OSD background), memory recall
OPERATING CONDITIONS	Temperature	32~104°F (0~40°C)
	Humidity	10~90% (non-condensing)
DIMENSIONS (W x H x D)	Physical with stand	15" x 15.8" x 8.3" (379mm x 400mm x 210mm)
	Physical without stand	15" x 13.3" x 2.7" (379mm x 337.4mm x 68mm)
	Packaging	17.3" x 19" x 5.8" (440mm x 480mm 147mm)
WEIGHT	Net with stand	8.9 lb. (4 kg)
	Net without stand	8.3 lb. (3.8 kg)
	Gross	11.2 lb. (5.1 kg)
REGULATIONS	UL, cUL, FCC-B, CB, CE, NOM, TUV/GS, TUV/ERGO (covers ISO13406-2), TCO'03, BSMI, CCC, ENERGY STAR®, PSB, C-TICK, RoHS, WEEE	
RECYCLE/DISPOSAL	The lamp in this product contains mercury. Please dispose of in accordance with local, state and federal laws.	
POWER MANAGEMENT	Meets TCO'03 and ENERGY STAR® standards	
PACKAGE CONTENTS	LCD display, video cable, power cable, Quick Start Guide, ViewSonic Wizard	
WARRANTY	Three-year limited warranty on parts, labor and backlight.	

ViewSonic®
See the difference®

Sales: (888) 881-8781 • SalesInfo@ViewSonic.com • ViewSonic.com

*Adapter may be required. Analog adapter available from ViewSonic. Specifications subject to change without notice. Selection, offers and programs may vary by country; see your ViewSonic representative for complete details. Windows Vista and the Windows logo are trademarks or registered trademarks of Microsoft Corporation in the United States and/or other countries. Corporate names, trademarks stated herein are the property of their respective companies. Copyright © 2008 ViewSonic Corporation. All rights reserved. [14722-00B-12/09] VA705b-1

For more product information, visit us on the web at ViewSonic.com