

BulletScan™

F200

The Faster, More Accurate Scanner



The Faster, More Accurate Desktop Color Scanner

The BulletScan F200 flatbed scanner with an integrated automatic document feeder (ADF) is the perfect solution for the small to medium-sized business office or for departmental use within a larger corporation. In today's digital world, businesses are finding the need to scan and send documents to email, intranet and web as well as becoming digitally compliant with state and federal regulations. The BulletScan F200 scans up to 20 pages per minute (20 ppm) and is the fastest scanner in its category. Moreover, the BulletScan F200 is bundled with BulletScan Manager software and powered by ABBYY FineReader Technology for unmatched accuracy.

Document Capture Made Simple

The BulletScan Manager Software provides everything needed to control the scanning process, file formats, and scan-to-destinations. BulletScan Manager offers both easy and advanced scan mode settings. Features such as autostraighten, auto-crop, auto-rotate, and edge clean-up are included as the default settings in easy mode and can be fine-tuned in advanced mode. The BulletScan F200 includes 9 Scan-to Destinations with one-click configuration for scan to-email, to-print, to-PDF and Searchable PDF, among others.

Powered by ABBYY FineReader® Technology

The BulletScan F200 is powered by ABBYY FineReader Technology, the same technology used for ABBYY FineReader Desktop OCR, voted 4-stars by PC Magazine, 2009. The ABBYY FineReader Technology reduces the size of the resulting PDF without loss of visual quality, retains text-under-image, text-over-image, text and pictures or image-only PDFs. The FineReader Technology also recognizes multilingual documents and can automatically detect English, French, Italian, German and Spanish language documents.

Reliability

The BulletScan F200 is backed by a 2-year manufacturer's warranty upon product registration. It is also Windows 7 compliant, certified Hi-Speed USB 2.0 interface, and includes TWAIN and WIA drivers. The BulletScan F200 is supported by iVina's U.S.-based technical support and customer service teams.

- Scan Business Cards, Receipts, Photos and Documents up to Legal Size
- 9 Scan-to-Destinations including Scan-to-Email, to-PDF or Searchable PDF, to-Print
- Powered by ABBYY FineReader® Technology for Unmatched Accuracy
- Scans Up to 20 Pages Per Minute*
- 50 Page Built-in Automatic Document Feeder
- 2 Year Warranty



www.bulletscan.com

BulletScan™

F200

The Faster, More Accurate Scanner



**20 Pages Per Minute in Black & White
9 Scan-to Destinations**

BulletScan Software

BulletScan Manager

- Leading-Edge, High Performance Scan Technology
- 9 Scan-to Destinations
- One-Click configuration for Scan-to-Email, to-Print, to-PDF and Searchable PDF

Easy & Advanced Mode Scan Settings

- Auto-Straighten
- Auto-Crop
- Auto-Rotate
- Edge Clean-up
- Color Dropout

Powered by ABBYY FineReader® Technology for Unmatched Optical Character Recognition Accuracy (included).

- Reduces the size of the resulting PDF without loss of visual quality
- Retains Text-under-image, Text-over-image, Text and Pictures or Image only PDFs
- Multilingual Document Recognition
- Automatic Language Detection for English, French, Italian, German and Spanish OCR Languages

BulletScan F200 Product Specifications

Throughput Speed: (at A4 size)	20 PPM @ 200 dpi in Black & White, Simplex 20 PPM @ 200 dpi in Color, Simplex 10 PPM @ 300 dpi in Black & White, Simplex 10 PPM @ 300 dpi in Color, Simplex
Scanning Technology	Charged Coupled Device (CCD)
Scanning Mode	48-Bit Color, 16-Bit Grayscale, and Black & White
BulletScan One-Click Scanning	9 Destinations
Optical Resolution	600 dpi
Scanning Output	24-Bit Color, 8-Bit Grayscale, Halftone, Dynamic Black & White, Fixed Threshold Black & White
Output Resolution	75, 100, 150, 200, 300, 400, and 600 dpi
Maximum Document Size	8.5 in. x 14 in. (215 mm x 355 mm)
Minimum Document Size	4.5 in. x 5.5 in. (114 mm x 140 mm)
Paper Thickness and Weight	16 – 28 lb. Paper
Connectivity	Hi-Speed USB 2.0
Image Acquisition Driver	TWAIN and WIA Drivers
File Compression	TIFF – G4, JPEG
File Format Outputs	PDF, Multi-page TIFF and JPEG, BMP, Doc.
Warranty	Two Years
Daily Duty Cycle	2,500 pages
Electrical Requirements	Input: 100-240 VAC, 50-60 Hz, Output: 24V, 1.0A
Power Consumption	<12W
Recommended Default Delay Times for Power Management Settings:	15 min

Minimum System Requirements:

- Pentium® 4 or equivalent processor
- Windows® 7/XP (SP2)/ Vista
- Minimum of 512MB of RAM (1GB for Vista)
- 350MB of available HD space
- CD/DVD-ROM drive
- USB Port

Contents of Box:

- Scanner
- USB Cable
- Power Supply
- Quick Install Guide
- CD ROM including:
 - BulletScan Manager
 - ABBYY FineReader® Technology
 - User's Manual

* Based upon scanning a 8.5" x 11" document at 200 dpi, black and white.

CONTACT INFORMATION:

Karen Corbett

TEL: (925) 336-0570

FAX: (925) 426-0840

EMAIL: karen@bulletscan.com