

## NetDirector 32-Port Cat5 IP KVM Switch 1U Rack-Mount 2+1 User

MODEL NUMBER: B064-032-02-IPG









## **Specifications**

OVERVIEW		
Users	3	
Max CPU	32	
INPUT		
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC; 200V AC; 208V AC; 220V AC; 230V AC; 240V AC	
Input Frequency	50/60Hz	
Input Current	120V (0.8A) / 230V (0.4A)	
PHYSICAL		
Unit Dimensions (hwd / in.)	1.75 x 17 x 16	
Unit Dimensions (hwd / cm)	4.45 x 43.18 x 40.64	
Unit Weight (lbs.)	12.1	
Unit Weight (kg)	5.49	
Color	Black	
ENVIRONMENTAL		
Storage Temperature Range	-20 to 60 C (-4 to 140 F)	
Relative Humidity	0 to 80% RH, Non-Condensing	
Operating Temperature	0 to 40 C (32 to 104 F)	





COMMUNICATIONS		
Port Control	Push Buttons, Hotkeys, OSD	
IP Remote Access	Yes	
CONNECTIONS		
Ports	32	
Computer/Server Ports	(x32) RJ45 Female	
PC/Server Connections	DVI; Serial; USB; VGA	
Local Console Ports - Port 3	(x2) PS/2 Female (via B015-000, sold separately))	
SPECIAL FEATURES		
Cat5 KVM Switch	Yes	
FEATURES & SPECIFICATIONS		
Autoscan (Y,N)	Y	
Autoscan Duration	User-definable from 1 to 255 seconds; default of 5 seconds	
CERTIFICATIONS		
Approvals	UL/cUL, FCC, CE, TAA, RoHS	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: http://www.tripplite.com/products/product-certification-agencies