

Antec
Believe it.

SONATA PROTO

SONATA SERIES



ENCLOSURES

Elegantly Silent

The affordable Quiet Computing™ case is here. Introducing the Sonata Proto: get all the features and performance of the renowned Sonata line of enclosures without breaking the bank. With 10 drive bays, 7 expansion slots and an intake air filter, the Sonata Proto offers a wealth of features and keeps the quiet performance that the Sonata line is famous for. Along with its convenient front mounted USB 2.0 and HD audio connectors, the Sonata Proto is the ideal combination of silence, efficiency and affordability.



UCC13# 0761345-15145-0 NA
UCC13# 0761345-08134-4 EU
UCC13# 0761345-10020-5 AP

SPECIFICATIONS:

- 10 drive bays:
 - External 3 x 5.25"
 - External 2 x 3.5"
 - Internal 4 x 3.5"
 - Internal 1 X 2.5"
- 7 expansion slots
- Advanced cooling system:
 - 1 rear 120 mm TwoCool™ two-speed switch control exhaust fan
 - 1 middle (optional) 120 mm fan
- Built-in washable air filter
- Front mounted I/O ports:
 - 2 x USB 2.0
 - Audio In and Out (AC'97 and HDA compatible)
- 0.8 mm cold rolled steel for durability
- Power supply not included
- Compatible motherboards: Mini-ITX, microATX, Standard ATX
- Weight: 16.9 lb / 7.7 kg
- Unit dimensions:
 - 18.7" (H) x 8.6" (W) x 16.8" (D)
 - 475 mm (H) x 218 mm (W) x 426 mm (D)

www.antec.com • 1-800-22ANTEC (US) / +31 (0) 10 462-2060 (EU)

