

GOOD VALUE, DEPENDABLE BUSINESS PRINTING

Epson AcuLaser CX16 Series



- Print, copy and scan
- Fast print speeds in colour and monochrome
- Duty cycle of up to 35,000 pages per month
- First page out 14 seconds in mono, 23 seconds in colour
- Professional quality colour with up to 1200x600 dpi resolution and Epson AcuBrite toner
- Hi-Speed USB 2.0 connection
- 200-sheet multi-purpose tray with dust cover
- ENERGY STAR® qualified, power-efficient solution
- Low running costs with high-capacity toner cartridges

Boost your business with a compact, affordable multifunction colour laser printer, scanner and copier. Add professional quality to all your business materials and keep running costs low.

Professional colour solution

The Epson AcuLaser CX16 Series easily handles all your colour and mono documents, from printing letters and presentations to scanning documents or making quick copies. It saves time too, with fast print speeds and a mono first page out time of just 14 seconds.

Compact and easy to manage

These multifunction lasers have a small footprint that fits discreetly into any business environment. Featuring high-speed USB 2.0 connectivity and a clear control panel, you'll find them simple to set up and use, making day-to-day print management straightforward. The 200-sheet multi-purpose media tray is easy to refill and makes changing paper fast and convenient. It even has a built-in dust cover to keep your paper pristine.

Economical and dependable

Enjoy excellent reliability with an impressive 35,000 pages per month duty cycle. High-capacity toner cartridges print more pages between changes and help reduce running costs. Further savings result from the Epson AcuLaser CX16 Series' ENERGY STAR® qualified power efficiency, which means it uses less power both in standby mode and when printing, helping you to reduce bills and environmental impact.


The Epson AcuLaser CX16NF has the addition of a fax unit, Ethernet connectivity, automatic document feeder, USB host for direct printing plus optional duplex and 500-sheet paper cassette.



PRODUCT SPECIFICATIONS

	Epson AcuLaser CX16	Epson AcuLaser CX16NF
PRINT FEATURES Printing technology Print resolution Print speed First page out time Warm-up time Maximum monthly volume	Colour laser Up to 1200x600 dpi Up to 19 ppm mono and 5 ppm colour Up to 20 ppm mono and 5 ppm colour Less than 14 seconds mono and 23 seconds colour Less than 35 seconds Up to 35,000 pages	
COPY FEATURES Copy speed Copy resolution First copy out time Multiple copies Zoom	Up to 19 ppm mono and 5 ppm colour Up to 20 ppm mono and 5 ppm colour Up to 600x600 dpi Less than 23 sec mono and 32 sec colour 1 – 99 sheets 50 – 200 %	
SCAN FEATURES Scan technology Scan speed Scan resolution Colour depth Compatibility Scan area Scan-to functions	A4 Flatbed colour scan Up to 59.62 mm/sec	A4 Flatbed and ADF colour scan Up to 59.62 mm/sec or 20 ppm with the ADF Up to 600x600 dpi 24 bits Twain, WIA Up to 216x297 mm Scan to E-mail, FTP, SMB (folder), USB memory
FAK FEATURES Fax speed Receive memory Compatibility Speed dialing numbers Group dial Fax functions	33.6 Kbps Up to 384 pages ECM / Super G3 Up to 220 dials Up to 20 groups Speed dial, Favorite, PC Fax (Windows only), Fax to E-mail, Fax to Fax, Memory Reception, Timer	
CONTROLLER Memory (standard/max) Processor Printer language	64MB	128MB 120MHz Host based
INTERFACES Standard interfaces Network printing protocols Panel	High Speed USB 2.0	Ethernet (10/100 Base-TX), High Speed USB 2.0, USB Host, RJ-11 (Fax) IPP 1.1, TCP/IP, LPD, FTP (client/server), DHCP, HTTP, SNMP, SMTP, POP3, BootP, Port9100RAW, SLP, ARP, LDAP, LDAP, DNS, Bonjour, AutoIP, Ping, IPv4 LCD (20 characters x 4 lines)
MEDIA HANDLING Standard paper input Additional paper input ADF Duplex Paper size Paper weight Paper output	200-sheet multi-purpose tray with standard dust cover 500-sheet paper cassette – Max: 1 35 sheets ADF Optional Manual A4, A5, B5 (ISO, JIS), LGL, LT, GLT, GLG, HLT, F4, Envelope (C6, DL), Postcard, EXE, Oficio, Custom size (Plain paper: Width: 92-216 mm, Length: 195-356 mm) 60 – 209 g/m ² 100 sheets (face down)	
POWER REQUIREMENTS Voltage/frequency/current Power consumption	220-240V ±10% / 50-60Hz ±3% / 4.4A Max: 1060W / Average: 560W / Ready: 170W / Sleep: 14W / Power Off: 1W Max: 1060W / Average: 560W / Ready: 170W / Sleep: 14W / Power Off: 1W	
OS SUPPORT Windows support Mac support	Windows 2000 / XP (32/64bit) / Vista (32/64bit) / Seven (32/64bit) / Server 2003 (32/64bit) / Server 2008 (32/64bit) Mac OS X 10.3.9 or earlier	
ADDITIONAL SOFTWARE	Local setup program, EpsonNet Config	
DIMENSIONS AND WEIGHT Dimension (WxDxH) Weight (without consumables)	CX16: 405x427x375 mm – 16.0 Kg	CX16NF: 405x427x432 mm – 17.6 Kg CX16DNF: 405x452x493 mm – 21.8 Kg CX16DTNF: 405x585x548 mm – 24.7 Kg
ENVIRONMENTAL CONDITIONS Temperature Humidity Sound power Sound pressure	Operation mode: 10–35°C / Storage: 0–35°C Operation mode: 15–85%RH / Storage: 30–85%RH Operation: 6.37B(A), Ready: 4.88B(A) Operation: 50.0dB(A), Ready: 38.0dB(A) Operation: 6.30B(A), Ready: 4.88B(A) Operation: 52.0dB(A), Ready: 38.0dB(A)	
REGULATIONS Materials Chemical regulations Environmental measures	Not containing any materials prohibited by country regulations Hazardous materials not exceeding permitted value Compliant with OSHA, TSCA, and EINECS ENERGY STAR®, RoHS compliant	
WARRANTY ³ Standard Optional	1 year on-site warranty 3 years on-site extended warranty: ECPGRP35 3 years on-site extended warranty: ECPGRP40	

Epson AcuLaser CX16 Series



PRODUCT MODELS

Epson AcuLaser CX16	C11CB05001
Epson AcuLaser CX16NF	C11CB05011
Epson AcuLaser CX16DNF	C11CB05011DZ
Epson AcuLaser CX16DTNF	C11CB05011DT

SUPPLIES

High-Capacity Toner Cartridges:	
Black – 2,700 pages*	C13S050557
Cyan – 2,700 pages*	C13S050556
Magenta – 2,700 pages*	C13S050555
Yellow – 2,700 pages*	C13S050554

Standard Capacity Toner Cartridges:	
Cyan – 1,600 pages*	C13S050560
Magenta – 1,600 pages*	C13S050559
Yellow – 1,600 pages*	C13S050558

Photoconductor unit: 45,000 pages for mono / 11,250 pages for colour	C13S051198
--	------------

Initial Capacity Toner Cartridge (CMY)
500 pages*, (Black) 1,000 pages*

* (ISO/IEC 19798 yield test report)

MEDIA

A4 Colour Laser Paper (82 g/m ²)	C13S041215
--	------------

OPTIONS (ONLY FOR THE ACULASER CX16NF)

500-sheet paper cassette	C12C802631
Duplex unit with attachment	C12C802621

TONER CARTRIDGE COLLECTION⁴

This free service helps us to collect and recycle used Epson toner cartridges in a safe and environmentally friendly way. There are three easy ways to dispose of your empty cartridges and take an active role in reducing waste:

- Put them in a Toner Cartridge Collection box which will be picked up once full
- Return them free of charge by post
- Drop them off at an Epson Express Centre

BETTER PRODUCTS FOR A BETTER FUTURE

At Epson, we know that planning for the future requires a strong commitment to the environment. That is why we strive to create innovative products that are reliable, recyclable, and energy efficient. Better products that use fewer resources help ensure a better future for us all.



Better Products for a Better Future

¹ For more information please visit www.epson-europe.com

² Full resolution 1200x600 dpi

³ Warranty offers are not available for all countries. Please contact your local Epson representative

⁴ Please visit www.epson.com/recycle for more details about products and availability

For further information please contact your local Epson office or visit www.epson-europe.com

Austria 0810/20 01 13 (0,07 €/Min.) Belgium 070/350120 (0.1735 €/min.) Czech 800/142 052 Denmark 44 50 85 85 Finland 0201 552 091 France 09 74 75 04 04 (Cost of local call, operator charges may apply) Germany 01805/23 41 10 (0,14 €/Min. aus dem dt. Festnetz, Mobilfunkpreise abweichend. Ab 1.3.2010 Mobilfunkpreis max. 0,42 €/Min.) Greece 210-8099499 Hungary 06800 147 83 Ireland 01 436 7742 Italy 02-660321 10 (0,12 €/min.) Luxembourg 900/43010 (0,24 €/min.) Middle East +9714 8818934 Netherlands 0900-5050808 (0,05 €/oproep + 0.15 €/min.) Norway +47 67 11 37 00 Poland 0-0-800 4911299 (0,16 z/min.) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429 South Africa (+2711) 465-9621 Spain 93 582 15 00 Sweden 0771-400135 (Mobilsamtal – 0,99 kr/min, Lokala samtal – 0,30 kr/min, Utlandssamtal – 0,89 kr/min) Switzerland 0848 448820 (4-8 cent./min.) Turkey (0212) 3360303 United Kingdom 0871 222 6702

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

