


LEXMARKTM

Up to 4800 x 1200 dpi Photo Quality Resolution

High Performance Made Easy

- Print Fast! Up to 19 ppm
- PC-Free, 1-Touch Black, Color and Photo Copies
- 48 bit Flatbed Color Scan, 600 x 2400 dpi
- Easy Scan to PC Fax



X5150 3 High-Performance
Machines in 1

KEY FEATURES



COLOR PRINTING

- Up to 4800 x 1200 dpi photo quality images
- Print Fast! Up to 19 ppm black and 14 ppm color

COLOR SCANNING

- Up to 600 x 2400 dpi resolution
(up to 19,200 dpi enhanced)
- Flatbed scanner easily handles books, reports and more
- 48 bit color
- 16 bit grayscale

COLOR COPYING

- PC-free copies up to 16 ppm black and 11 ppm color
- Reduction/enlargement capability from 25% to 400%
- 1-99 copies at one time
- One-touch photo

EASY TO USE FEATURES

- Integrated photo editing software enables users to perform multiple photo editing tasks easily with a PC
- Reprint your favorite 35mm photos quickly and easily using the one-touch photo copy feature
- Automatic cartridge alignment ensures the best print output without manual adjustment
- PrecisionSense™ – media sensing technology automatically determines paper type and adjusts the printer driver to optimize output
- Accu-Feed™ paper handling system virtually eliminates paper jams

FAXING

- PC fax capability

PRODUCT SPECIFICATIONS

COMPATIBILITY

- Windows 98, Me, 2000, XP
- Mac OS 9.2.2, OS 10.1.5

INPUT TRAY

- 100-sheet for paper
- 25-sheet for transparencies; 12-sheet for envelopes
- Output – 50 sheets

DUTY CYCLE

- Up to 3,000 pages/month

PAPER TYPES

- Plain, inkjet and photo paper; transparencies, labels, envelopes, index cards, greeting cards and iron-on transfers

PAPER SIZES

- Letter, legal, A4, A5, A6, B5, Exec, Index (3" x 5"), Postcard (4" x 6"), Hagaki, banner, and multiple envelope sizes

BOX CONTENTS

- Lexmark™ X5150 All-In-One Print Center
- High resolution color cartridge (83)
- High resolution black cartridge (82)
- User's Guide and Setup Sheet with printer driver (CD-ROM)

PRODUCT SIZES

- 9.4" w x 18.5" d x 15.5" h (tray retracted)
- 13.2" w x 18.5" d x 21.5" h (tray extended)

LOW NOISE

- Smooth printing – 51 dB(A)

CONNECTIVITY

- USB

COMPLIANCE

- Energy Star

WARRANTY

- LexExpress™ one year limited exchange

Compatibility	
Color Cartridge	Black Cartridge
83	82



www.lexmark.com

Lexmark, Lexmark with the diamond design, Accu-Feed and PrecisionSense are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. LexExpress is a service mark of Lexmark International, Inc. All other trademarks are the property of their respective holders. Information in this document is subject to change without notice.

©2003 Lexmark International, Inc. 740 West New Circle Road, Lexington, KY 40550. Printed in the USA 2/03.

X5150001

X5150 3 High-Performance
Machines in 1

LEXMARK