

Intercom Door Unit, Weather Resistant, Oil Rubbed Bronze

F7596-OB



This Intercom Door Unit is sure to increase the curb appeal of any home. It home runs from the enclosure for efficient installation and features a backlit button for easy operation at night. The door unit is the perfect addition to any intercom system.

features & benefits

- **Back lit button allows for easy operation at night.**
- **Easy installation with 110 punchdown connection.**
- **Available in five colors:** White, Antique Brass, Brushed Stainless, Oil-Rubbed Bronze and Shiny Brass.

specifications

General Info

Cable Type: Cat 5
Color: Oil Rubbed Bronze
Connection Type: 110 IDC Punchdown
Product Series: inQuire 1000
Type: Door Unit
Housing Material: Zinc Alloy

Assembly/Installation Information

Mounting Hardware Included: Yes

Listing Agencies/Third Party Information

FCC Standard: Yes
UN SPS C: 43221525

Construction Information

Installation Location: Outdoor

Dimensions

Depth Metric: 3.8 cm

Depth U S: 1.5"

Height Metric: 12.1 cm

Height U S: 4.75"

Width Metric: 12.1 cm

Width U S: 4.75 in

Cord Information

Cord Length U S: 325 Foot home-run

Pinning:

1. Blue/White Audio In (Speaker)
2. Blue Ground
3. Power
- Orange/White
4. Orange Audio Out (Microphone)
5. Green/White Relay (changing from Mic to Speaker)
6. Green Not Used
7. Brown/White Not Used
8. Brown Door Chime Activation (when doorbell button is pressed)

Technical Information

Frequency Response: up to 16kHz

Humidity: 90% Relative Humidity (Non-Condensing)

Mounting: Wall

Operating Temperature Celsius: -25°C to 55°C

Operating Temperature Fahrenheit: -13°F to 131°F

Power Peak: 2 W

Power RM S: 3 W

Product Fits Into: Double Gang Electrical Box

Speaker Depth Metric: 28 mm

Speaker Depth U S: 1.1 in

Speaker Impedance Load: 8 ohms

Supported Standards: FCC PART 15 B