

Selective Call Intercom Door Unit, Oil Rubbed Bronze

IC5002-OB



Housed in an attractive weatherproof finish, the selective call door unit supports 20 high-quality digital door tones as well as door and gate release.

features & benefits

- **Stylish, weatherproof design increases the curb appeal of any home.**
- **Installs in a standard double gang opening with simple RJ45 plug design for easy installation and troubleshooting.**
- **Supports 20 digital door tones.**
- **Integrates with gate/door release.**

specifications

General Info

Color: Oil Rubbed Bronze

Dimensions

Overall Dimensions U S: 5.1" H x 4.5" W x 1.1" D

Weight: 1.5 lb

Cord Information

Pinning:

Pin 1 24 VDC Out

Pin 2 GND

Pin 3 Audio (+)

Pin 4 COMMA

Pin 5 COMMB

Pin 6 Audio (-)
Pin 7 NOT USED
Pin 8 NOT USED

Technical Information

Cat5 Cable Rating: CAT5 UTP, 4 pair solid conductor (24 AWG)

Humidity: Up to 90% RH (non-condensing)

Material: Cast; Zinc Alloy

Operating Temperature Celsius: -25 to 55 degrees

Operating Temperature Fahrenheit: -13 to 131 degrees

Power Requirements: +24Vdc, +/-1.5Vdc, 0.20A max

Q Link Selective Call Ports: RJ-45

Storage Temperature: -45 to 85°C (-49 to 185°F)