



"One-touch printing with do-it-all versatility?"  
**Right here.**

With one-touch print screen convenience and one-touch eco print, this Samsung printer offers everything you need in a single machine.



This Samsung printer is all about one-touch convenience and multi-tasking versatility. Thanks to a handy print screen feature, you can print whatever is on your screen with just a quick press of a button. The one-touch eco print button saves paper while the default toner mode makes saving toner effortless. Since you can print, copy and scan, this laser printer is a multi-tasker you can't do without.



**From the screen to the page with just One Touch**

The SCX-3205's Print Screen button – conveniently located on the printer control panel – lets you print the contents from your screen, quickly and easily. With one touch, there's no more extra editing or cropping of unwanted content-clutter from original webpages or documents. One simple press of a button prints your screen. Hold the button for more than two seconds and the SCX-3205 prints the activated window on your screen. Now you can print anything, anytime.



**Save time and earth with convenient one-touch eco print**

Our easy one-touch eco print button lets you combine two pages into one document with less toner consumption, saving you valuable time. Conveniently located on the front panel, a single step is all it takes. And once you choose eco print, it becomes your default setting. Saving paper, toner and ultimately earth is an added bonus you'll appreciate.



**Big features, small size**

Looking for bigger performance from a desktop printer? Think smaller. Measuring a ultra compact 388 x 299 x 234mm (15.3" x 11.8" x 9.2"), the Samsung SCX-3205 has a smaller size than any other laser multifunctional printer on the market. It easily fits onto any size of desktop while leaving plenty of room for you to get your work done. But don't let the SCX-3205's ultra-compact size fool you: this is one featherweight who's ready to take on the heavyweight contenders any day.



### It multi-tasks so you don't have to.

Productivity is a key to running any office or professional workgroup. The ultra-versatile, fast-printing SCX-3205 is designed to deliver productivity. Now you can print, copy and scan with convenience, ease and speed. Why clutter a corner of your office with several different machines when all you need is one versatile device – the 3-in-1 SCX-3205 laser multifunction printer.

### One less noisy office distraction



You shouldn't have to struggle to hear yourself think while sitting at your own desk. That's why the Samsung SCX-3205 is engineered to be whisper quiet, generating a noise level of just 49dBA while it's printing. That's less than the gentle hum of a running refrigerator! A desktop printer that does its work while letting you focus on yours? Cool.

### Capture what catches your eye



Samsung's AnyWeb Print software lets you go hunting and gathering on the Web. You can utilize the SCX-3205 to easily select, drag, and drop content from different web pages onto a printable scrap board in your browser window, all while you surf the web. Items can be printed quickly or saved in different file formats. It's an easy way to collect, arrange, and edit useful reference points and resources you can only find on the web for big projects – or even just for fun.

### Lessen your wait, not your expectations



Quit losing productivity waiting around for your documents to print? The Samsung SCX-3205's fast print speed (16ppm for A4 paper, 17ppm for letter-sized) will have you back to work in no time. In Ready Mode, the SCX-3205 features a First Page Output Time (FPOT) of just 8.5 seconds and an impressive 1200 x 1200dpi print resolution, satisfying both your need for speed and your demand for quality.



### Soft power button

The easy-to-reach power button is located right on the front panel, so you can switch on and off easily, avoiding unnecessary energy consumption. Ready to print? Push the button again to power back up, and you're ready to go.

<b>Overview</b>	<b>Function</b>	Print, Scan, Copy
<b>Print</b>	<b>First Print Out Time (Mono)</b>	Less than 8.5 seconds (From Ready Mode)
	<b>Resolution</b>	Up to 1200 x 1200dpi effective output
	<b>Duplex</b>	Manual
	<b>Emulation</b>	SPL, PCL5e
	<b>Speed (Mono)</b>	Up to 16ppm in A4 (17ppm in Letter)
<b>Paper Handling</b>	<b>Input Capacity and Types</b>	150-sheet Cassette
	<b>Media Size</b>	A4, A5, Letter, Legal, Executive, Folio, Oficio, ISO B5, JIS B5, Envelope(Monarch, No.9, No.10, DL, C5), Custom
	<b>Media Type</b>	Plain ,Thin, Cotton, Recycled, Archive, Colored, Pre-Printed, Label, Bond, Thick, Envelopes, Cardstock, Transparency
	<b>Output Capacity and Types</b>	50-sheet Face Down
	<b>ADF Capacity</b>	N/A
	<b>ADF Document Size</b>	N/A
	<b>General</b>	<b>Memory / Storage</b>
	<b>OS Compatibility</b>	Windows 2000 / XP / Vista / 7 / 2003 Server / 2008 Server, Mac OS X 10.3 ~ 10.6, Various Linux OS
	<b>Interface</b>	High speed USB 2.0
	<b>Noise Level</b>	Less than 49dBA (Printing / Copy), Less than 26dBA (Standby)
	<b>Dimension (W x D x H)</b>	388 x 299 x 234mm
	<b>Weight</b>	7.4kg
	<b>LCD</b>	2 digit LED
	<b>Duty Cycle, Monthly</b>	Up to 5000 pages
<b>Consumables</b>	<b>Yield</b>	Standard : Average Cartridge Yield 1500 standard pages, (Ships with 700 pages Starter Toner Cartridge), Declared cartridge yield in accordance with ISO/IEC 19752
	<b>Type</b>	1-piece Cartridge
	<b>Model Code</b>	MLT-D1042S
<b>Copy</b>	<b>Speed</b>	Up to 16cpm in A4 (17ppm in Letter) Up to 1200 x 1200dpi effective output
	<b>First Copy Out Time (Mono)</b>	Less than 10 seconds (From Ready Mode)
	<b>Zoom Rate</b>	N/A
	<b>Multi Copy</b>	1 ~ 99 pages
	<b>Copy Features</b>	ID Copy
<b>Scan</b>	<b>Compatibility</b>	TWAIN Standard, WIA Standard
	<b>Method</b>	Color CIS

	<b>Resolution (Enhanced)</b>	Up to 4800 x 4800dpi
	<b>Scan to</b>	PC
<b>Fax</b>	<b>Compatibility</b>	N/A
	<b>Modem speed</b>	N/A
		N/A
	<b>Memory</b>	N/A
	<b>Auto Dial</b>	N/A
	<b>Fax Feature</b>	N/A

Features and specifications are subject to change without prior notification.

