



iOne-MP172 Fanless Medical All-in-One PC

CPU SUPPORT	Intel® Core™ 2 Duo U7500 1.06GHz, 10W TDP (Thermal Design Power)
MOTHERBOARD CORE LOGIC	Intel® GME965 chipset + ICH8M, 800MHz FSB & socket BGA479
MEMORY	2 Dual Channel DDR2 SODIMM socket supports up to 4GB
HDD SUPPORT	Serial ATA SATA port with 150 MB/s transfer rate
NETWORKING	2x1GbE ports, Realtek RTL8111B Gigabit Ethernet
AUDIO	Realtek ALC286 Audio Codec, 2 + 2 watts power amplifier
I / O PORTS	6 USB (4 external I/O, 2 ports with on-board pin headers) 1 VGA DB-15, 1 DVI output, Triple audio jack, 1 Serial Port, 2 Keyboard/Mouse Connector, 2 LAN, 1 DC-in power connector
STORAGE	2.5" SATA HDD drive bay with anti-vibration mechanism, bootable Compact Flash slot for CF type I/II storages
EXPANSION SLOTS	One PCI 2.2 slot One 32-bit Mini-PCI socket
BIOS	Award BIOS, ACPI supported
POWER SUPPLY	Uses 100Watt AC Adapter. Input: DV12V~28V. AC 90 ~ 264V / 47 ~ 63 Hz
DIMENSIONS	420mm x 360mm x 80mm (W x H x D) approximate w/out stand
WEIGHT	Unit: 22lbs with base, 15.4lbs without base, Power Adapter: 1.9lbs.
OPERATING ENVIRONMENT	Operation Temperature: 0 ~ 40°C, Storage Temperature: -20 ~ 80°C, Operation Relative Humidity: 10% ~ 90% - non condensing, Storage Relative Humidity: 10% ~ 90% - non condensing
ANTI-BACTERIAL COATING	The plastic coating PU-206 contains 0.4% Vanquish-100 (antimicrobial) demonstrated at least 99.6% bacterial reduction after 24 hours of contact
AVAILABLE COLORS	White
WATERPROOF	IP65 at front side / IPX1
CERTIFICATIONS	CE / FCC Class B / EN60601-1 / EN60601-1-2 / UL60601-1 / VCCI / UL/cUL
DISPLAY & TOUCH	17" TFT LCD Panel, 380 nits, 5-wire resistive touch
WALL MOUNT	VESA Mount 75x75 & 100x100 mm

Mounting Options:



100 Series Double Pivot



100 Series Single Pivot



DS100 Dual-Monitor Desk Stand



LX Desk Mounting Arm



LX Wall Mounting Arm



Cybernet Corporate Headquarters

5 Holland, Building 201
Irvine, CA 92618
toll-free: 888-834-4577
tel: 949-600-8000
fax: 949-600-8013

Cybernet Europe

Network House
Hawkins Road, Colchester
Essex, C02 8LA
United Kingdom
UK tel: 0845 5391200
UK fax: 0845 5391201
International tel: 44 1442 863388
International fax: 44 1442 863444

Cybernet Taiwan

Space Technology Company, Ltd.
(A Cybernet Company)
4F, No 49, Lane 76, Rui Guang Rd.
NeiHu District, Taipei, Taiwan, R.O.C.
tel: 866 2 2790 47766
Fax: 866 2 2793 3172