

Enjoy Wireless Freedom with One Touch



An ultra small printer made to fit your specific needs. With its powerful wireless capabilities and One Touch WiFi Setting, you're no longer bound by cords, cables and wires.



Samsung introduces a smaller laser printer with greater convenience, the ML-1865W. With its ultra-compact, elegant design this powerful little printer will go anywhere. Clever, built-in features like One Touch Wi-Fi Setting make the ML-1865W one smart printer. The ML-1865W low noise level, rapid print speed, and easy power button assure maximum convenience. With the Samsung ML-1865W printer, sometimes the best things in life do come in the small packages.

Setup is a cinch with our secure, one-touch wireless connection.



The ML-1865W One Touch Wi-Fi Setting lets you connect quickly and easily. Simply select the WPS (WiFi Protected Set-up) button on the access point (router), press the WPS button on the printer and you're done. Normally, you would have to spend time creating a wireless network name and manually entering a security key or password on all the wireless devices. But the ultra-convenient One Touch Wi-Fi Setting automatically configures — and protects — your wireless network for you.



Big features, small footprint

Looking for bigger performance from a desktop printer? Think smaller. Measuring a ultra compact 341 x 224 x 184mm (13.4 x 8.8 x 7.2in), the Samsung ML-1865W easily fits onto any size desktop while leaving plenty of room for you to get your work done.

Capture what catches your eye



Samsung's AnyWeb Print software lets you go hunting and gathering on the Web. You can utilise the ML-1865W to easily select, drag and drop content from different web pages onto a printable scrap board in your browser window, all while you surf. It's the easy way to collect, arrange and edit those useful reference points and resources you can only find on the Internet for that big project or just for fun.

A printer with brains and beauty



Finally, your desk can look stylish because of your printer, not in spite of it. The Samsung ML-1865W laser printer has an elegant exterior design, sure to fit in with any workspace. Its glossy top cover looks chic and polished while offering dust-free protection. Spiff up your space with a desktop accessory that actually helps you work better.

One less noisy office distraction



You shouldn't have to struggle to hear yourself think while sitting at your own desk. That's why the Samsung ML-1865W is engineered to be whisper quiet, generating a noise level of less than 50 dBA while it's printing. That's less than the gentle hum of a running refrigerator! A desktop printer that does its work while letting you focus on yours? Cool.

Lessen your wait, not your expectations



Quit losing productivity waiting around for your documents to print? The Samsung ML-1865W fast print speed (18ppm for A4 paper, 19ppm for letter-sized) will have you back to work in no time. The ML-1865W features a first page output time (FPOT) of just 8.5 seconds and an impressive 1200 x 600dpi print resolution, satisfying both your need for speed and your demand for quality.

A soft approach to energy efficiency



In today's green office environment, there's simply no room for energy-hogging printers. That's why the Samsung ML-1865W features an easy-to-reach power button right on the front panel, so you can switch to an energy-saving standby mode at the push of a button. Ready to print? Just push the button again to power back up, and you're ready to go.

Overview	Function	Print
	Value Added Function	WPS, Anyweb
Print	Resolution	Up to 1200 x 1200dpi effective output
	First Print Out Time (Mono)	Less than 8.5 seconds (From Ready Mode)
	Emulation	PCL5e, SPL (Samsung Printer Language)
	Duplex	Manual
Paper Handling	Input Capacity and Types	150-sheet Cassette
	Output Capacity and Types	100-sheet Face Down
	Media Size	A4, A5, Letter, Legal, Executive, Folio, Oficio, ISO B5, JIS B5, Envelope (Monarch, No.10, DL, C5), Custom
	Media Type	Plain, Thin, Cotton, Recycled, Archive, Coloured, Pre-Printed, Label, Bond, Thick, Envelopes, Cardstock, Transparency
General	Processor	375MHz
	Memory / Storage	64MB
	OS Compatibility	Windows 2000 / XP / Vista / 7 / 2003 Server / 2008 Server, Mac OS X 10.3 ~ 10.6, Various Linux OS

	Interface	IEEE 802.11b/g/n Wireless Network
	Noise Level	Less than 50dBA (Printing), Less than 25dBA (Standby)
	Duty Cycle, Monthly	Up to 5000 pages
	Dimension (W x D x H)	341 x 224 x 184mm (13.4" x 8.8" x 7.2")
	Weight	4.2kg (9.2lbs)
	Power Consumption	Ready < 45 Watt, Active < 350 Watt, Standby < 3.9 Watt, PowerOff < 0.45 Watt
Consumables	Yield	Standard : Average Cartridge Yield 1500 standard pages (Ships with 700 pages Starter Toner Cartridge) Declared cartridge yield in accordance with ISO / IEC 19752
	Type	1-piece Cartridge
	Model Code	MLT-D1042S

Features and specifications are subject to change without prior notification.