

## 6 ft IEEE-1394 FireWire Cable 9-6 M/M

Product ID: 1394\_96\_6



This 6ft IEEE 1394b FireWire 800 Cable provides one FireWire 9-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 800Mbps, FireWire 800 (IEEE 1394b) technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

This high quality FireWire 800 (9 to 6-pin) cable compatible with all 1394a & 1394b PC FireWire (400/800), Apple FireWire, and Sony iLink devices and is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

### Features

- Fast data transfer rate of up to 800 Mbits/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards
- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

	Warranty	Lifetime
<b>Hardware</b>	Industry Standards	IEEE 1394a, 1394b
<b>Connector(s)</b>	Connector A	1 - FireWire 800 (9 pin, IEEE 1394b) Male
	Connector B	1 - FireWire 400 (6 pin, IEEE 1394a) Male
<b>Physical Characteristics</b>	Cable Length	6 ft [1.8 m]
	Color	Black
	Product Length	6 ft [1.8 m]
	Weight of Product	3.8 oz [106.7 g]
<b>Packaging Information</b>	Package Height	8.3 in [21.1 cm]
	Package Length	7.8 in [19.9 cm]
	Package Width	0.7 in [17 mm]
	Shipping (Package) Weight	3.8 oz [107.7 g]
<b>What's in the Box</b>	Included in Package	1 - 6 ft IEEE-1394 FireWire Cable 9-6 M/M

Product appearance and specifications are subject to change without notice.