

#### Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

## TAA SmartPro 208/120V 5kVA 4kW Line-Interactive Sine Wave UPS, 6U, Extended Run, Network Card Options, USB, DB9

## MODEL NUMBER: SM5000RT3UTAA





### Description

Tripp Lite's line-interactive SM5000RT3UTAA UPS System is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. This UPS protects server, networking or telecommunications equipment from blackouts, voltage fluctuations and surges in a compact tower/rackmount housing. In rack configuration, the power module and battery pack occupy only 3 rack spaces (3U) each. Large capacity 5000VA/4000W power module converts raw 208V AC input to fully regulated dual output 208/120 voltage for simultaneous protection of both high- and low-voltage equipment loads. True sine wave output at all times offers guaranteed compatibility with all equipment types. Includes 14 outlets, 8 of which can be individually reset via software interface to selectively reboot remote equipment or shed less critical loads to extend battery runtime for more critical equipment. Battery support can be extended indefinitely with additional external 3U rackmount battery packs. Network management interfaces support communications via USB, RS-232 and optional slot for network management card options.

#### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Large 5000VA/4000W output capacity with full-time sine wave output offers guaranteed compatibility with all equipment types
- High power density 5kVA power module and battery pack occupy only 3 rack spaces (3U) each (UPS and battery pack require 6U total installed)
- 38 min. half load runtime, expandable with multiple external battery packs (part# BP48V60RT3U)
- Line-interactive voltage regulation corrects severe brownouts and overvoltages without using battery
  power
- Dual voltage output is simultaneously compatible with both 208V and 120V equipment

## Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 5kVA / 5000VA / 4000W line interactive 6U rack/tower UPS, Sine wave output
- 208 & 120V output during brownouts to 151V and overvoltages to 260V
- USB, RS232, EPO and slot for network communication card options
- Expandable runtime, 8 singleoutlet switched output load banks
- NEMA L6-30P input, 10 5-15R, 2 5-15/20R, 1 L6-30R & 1 L14-30R outlets
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

#### **Package Includes**

- SM5000RT3UTAA UPS System
- BP48V60RT3U battery pack
- USB, DB9 and EPO Cabling
- Mounting hardware
- Instruction manual with warranty information



- 14 total outlets (120V: 10 x 5-15R, 2 x 5-20R/208V: 1 x L6-30R, 1 x L14-30R)
- Diagnostic LEDs provide visual indication of 17 separate performance conditions
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- 4 built-in communications ports (2 x DB9, 2 x USB) for remote monitoring and unattended shutdown
- Compatible with Tripp Lite UPS management card options WEBCARDLX and SNMPWEBCARD
- 8 customized load management receptacles can be individually powered off and back on again via software interface to reboot remote equipment or perform "load shedding" of less critical loads to extend battery runtime for the most critical equipment
- Emergency Power Off (EPO) interface for emergency shutoff in large facilities
- Hot-swappable/user replaceable batteries allow on-site battery replacement through the front panel without powering off connected equipment or removing the UPS from the rack
- UPS battery set ships fully assembled and ready for connection to the power module, no time consuming, connection of individual internal batteries by user is necessary
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- NAFTA compliant

# **Specifications**

OVERVIEW	
UPC Code	037332161475
UPS Type	Line-Interactive
INPUT	
Nominal Input Voltage(s) Supported	208V AC
UPS Input Connection Type	L6-30P
Input Circuit Breakers	30A double-pole
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A 208V
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	5000
Output kVA Capacity (kVA)	5
Output Watt Capacity (Watts)	4000
Output kW Capacity (kW)	4



[	
Output Capacity Details	Maximum output increases to 4800W when hardwire or user supplied 50A rated input plug is used
Power Factor	0.8
Nominal Voltage Details	208/120V nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	208 & 120V (-10%, +20%)
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Eight switchable single-outlet 5-15R load banks
Output Circuit Breakers	15A branch rated (x3) - 2 breakers support 5 5-15R outlets each, one breaker supports 2 5-20R outlets, L6-30R and L14-30R outlets are unbreakered
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V; 208V
Output Receptacles	(10) 5-15R; (2) 5-15/20R; (1) L14-30R; (1) L6-30R
Individually Controllable Load Banks	Yes

#### BATTERY

Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	16 min. (4000w)
Half Load Runtime (min.)	38 min. (2000w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs
Expandable Runtime	Yes
External Battery Pack Compatibility	<a class="productLink" href="//www.tripplite.com/External-48V-2U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V24-2U">BP48V24-2U</a> (limit 1); <a class="productLink" href="//www.tripplite.com/External-48V-3U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V60RT-3U">BP48V24-2U</a> (limit 1); <a class="productLink" href="//www.tripplite.com/External-48V-3U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V60RT-3U">BP48V60RT-3U</a> (multi-pack compatible); <a class="productLink" href="//www.tripplite.com/External-48V-3U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V60RT-3U">BP48V60RT-3U</a> (multi-pack compatible); <a class="productLink" href="//www.tripplite.com/External-48V-2U-Rack-Tower-Battery-Pack-for-UPS-Systems~BP48V27-2US">BP48V27-2US</a> (multi-pack compatible); <a class="productLink" href="//www.tripplite.com/External-48V-2U-Rack-Tower-Battery-Pack-for-UPS-Systems~BP48V27-2US">BP48V27-2US</a>
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	3 hours
Battery Replacement Description	Hot-swappable, user replaceable batteries

## VOLTAGE REGULATION

Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 151 to 282
Overvoltage Correction	Input voltages between 240V and 282 are reduced by 12%
Undervoltage Correction	Input voltages between 180V and 199 are boosted by 12%
Severe Undervoltage Correction	Input voltages between 151V and 179 are boosted by 24%



Г

USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low- battery status
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	1020
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Cooling Method	Fans
Included Battery Pack Dimensions (hwd / in.)	5.2 x 17.5 x 22.8
Included Battery Pack Weight (lbs.)	135
Included Battery Pack Weight (kg)	61.23
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a class="productLink" href="//www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-&lt;br&gt;Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2POSTRMKITHD</a> ); Tower ( <a class="productLink" href="//www.tripplite.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-&lt;br&gt;Systems~2-9USTAND">2-9USTAND</a> )
Minimum Required Rack Depth with External Battery Pack (cm)	75
Minimum Required Rack Depth with External Battery Pack (in.)	29.5
Minimum Required Rack Depth without External Battery Pack (cm)	72
Minimum Required Rack Depth without External Battery Pack (in.)	28.25
Optional Mounting Accessory Notes	2 sets of <a class="productLink" href="//www.tripplite.com/2-Post-Rack-Mount-Installation-Kit-3U-Larger-&lt;br&gt;UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD">2POSTRMKITHD</a> required for 2 post rackmount installation of separate power module and battery pack
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	572
Primary UPS Height (mm)	132
Primary UPS Width (mm)	445
Rack Height	6U
Shipping Dimensions (hwd / cm)	62.23 x 88.90 x 60.96



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Shipping Dimensions (hwd / in.)	24.50 x 35.00 x 24.00
Shipping Weight (kg)	145.88
Shipping Weight (lbs.)	321.62
Unit Dimension Details	Includes 3U UPS/power module and 3U external battery pack
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	13.21 x 44.45 x 57.15
UPS Power Module Dimensions (hwd, in.)	5.2 x 17.5 x 22.5
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
Battery Mode BTU / Hr. (Full Load)	1518
AC Mode Efficiency Rating (100% Load)	94%
Audible Noise	45 dBA maximum, front side 1m
COMMUNICATIONS	
Network Management Cards	<a class="productLink" href="//www.tripplite.com/SNMP-Web-Management-Accessory-Card-SmartPro-&lt;br&gt;SmartOnline-UPS-Systems~SNMPWEBCARD">SNMPWEBCARD</a> ; <a <br="" class="productLink">href="//www.tripplite.com/Web-Management-Accessory-Card~WEBCARDLX"&gt;WEBCARDLX</a>
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; 2 USB ports, 1 DB9 serial and 1 DB9 contact closure port (4 total)
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Communications Interface	Contact closure; DB9 Serial; USB
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	151
High Voltage Transfer to Battery Power (Setpoint)	282
SPECIAL FEATURES	
Grounding Lug	Back panel grounding lug
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported



High Availability UPS Features	Automatic Voltage Regulation (AVR); Expandable battery backup; Hot swappable batteries; Sine wave output; Surge/noise protection	
STANDARDS & COMPLIANCE		
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI); TAA Compliant	
WARRANTY		
Product Warranty Period (Worldwide)	2-year limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>