

SM-1580

Professional 15" LCD CCTV Monitor with Speaker



Speaker



Monitor Viewing Angle



SVGA



720 TV Line



Color



Remote



SecurityMan SM-1580 is a professional 15-inch LCD CCTV monitor. It is the most economical and popular size of LCD CCTV monitor. It is mostly used in home, business, medical care and industrial for monitoring and replacing the traditional bulky CRT monitor. In comparison to a LCD TV or a computer LCD monitor, it is more reliable, stable, and last longer due to the nature of CCTV monitor. LCD CCTV monitor features higher definition, better color revivification, wider viewing angle, higher brightness and contrast ratio, better than a standard LCD display monitor. SM-1580 monitor is designed with convenient CCTV connection interfaces for your security needs.

Features:

- High quality A-grade 15-inch TFT/LCD color monitor
- High definition 720 TV lines and 1024x768 60Hz resolution
- High resistance to pressure, electric current, humidity and temperature
- Wide viewing angle 170°/150° (horizontal/vertical)
- Easy operation by front panel buttons and remote control
- Convenient CCTV interfaces; S-Video, BNC Video, RCA Audio, and VGA

Key Specifications:

System
VGA**Display Panel**

NTSC, PAL

Resolution/TVL

15" 4:3 Color TFT/LCD

Brightness

1024x768 60Hz/720TV Lines

Contrast300cd/m²**Response Time**

450:1

Viewing Angle (horizontal/vertical)

16ms

Composite Video

170°/150°

Video Input/Output**S-Video**

2 BNC inputs and 2 BNC outputs, 1.0Vpp, 75Ω,

VGA

1 input and 1 output

Audio

1 input

Menu

3 RCA inputs, 3 RCA outputs, and Speaker 2W

Dimension

OSD (On-Screen Digital)

Weight (Net/Gross)

14.02"x11.73"x2.64"

Power Supply

9.92 lbs (4.5 Kg) / 13.23 lbs (6 Kg)

Operating Temperature

AC100-230V 50-60 Hz

Operating Humidity

32W Max.

0°C - 40°C (32°-104°F)

10% - 85%

Package Includes:

- 1 x 15" LCD monitor with desktop base
- 1 x Power adapter
- 1 x Remote control (battery included)
- 1 x User's manual

(Optional item: SM-BK1580 Wall-mount bracket)