

## Wall-Mount Server Rack - 2U

Product ID: RK219WALVO



The RK219WALVO 2U 19-inch Steel Side Mount Rack is a Wall Mountable Server Rack that provides a robust solution for mounting your telecom, network or server equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 2U rack can be mounted to a wall or directly under a desk/table, expanding your workspace and keeping equipment easily accessible.

Perfect for SOHO (Small Office, Home Office) environments, the wallmount rack offers a space-saving installation for environments lacking the footprint space for a full-size server equipment rack. The rack allows your equipment to be mounted vertically - non-rackmount equipment can be installed using the rack as a wall case/chassis.

Constructed to EIA-RS310 19-inch rack standards, the RK219WALVO features a sturdy steel design and is backed by a Lifetime warranty.

## Certifications, Reports and Compatibility



## Applications

- Mount servers and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Install a blade server anywhere in an office without a full server room

- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

## Features

- **EASY TO USE:** This 2U wall mount rack can be mounted to a wall or directly under a desk/table, expanding your workspace and keeping equipment easily accessible
- **2U**
- **SAVES SPACE:** Perfect for SOHO environments, the wallmount network cabinet offers a space-saving installation for environments lacking the footprint space for a full-size server equipment rack
- **SOHO**
- **STURDY DESIGN:** Constructed to EIA-RS310 19-inch rack standards, the vertical wall mountable server rack features a sturdy steel design
- **EIA-RS310 19**
- **TAA COMPLIANT:** This TAA compliant 2U 19-inch Steel Side Mount Rack adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases
- **TAA TAAGSA 2U 19**
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this wall mount rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance
- **StarTech.com30IT**

---

## Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Enclosed Cabinet
U Height	2U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

**Performance**

Weight Capacity	61.1 lb [27.7 kg]
-----------------	-------------------

---

**Physical Characteristics**

Color	Black
Side Panel Construction	Steel

---

**Product Measurements**

Internal Width	19.6 in [49.7 cm]
Internal Depth	18.9 in [48.1 cm]
Product Length	4.7 in [11.9 cm]
Product Width	19.7 in [50.1 cm]
Product Height	21.8 in [55.4 cm]
Weight of Product	17.6 lb [8.0 kg]
Maximum Mounting Depth	18.9 in [48.1 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	22.6 in [57.4 cm]
Package Width	20.9 in [53.2 cm]
Package Height	6.1 in [15.4 cm]
Shipping (Package) Weight	21.3 lb [9.7 kg]

---

**What's in the Box**

Included in Package	1 - RK219WALVO 2U Wallmount rack 8 - #10-32 Screws 8 - #10-32 Cage Nuts
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*