

DESIGNED WITH YOUR BUSINESS IN MIND: HIGH PERFORMANCE PRINT, COPY AND SCAN

The Brother DCP-9270CDN is the perfect office companion for small or medium sized businesses. With three distinct functions – high speed print, copy and scan (single or double-sided), this versatile machine will answer all your demands for a machine that combines flexibility with sheer hard work. Here's why:

It's super-fast – delivering printing and copying speeds in colour and black and white, up to 28 pages per minute. What's more, the super high yield toners maintain high print quality whilst keeping costs down. You can print up to 800 sheets without re-stocking when you use the optional 500 sheet lower tray, plus the 50 sheet automatic document feeder is great for multiple scanning and copying of large print runs. Thanks to its large colour LCD touchscreen, the DCP-9270CDN is not only easy to operate but also easy to navigate too. And for total security, it has access restriction to control usage within the office.

PERFECT
FOR



- ✓ Printing, copying and scanning professional, quality documents
- ✓ Document management with ISIS accreditation
- ✓ Office work groups up to 10 users
- ✓ Printing volumes up to 4,000 pages per month
- ✓ Where high speed and superior performance matter
- ✓ Creating high-impact graphics
- ✓ Detailed documents that demand precise reproduction
- ✓ Cost control, security and fleet management
- ✓ Low running costs



DCP-9270CDN Technical Specifications

Duplex colour laser printer

Technology: Electrophotographic laser printer (singlepass)
Laser notice: Class 1 laser product (IEC60825-1:2007)
Print speed A4: Up to 28ppm (pages per minute) colour & mono
Print speed A4 (duplex): Up to 14 sides per minute (7 sheets per minute) colour & mono
Resolution: Up to 2,400 x 600dpi print resolution
Warm up time: Less than 33 seconds (from sleep mode)
First print out time: Less than 16 seconds (from ready mode)
Emulation: PCL6, BR-Script3 (PostScript®3 language emulation)
Resident fonts: PCL6 – 66 scalable fonts, 12 bitmap fonts, 13 barcodes, PostScript®3 – compatible fonts: 66
Memory capacity: 256MB – expandable up to 512MB, using industry standard 1 x DDR2 (144 PIN) slot
Interface: Hi-speed USB 2.0
Network: 10/100 Base-TX
Display: 5" (12.6cm) wide colour touch screen LCD
LEDs: Data LED (green) & error LED (orange)

Duplex colour copier

Copy speed A4: Up to 28cpm colour & mono
Resolution: Up to 1,200 x 600dpi
First copy out time: 21 seconds (colour), 19 seconds (mono)
Multi-copying / stack / sort: Makes up to 99 copies of each page / stacks or sorts
Reduction / enlargement ratio: Reduce and enlarge documents from 25% to 400% using 1% increments
N in 1 Copying: Allows the user to compress 2 or 4 pages on to a single A4 sheet

Duplex colour scanner

Resolution: Up to 1,200 x 2,400dpi (from scanner glass) 1,200 x 600dpi (from ADF)
Resolution (enhanced): Up to 19,200 x 19,200dpi
Grey scale: 256 shades of grey are available for copying and scanning
Colour depth: 48 bit internal, 24 bit external
Scan functions: Enables users to scan documents to email, image, OCR or file.** When used directly on the network also supports scan to network, scan to FTP and scan to email server, can also scan to USB flash memory drives when the machine has no connection to a PC

Media specifications

Media types: Standard / optional paper tray – plain paper, thin paper, recycled paper; multi-purpose tray – plain paper, thin paper, thick paper, thicker paper, recycled paper, glossy paper, bond, label, envelopes (thick & thin); ADF (automatic document feeder) – plain paper, recycled paper
Media capacity & weights: 250 sheet standard paper tray – 60 to 105g/m² (16 to 28lb); 500 sheet optional paper tray (LT-300CL) – 60 to 105g/m² (16 to 28lb); 50 sheet multi-purpose tray – 60 to 163g/m² (16 to 43lb); 50 sheet ADF (automatic document feeder) – 64 to 90 g/m² (17 to 24lb)

Media sizes: Standard / optional paper tray – A4, letter, B5 (ISO/JIS), A5, A5 (long edge), B6 (ISO), A6, executive, legal, folio; Multi-purpose tray – width 69.8mm to 216mm, length 116mm to 406.4mm

Paper output: 150 sheets (face down); 1 sheet (face up) straight paper path

Printer driver software

Windows®: Windows® 7 (32 & 64 bit editions), Windows Vista® (32 & 64 bit editions), Windows® XP Home Edition, Windows® XP Professional (32 & 64 bit editions), Windows® 2000 Professional, Windows Server® 2003 (network only / 32 & 64 bit editions), Windows Server® 2008 (network only / 32 & 64 bit editions), Windows Server® 2008 R2 (network only)
Macintosh: Mac OS X 10.4.11, 10.5.x, 10.6.x
Linux:** CUPS printing system (x86, x64 environment), LPD/LPRng printing system (x86, x64 environment)

Contact:

Printer driver functions

N-up printing: Save paper reducing 2, 4, 9, 16 or 25 A4 pages to 1 A4 page
Poster printing†: Enlarge 1 A4 page into a poster using 4, 9, 16 or 25 A4 pages for a bigger impact
Watermark printing†: Add predefined text or user-defined messages to your documents as a watermark
Booklet printing†: Print easy-to-read, professional documents in A5 booklet format using automatic duplex
Secure print††: Protect your print jobs with a PIN
Colour control tool: Edit the colour settings in the printer driver to get accurate colours every time
Colour restriction tool†: Colour printing can be restricted for individual users by an administrator to control costs
Header and footer†: Print the time & date and / or the user ID on the documents

Network

Web based management: Web browser print server management
Driver deployment wizard: A quick and easy way to deploy Brother printer drivers on a networked Windows® PC
BRAdmin Light: Print server management for Windows® and Mac OS X 10.4.11, 10.5.x, 10.6.x
BRAdmin Professional*:** For LAN/WAN management
Protocols: TCP/IP (IPv4 & IPv6)
IPv4 supported protocols: ARP, RARP, BOOTP, DHCP, APIPA (auto IP), WINS/NetBIOS name resolution, DNS resolver, mDNS, LLNMR responder, LPR/LPD, custom raw Port/Port9100, POP3, SMTP client with SSL, FTP client and server, LDAP client, CIFS client, TELNET server, SNMPv1/v2c/v3, HTTP/HTTPS server, SSL/TLS, IPP/PPS, TFTP client and server, LLTD responder, WebServicePrint, SNTp

IPv6 supported protocols: NDP, RA, DNS resolver, mDNS, LLNMR responder, LPR/LPD, custom raw Port/Port9100, IPP/PPS, FTP client and server, CIFS client, TELNET server, SNMPv1/v2c/v3, HTTP/HTTPS server, TFTP client and server, SMTP client, ICMPv6, SNTp client, LLTD responder, WebServicePrint
Network security: APOP, POP before SMTP, SMTP-AUTH, SSL/TLS (PPS, HTTPS, SMTP, POP), SNMP v3, 802.1x (EAP-MD5, EAP-FAST, PEAP, EAP-TLS, EAP-TTLS), Kerberos

Supplies

Inbox toners: 2,500 pages* BK; 1,500 pages* CM/Y
Standard toner black (TN-320BK): 2,500 pages*
Standard toner colour (TN-320C/M/Y): 1,500 pages*
High yield toner black (TN-325BK): 4,000 pages*
High yield toner colour (TN-325C/M/Y): 3,500 pages*
Super high yield black (TN-328BK): 6,000 pages*
Super high yield colour (TN-328C/M/Y): 6,000 pages*
Drum unit (DR-320CL): 25,000 A4 pages
Belt unit (BU-300CL): Up to 50,000 pages
Waste toner box (WT-300CL): Up to 50,000 pages

Dimensions / weight

With carton: 663(W) x 699(D) x 694(H)mm / 34kg
Without carton: 490(W) x 526(D) x 530(H)mm / 28.5kg

Others

Power consumption: 615W copying, 75W ready, 1.5W deep sleep
TEC value: 2.03kWh
Noise level: Sound pressure – less than 57dBA when printing, less than 33dBA in ready; sound power – less than 6.7B when printing, less than 4.21B in ready
Ecology: Power save – consume less energy when not in use; toner save – reduces toner usage
Recommended monthly print volume: 750 to 4,000 pages

* Declared yield value in accordance with ISO/IEC 19798 ** Requires Brother Software
 † Windows® only *** Optional free download available from <http://solutions.brother.com>
 †† Windows® & Apple Macintosh only

brother
at your side



Brother UK Ltd, Audenshaw, Manchester M34 5JD
 Tel: +44(0)8444 999 444 Fax: +44(0)161 931 2218
 Web: www.brother.co.uk

4890 DCP-9270CDN RAPPORT 01/11 V1

All specifications correct at time of printing. Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

Material code ZLFTDCP9270CDNU1

brother
at your side

HIGH SPEED PRINTING PIN SHARP COPYING REMARKABLY LOW RUNNING COSTS



DCP-9270CDN
PROFESSIONAL COLOUR LASER ALL-IN-ONE



28PPM
COLOUR PRINT
& COPY SPEEDS

**NETWORK
READY**

**AUTO
DOUBLE-SIDED**
PRINT, COPY & SCAN

**300 SHEET
CAPACITY**
EXPANDABLE TO 800

**12.7CM
TOUCHSCREEN
LCD**

**EASY PRINT
MANAGEMENT**

**SUPER HIGH
YIELD TONER**

DCP-9270CDN

PROFESSIONAL COLOUR LASER ALL-IN-ONE



INCREASE OFFICE EFFICIENCY

Super-fast printing and copying speeds up the way you work

SHARE WITH UP TO 10 PEOPLE

Give all your team the benefits of one powerful printer

SAVE ON PAPER COSTS

Slash paper costs with double-sided printing

LESS TIME REFILLING

Extra tray capacity for larger documents and print runs

SAVE TIME

Intuitive LCD touchscreen for easy use

EASY PRINT MANAGEMENT

Smooth installation and central monitoring for less downtime

LOWER RUNNING COSTS

Up to 6,000 page toner gives you even more savings

BEST EVER COLOUR, FASTEST EVER PRINT AND COPY SPEEDS

With its new generation advanced print engine, the DCP-9270CDN delivers stunning, business-enhancing results and real cost savings, fast.

YOU'RE COVERED

Buy a Brother printer and our UK based team of print specialists are always there to help, advise and support. Whatever you need to know, whenever you need it, online, on the phone or by email.

GREEN AND CLEAN



- Save up to 75% on paper with the booklet print feature
- Save power with a deep sleep mode of 1.5w and a TEC value of 2.03 kWh/week
- Reduce the need for reprint by using Brother original supplies
- Less packaging – less recycling with the super high yield toner