

**Phaser® 6500 and
WorkCentre® 6505**
Letter-size
Color Printer and
Color Multifunction Printer



Xerox® Phaser® 6500 Color Printer and WorkCentre® 6505 Color Multifunction Printer

The right colors, the easy way



Phaser® 6500 Color Printer and WorkCentre® 6505 Color Multifunction Printer

The right solution for today's pace of business. Your busy workteam needs a value-packed color device that gets the job done with the rare combination of outstanding print quality, unparalleled simplicity, and day-in, day-out dependability. Introducing the Phaser 6500 and WorkCentre 6505.



The colors your business needs

The Phaser 6500 color printer and WorkCentre 6505 color multifunction printer give your important documents a powerful, colorful boost.

- **Outstanding print quality.** A print resolution of up to 600 x 600 x 4 dpi makes your printed communications stand out and grab attention.
- **True Adobe® PostScript® 3™.** Count on consistently precise print jobs with bright, true colors and superior graphics.
- **Advanced toner technology.** Xerox-exclusive EA Toner uses particles engineered for uniform size and shape, producing superior image detail and line definition, and text that's sharp and clear.
- **Always the right color.** Pantone® Color approved solid-color simulations and Xerox color correction technology ensure results that match your expectations.

Ready to help

We designed the Phaser 6500 and WorkCentre 6505 as simple color devices that support single users and small workteams.

- **Print and go.** Work quickly with print speeds of up to 24 ppm for color and black-and-white (letter) or 23 ppm for color and black-and-white (A4).
- **More productivity for more people.** Connect and go, thanks to built-in networking and seamless compatibility with mixed-user environments, including PC, Macintosh and Linux.
- **Easy management.** With Xerox CentreWare® IS, remote device administration is handled with ease right from your computer's browser.
- **Out of color toner?** Our Run Black feature lets you continue printing with black until you can replace toner.
- **Total peace of mind.** Our standard one-year on-site warranty is backed by the industry-leading Xerox Total Satisfaction Guarantee.

Easy on your environment

From arrival to disposal, the Phaser 6500 and WorkCentre 6505 help you meet today's environmental challenges.

- **Print more, use less.** Whether you choose manual two-sided printing or upgrade to convenient automatic duplexing, you'll conserve paper for reduced costs and lower environmental impact.
- **Toner-only cartridges.** With minimal packaging, our toner-only cartridges allow for 80% less waste than comparable color devices, using integrated print cartridges.
- **A perfect fit.** Both devices feature a small footprint, which allows for easy integration within your work space, whether on your desk or in a shared location.
- **The quiet partner.** Engineered for extra-quiet operation to minimize impact on busy offices.
- **Consolidate and save.** The value-packed WorkCentre 6505 multifunction printer will save on energy and supplies costs by combining the functions of multiple devices into one.

Phaser® 6500 Quick Facts

- Print up to 24 ppm (letter) or 23 ppm (A4)
- 600 x 600 x 4 dpi
- Optional automatic two-sided printing*
- Powerful 400 MHz processor
- Robust 40,000 pages/month duty cycle
- 256 MB memory, expandable to 768 MB
- First page out time of 13 seconds color, 12 seconds black-and-white

* Standard on DN configuration




Print

8.5 x 11 in. / A4

ppm letter / A4

WxDxH:

15.9 x 16.75 x 16.4 in.
404 x 426 x 416 mm



Productivity, accelerated. The WorkCentre 6505 color multifunction printer builds on the outstanding print performance found in the Phaser 6500, delivering a host of powerful productivity tools designed to make your daily office tasks more efficient than ever.



1

The WorkCentre 6505 includes an intuitive front panel for configuring device settings and programming jobs.

2

A 35-sheet automatic document feeder handles media sizes from 5.5 x 5.5 in. to 8.5 x 14 in.

3

A front-side USB port allows users to quickly print from or scan to any standard USB memory device.

4

Powerful scanning capabilities include Scan to Email, Network Scanning, Direct Scan to Applications including Optical Character Recognition, and Scan to USB memory device.

5

Standard copy features include ID Card Copy, N-up, auto fit, cloning, collate and more.

6

Send faxes from the network using LAN Fax, or take advantage of full walkup fax features such as speed dial, remote receive and fax broadcast.

7

A standard 533 MHz processor and 256 MB memory (expandable to 768 MB) let the WorkCentre 6505 easily handle a heavy workload — even a steady stream of pages with graphics, photos and charts.

8

Optional 250-sheet paper tray increases capacity to 500 sheets — enough to load a full ream of paper.

WorkCentre® 6505 Quick Facts

- Print up to 24 ppm (letter) or 23 ppm (A4)
- 600 x 600 x 4 dpi
- Optional automatic two-sided printing*
- Powerful 533 MHz processor
- Robust 40,000 pages/month duty cycle
- 256 MB memory, expandable to 768 MB
- First page out time of 12 seconds color, and black-and-white

* Standard on DN configuration



Copy / Print / Scan / Fax / Email

8.5 x 11 in. / A4

24
23
ppm letter / A4

WxDxH:

16.9 x 21.4 x 23 in.
430 x 544 x 584 mm



Phaser® 6500 and WorkCentre® 6505

	Phaser 6500N		Phaser 6500DN		WorkCentre 6505N		WorkCentre 6505DN		
Speed	Up to 24 ppm color and black-and-white (Letter) / 23 ppm color and black-and-white (A4)								
Duty Cycle	Up to 40,000 pages / month ¹								
Paper Handling	Standard	NA				Automatic Document Feeder (ADF): 35 sheets: Custom Sizes: 5.5 x 5.5 in. to 8.5 x 14 in. / 139.7 x 139.7 mm to 215.9 x 355.6 mm			
		Manual Feed Slot: 1 sheet; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm							
	Optional	Tray 1: 250 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm							
		Tray 2: 250 sheets; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm							
Paper output	150 sheets face down								
Automatic two-sided printing	Optional		Standard		Optional		Standard		
Print First-page-out-time	As fast as 13 seconds color / 12 seconds black-and-white				As fast as 12 seconds color / 12 seconds black-and-white				
Resolution (max)	Up to 600 x 600 x 4 dpi								
Processor	400 MHz				533 MHz				
Memory (std / max)	256 MB / 768 MB								
Connectivity	USB 2.0, 10/100/1000 Base-T Ethernet								
Page description languages	Adobe® PostScript® 3™, PCL® 6 emulation								
Print features	Standard	PANTONE® Color approved solid-color simulations, N-up, Fit to page, Booklet printing, Skip blank pages, Run black, Covers/Separators ² , Poster printing ² , Watermarks ² , Overlays ² , Banner sheets ² , Draft mode ²							
	Optional ³	Secure print, Proof print, Personal print, Saved print, RAM collation							
Copy First-copy-out-time					As fast as 20 seconds color / 13 seconds black-and-white				
Copy resolution	NA				600 x 600 dpi				
Copy features					1 sided to 2 sided copying ⁴ , Reduce/enlarge (25 % -400 %), N-up copying, Auto fit, Cloning, Collate, ID Card Copy, Edge erase				
Fax Fax features ⁵	NA				33.6 Kbps with MH/MR/MMR/JBIG/JPEG compression, Secure fax receive, Lighter / darker, Polling, Remote receive (with external phone), Junk fax protection, Fax forwarding, Delay send, Broadcast, Address book (up to 200 speed dials, 6 group dials), Resolution up to 400 x 400 dpi, LAN Fax (Send)				
Scan Scan destinations	NA				Scan to Email (local address book or LDAP integration), Network Scanning via FTP (server) and SMB (server or computer), Direct Scan to Applications including OCR, USB Memory Device				
Scan features					Up to 1200 x 1200 dpi resolution, 24-bit color / 8-bit grayscale, PDF / JPEG / TIFF (single and multi-page) / XDW				
Security	Secure HTTPS (SSL), IPsec, 802.1x Authentication, IPv6, SNMPv3, Audit Log, IP Filtering								
Warranty	One-year on-site warranty, Xerox Total Satisfaction Guarantee								

¹ Monthly volume capacity expected in any one month. Not expected to be sustained on a regular basis; ² Accessed via PCL driver; ³ Requires optional Productivity Kit with 512 MB memory; ⁴ requires DN model or optional duplex unit; ⁵ Analog phone line required

Device Management

CentreWare® Internet Services, CentreWare Web, PrintingScout®, Email alerts

Print Drivers

Windows® XP, Vista, Server 2003, Server 2008, 7; Mac OS® version 10.5 and higher; Linux, Xerox Global Print Driver®, Xerox Mobile Express Driver™

Media Handling

Automatic Document Feeder^{**}: 12.5 lb. Bond – 45 lb. cover / 50 – 125 gsm; Manual Feed Slot and Trays: 16 lb. bond – 80 lb. cover / 60 – 216 gsm; Media types: Plain paper, glossy, business cards, envelopes, labels, cardstock

Operating Environment

Temperature: Storage: -4° to 104° F / -20° to 40° C; Operating: 50° to 90° F / 10° to 32° C; Humidity: 10% to 85%; Sound pressure levels: 6500: Printing (Enhanced): 53 dB(A), Standby: 25 dB(A); 6505: Printing (Enhanced): 52 dB(A), Standby: 22 dB(A); Sound power levels: Printing (Enhanced): 6500: 67.3 dB(A), Standby: 38.6 dB(A); 6505: 66.3 dB(A), Standby: 36.5 dB(A); Warm-up time (from sleep mode): as fast as 31 seconds

Electrical

Power: 110-127 VAC, 50/60 Hz or 220-247 VAC, 50/60 Hz; Power consumption: 6500: Standby: 55 W, Printing: 375 W, Sleep: 15 W; 6505: Standby: 65 W, Printing: 425 W, Sleep: 18.4 W; ENERGY STAR® qualified

Dimensions (WxDxH)

6500N/DN: 15.9 x 16.75 x 16.4 in. / 403.5 x 425.5 x 415.6 mm; Weight: 6500N: 40 lbs / 18.2 kg; 6500DN: 42.7 lbs / 19.4 kg; 250-sheet feeder: 15.75 x 18 x 4.2 in. / 400 x 457 x 107 mm; Weight: 9.7 lbs / 4.4 kg; 6505N/DN: 16.9 x 21.4 x 23 in. / 430 x 544.2 x 584.4 mm; Weight: 6505N: 62.5 lbs / 28.4 kg; 6505DN: 65.1 lbs / 29.6 kg; 250-sheet feeder: 16.5 x 20.4 x 4.2 in. / 419.2 x 518 x 107 mm; Weight: 9.9 lbs / 4.5 kg

Certifications

FCC Part 15, Class B, FCC Part 686, UL 60950-1/CSA 60950-1-07, 2nd Edition, CE Mark applicable to Low Voltage Directive (2006/95/EC), EMC Directive (2004/108/EC), and R&TTE Directive (1999/5/EC) 6, GOST, NOM, GS Mark, Citrix Ready, Section 508 (compliant with minor exceptions), ENERGY STAR® qualified

Supplies

High-capacity Print Cartridges*:
Black: 3,000 std. pages 106R01597
Cyan: 2,500 std. pages 106R01594
Magenta: 2,500 std. pages 106R01595
Yellow: 2,500 std. pages 106R01596

Standard-capacity Print Cartridges*:
Cyan: 1,000 std. pages 106R01591
Magenta: 1,000 std. pages 106R01592
Yellow: 1,000 std. pages 106R01593

Options

250-sheet feeder for Phaser 6500 097S04070
250-sheet feeder for WorkCentre 6505 097S04264
Productivity Kit 097S04269
Duplex unit 097S04069
Wireless network adapter
– N. America power converter 097S03740
– European power converter 097S03741
– UK power converter 097S03742

* Average standard pages. Declared Yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.



For more information, call 1-877-362-6567 or visit us at www.xerox.com/office

© 2011 Xerox Corporation. All rights reserved. Contents of this publication may not be reproduced in any form without permission of Xerox Corporation. XEROX®, XEROX and Design®, CentreWare®, Phaser® and WorkCentre® are trademarks of Xerox Corporation in the U.S. and/or other countries. Adobe® and PostScript® 3™ are registered trademarks or trademarks of Adobe Systems, Incorporated. PCL® is a registered trademark of Hewlett-Packard. As an ENERGY STAR® partner, Xerox Corporation has determined that this product meets the ENERGY STAR guidelines for energy efficiency. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. All other trademarks are the property of their respective manufacturers. The information in this brochure is subject to change without notice. 2/11 610P730196 650BR-01UA

