

**Xerox® Phaser® 6500 and
Xerox® WorkCentre® 6505**

Letter-size

Color Printer and

Color Multifunction Printer



Xerox® Phaser® 6500 Color Printer and Xerox® WorkCentre® 6505 Color Multifunction Printer

The right colors, the easy way.



Xerox® Phaser® 6500 Color Printer and Xerox® WorkCentre® 6505 Color Multifunction Printer

The right solution for today's pace of business. Your busy workteam needs a value-packed color device that gets the job done with the rare combination of outstanding print quality, unparalleled simplicity, and day-in, day-out dependability. Introducing the Phaser 6500 and WorkCentre 6505.



The colors your business needs

The Phaser 6500 color printer and WorkCentre 6505 color multifunction printer give your important documents a powerful, colorful boost.

- **Outstanding print quality.** A print resolution of up to 600 x 600 x 4 dpi makes your printed communications stand out and grab attention.
- **True Adobe® PostScript® 3™.** Count on consistently precise print jobs with bright, true colors and superior graphics.
- **Advanced toner technology.** Xerox-exclusive EA Toner uses particles engineered for uniform size and shape, producing superior image detail and line definition, and text that's sharp and clear.
- **Always the right color.** PANTONE® Color approved solid-color simulations and Xerox color correction technology ensure results that match your expectations.

Ready to help

We designed the Phaser 6500 and WorkCentre 6505 as simple color devices that support single users and small workteams.

- **Print and go.** Work quickly with print speeds of up to 24 ppm for color and black-and-white (letter) or 23 ppm for color and black-and-white (A4).
- **More productivity for more people.** Connect and go, thanks to built-in networking and seamless compatibility with mixed-user environments, including PC, Macintosh and Linux.
- **Easy management.** With Xerox® CentreWare Internet Services, remote device administration is handled with ease right from your computer's browser.
- **Out of color toner?** Our Run Black feature lets you continue printing with black until you can replace toner.
- **Total peace of mind.** Our standard one-year on-site warranty is backed by the industry-leading Xerox Total Satisfaction Guarantee.

Easy on your environment

From arrival to disposal, the Phaser 6500 and WorkCentre 6505 help you meet today's environmental challenges.

- **Print more, use less.** Whether you choose manual two-sided printing or upgrade to convenient automatic duplexing, you'll conserve paper for reduced costs and lower environmental impact.
- **Toner-only cartridges.** With minimal packaging, our toner-only cartridges allow for 80% less waste than comparable color devices, using integrated print cartridges.
- **A perfect fit.** Both devices feature a small footprint, which allows for easy integration within your work space, whether on your desk or in a shared location.
- **The quiet partner.** Engineered for extra-quiet operation to minimize impact on busy offices.
- **Consolidate and save.** The value-packed WorkCentre 6505 color multifunction printer will save on energy and supplies costs by combining the functions of multiple devices into one.


Phaser® 6500 Quick Facts

- Print up to 24 ppm (letter) or 23 ppm (A4)
- 600 x 600 x 4 dpi
- Optional automatic two-sided printing*
- Powerful 400 MHz processor
- Robust 40,000 pages/month duty cycle
- 256 MB memory, expandable to 768 MB
- First-page-out time of 13 seconds color, 12 seconds black-and-white

WxDxH:

15.9 x 16.75 x 16.4 in. / 404 x 426 x 416 mm

* Standard on DN configuration



Productivity, accelerated. The Xerox® WorkCentre® 6505 color multifunction printer builds on the outstanding print performance found in the Xerox® Phaser® 6500, delivering a host of powerful productivity tools designed to make your daily office tasks more efficient than ever.

1

The WorkCentre 6505 includes an intuitive front panel for configuring device settings and programming jobs.

2

A 35-sheet automatic document feeder handles media sizes from 5.5 x 5.5 in. to 8.5 x 14 in.

3

A front-side USB port allows users to quickly print from or scan to any standard USB memory device.

4

Powerful scanning capabilities include Scan to Email, Network Scanning, Direct Scan to Applications including Optical Character Recognition, and Scan to USB memory device.

5

Standard copy features include ID Card Copy, N-up, auto fit, cloning, collate and more.

6

Send faxes from the network using LAN Fax, or take advantage of full walkup fax features such as speed dial, remote receive and fax broadcast.

7

A standard 533 MHz processor and 256 MB memory (expandable to 768 MB) let the WorkCentre 6505 easily handle a heavy workload—even a steady stream of pages with graphics, photos and charts.

8

Optional 250-sheet paper tray increases capacity to 500 sheets—enough to load a full ream of paper.



WorkCentre® 6505 Quick Facts

- Print up to 24 ppm (letter) or 23 ppm (A4)
- 600 x 600 x 4 dpi
- Optional automatic two-sided printing*
- Powerful 533 MHz processor
- Robust 40,000 pages/month duty cycle
- 256 MB memory, expandable to 768 MB
- First-page-out time of 12 seconds color, and black-and-white

WxDxH:

16.9 x 21.4 x 23 in. / 430 x 544 x 584 mm

* Standard on DN configuration



Xerox® Phaser® 6500 and Xerox® WorkCentre® 6505

Device Specifications		Phaser 6500N		Phaser 6500DN		WorkCentre 6505N		WorkCentre 6505DN	
Speed		Up to 24 ppm color and black-and-white (Letter) / 23 ppm color and black-and-white (A4)							
Duty Cycle		Up to 40,000 pages / month¹							
Paper Handling									
Paper Input		Standard		Automatic Document Feeder (ADF): 35 sheets: Custom Sizes: 5.5 x 5.5 in. to 8.5 x 14 in. / 139.7 x 139.7 mm to 215.9 x 355.6 mm					
		Manual Feed Slot: 1 sheet; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm							
		Tray 1: 250 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm							
Optional		Tray 2: 250 sheets; Custom sizes: 5.8 x 8.3 in. to 8.5 x 14 in. / 148 x 210 mm to 216 x 356 mm							
Paper Output		150 sheets face down							
Automatic Two-sided Printing		Optional		Standard		Optional		Standard	
Print First-page-out Time		As fast as 13 seconds color / 12 seconds black-and-white				As fast as 12 seconds color / 12 seconds black-and-white			
Resolution (max)		Up to 600 x 600 x 4 dpi							
Processor		400 MHz				533 MHz			
Memory (std / max)		256 MB / 768 MB							
Connectivity		USB 2.0, 10/100/1000Base-T Ethernet							
Page Description Languages		Adobe® PostScript® 3™, PCL® 6 emulation							
Print Features		Standard		PANTONE® Color approved solid-color simulations, N-up, Fit to page, Booklet printing, Run black, Covers/Separators², Poster printing², Watermarks², Overlays², Banner sheets², Draft mode²					
		Optional³		Secure print, Proof print, Personal print, Saved print, RAM collation					
Mobile Printing		Optional		Xerox® Wireless Print Solutions Adapter (includes Apple AirPrint, Google Cloud Print™ v2.0 and Mopria®. For more information, visit www.xerox.com/WPSA)					
Copy First-copy-out Time						As fast as 20 seconds color / 13 seconds black-and-white			
Copy Resolution		NA				600 x 600 dpi			
Copy Features						1 sided to 2 sided copying⁴, Reduce/enlarge (25 %-400 %), N-up copying, Auto fit, Cloning, Collate, ID Card Copy, Edge erase			
Fax									
Fax Features⁵		NA		33.6 Kbps with MH/MR/MMR/JBIG/JPEG compression, Secure fax receive, Lighter / darker, Polling, Remote receive (with external phone), Junk fax protection, Fax forwarding, Delay send, Broadcast, Address book (up to 200 speed dials, 6 group dials), Resolution up to 400 x 400 dpi, LAN Fax (Send)					
Scan									
Scan Destinations						Scan to Email (local address book or LDAP integration), Network Scanning via FTP (server) and SMB (server or computer), Direct Scan to Applications including OCR, USB Memory Device			
Scan Features		NA		Up to 1200 x 1200 dpi resolution, 24-bit color / 8-bit grayscale, PDF / JPEG / TIFF (single and multi-page) / XDW, Xerox® Scan to PC Desktop SE (includes OCR, file conversion to Microsoft® Word®, Excel® and PowerPoint®. For more information, visit www.xerox.com/scan2pcSE)					
Security		Secure HTTPS (SSL), IPsec, 802.1x Authentication, IPv6, SNMPv3, Audit Log, IP Filtering							
Warranty		One-year on-site warranty, earn free service coverage with Xerox eConcierge®, Xerox® Total Satisfaction Guarantee							

¹ Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis.; ² Accessed via PCL driver.; ³ Requires optional Productivity Kit with 512 MB memory.; ⁴ requires DN model or optional duplex unit.; ⁵ Analog phone line required

Device Management

Xerox® CentreWare® Internet Services, CentreWare Web, Xerox® PrintingScout®, Email alerts, Apple® Bonjour

Print Drivers

Windows® XP, Vista, Server 2003, Server 2008, 7; Mac OS® version 10.5 and higher; Linux, Xerox® Global Print Driver®, Xerox® Mobile Express Driver®

Media Handling

Automatic Document Feeder^{**}: 12.5 lb. Bond – 45 lb. cover / 50 – 125 gsm; Manual Feed Slot and Trays: 16 lb. bond – 80 lb. cover / 60 – 216 gsm; Media types: Plain paper, glossy, business cards, envelopes, labels, cardstock

Operating Environment

Temperature: Storage: -4° to 104° F / -20° to 40° C; Operating: 50° to 90° F / 10° to 32° C; Humidity: 10 % to 85 %; Sound pressure levels: 6500: Printing (Enhanced): 53 dB(A), Standby: 25 dB(A); 6505: Printing (Enhanced): 52 dB(A), Standby: 22 dB(A); Sound power levels: Printing (Enhanced): 6500: 67.3 dB(A), Standby: 38.6 dB(A); 6505: 66.3 dB(A), Standby: 36.5 dB(A); Warm-up time (from sleep mode): as fast as 31 seconds

Electrical

Power: 110-127 VAC, 50/60 Hz or 220-247 VAC, 50/60 Hz; Power consumption: 6500: Standby: 55 W, Printing: 375 W, Sleep: 15 W; 6505: Standby: 65 W, Printing: 425 W, Sleep: 18.4 W; ENERGY STAR® qualified

Dimensions (WxDxH)

6500N/DN: 15.9 x 16.75 x 16.4 in. / 403.5 x 425.5 x 415.6 mm; Weight: 6500N: 40 lbs / 18.2 kg; 6500DN: 42.7 lbs / 19.4 kg; 250-sheet feeder: 15.75 x 18 x 4.2 in. / 400 x 457 x 107 mm; Weight: 9.7 lbs / 4.4 kg; 6505N/DN: 16.9 x 21.4 x 23 in. / 430 x 544.2 x 584.4 mm; Weight: 6505N: 62.5 lbs / 28.4 kg; 6505DN: 65.1 lbs / 29.6 kg; 250-sheet feeder: 16.5 x 20.4 x 4.2 in. / 419.2 x 518 x 107 mm; Weight: 9.9 lbs / 4.5 kg

Certifications

FCC Part 15, Class B, FCC Part 686, UL 60950-1/CSA 60950-1-07, 2nd Edition, CE Mark applicable to Low Voltage Directive (2006/95/EC), EMC Directive (2004/108/EC), and R&TTE Directive (1999/5/EC) 6, GOST, NOM, GS Mark, Citrix Ready, Section 508 (compliant with minor exceptions), ENERGY STAR® qualified

Supplies

High-capacity Print Cartridges*:

Black: 3,000 std. pages	106R01597
Cyan: 2,500 std. pages	106R01594
Magenta: 2,500 std. pages	106R01595
Yellow: 2,500 std. pages	106R01596

Standard-capacity Print Cartridges*:

Cyan: 1,000 std. pages	106R01591
Magenta: 1,000 std. pages	106R01592
Yellow: 1,000 std. pages	106R01593

Options

250-sheet feeder for Phaser 6500	097S04070
250-sheet feeder for WorkCentre 6505	097S04264
Productivity Kit	097S04269
Duplex unit	097S04069
Wireless network adapter	
– N. America power converter	097S03740
– European power converter	097S03741
– UK power converter	097S03742

* Average standard pages. Declared Yield in accordance with ISO/IEC 19798. Yield will vary based on image, area coverage and print mode.

For more information, visit us at www.xerox.com/office

©2016 Xerox Corporation. All rights reserved. Xerox®, Xerox and Design®, CentreWare®, Phaser®, WorkCentre® and Xerox eConcierge® are trademarks of Xerox Corporation in the United States and/or other countries. As an ENERGY STAR® partner, Xerox Corporation has determined that this product meets the ENERGY STAR guidelines for energy efficiency. ENERGY STAR and the ENERGY STAR mark are registered U.S. marks. The information in this brochure is subject to change without notice. Updated 4/16 610P730196B 650BR-01UC

