



Embargo Date: 7th February 2011
Sales Start Date: April, 2011
Target Market: SOHO Users wanting A3+ prints with speed and quality

Compact and stylish A3+ printer for photos and documents.

This ultra compact and stylish printer delivers exceptional quality prints of photos and documents up to A3+ format. Featuring a raft of creative facilities, it's ideal for the home or small office.

Key Features

Ultra compact and stylish A3+ printer ideal for home or small offices

Photolab-quality prints with min. 1pl ink droplets and up to 9600 dpi

5 Single Ink Tanks minimise waste and print costs

Efficient document print speeds - ISO ESAT 11.3 ipm for black and 8.8 ipm for colour

Print high quality 10x15 cm borderless photos in approx. 36 seconds

Create professional marketing materials with Solution Templates

Print quality photos from movies captured on select Canon cameras with Full HD Movie Print

Efficient web printing with Easy-WebPrint EX

Access exclusive professional content with CREATIVE PARK PREMIUM

ChromaLife100⁺ for long lasting beautiful photos

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PIXMA iX6550	4895B008AA	4960999682815	£199

What's in the box: PIXMA iX6550 printer, Canon genuine Ink Tanks (PGI-525PGBK, CLI-526BK, CLI-526C, CLI-526M, CLI-526Y), Setup CD, printed documents and power cord.

Technical Specifications

PRINTER FUNCTIONS	
Print Resolution	Up to 9600 ^[1] x 2400 dpi
Print Engine	Inkjet, 5 Single Inks, 5-colour system with minimum 1 pl droplet size
Photo Lab Quality Speed	Borderless 10 x 15cm: Approx. 36 seconds A3+ Bordered: Approx. 120 seconds ^[2]
Mono Print Speed	ESAT: Approx. 11.3 ipm
Colour Print Speed	ESAT: Approx. 8.8 ipm
Ink Cartridge Configuration	Single Ink technology - 5 separate ink tanks (PGI-525PGBK, CLI-526BK, CLI-526C, CLI-526M, CLI-526Y)
Black Ink Tank Life	Black: 335 pages (PGI-525PGBK), 3160 pages* (CLI-526BK) ^[3] Black: 2835 photos* (PGI-525PGBK), 615 photos* (CLI-526BK) ^[4] *Estimated Supplemental Yield
Colour Ink Tank Life	Cyan: 530 pages (CLI-526C), Magenta: 495 pages (CLI-526M), Yellow: 515 pages (CLI-526Y) ^[3] Cyan: 202 photos (CLI-526C), Magenta: 204 photos (CLI-526M), Yellow: 202 photos (CLI-526Y) ^[4]
Media Type	Plain Paper, High Resolution Paper (HR-101), Envelopes, Photo Paper Pro Platinum (PT-101), Photo Paper Plus Glossy II (PP-201), Photo Paper Plus Semi-gloss (SG-201), Glossy Photo Paper "Everyday Use" (GP-501), Matte Photo Paper (MP-101), Photo Stickers (PS-101), T-Shirt Transfer (TR-301)
Media Input	Sheet Feeder: Max. 150 sheets
Media Size	Sheet Feeder: A3+, A3, B4, A4, B5, A5, Letter, Legal, Envelopes (DL size or Commercial 10), 25 x 30cm (10 x 12 in), 20 x 25cm (8 x 10 in), 13 x 18cm, 10 x 15cm
Media Weight	Sheet Feeder: 64 to 105 g/m ² and supported Canon special media up to 300 g/m ²
Two Sided Printing	Available by manual operation only
Borderless Printing	Yes (A3+, A3, A4, 25 x 30cm, 20 x 25cm, 13 x 18cm, 10 x 15cm sizes) ^[5]

Standard Disclaimers

All specifications subject to change without notice.

Borderless 10x15cm photo lab quality print speed based on default driver setting using ISO/JIS-SCID N2 on Canon Photo Paper Plus Glossy II media.

Document print speed (ipm) on plain paper is measured based on the average of office category test ISO/IEC 24734.

Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used and does not take into account data processing time on host computer.

Ink yield may vary depending on texts/photos printed, applications software used, print mode and type of paper used. For yield information see www.canon-europe.com/ink/yield

All brand and product names are trademarks of their respective companies.

Microsoft, Windows and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.

For more information on ChromaLife100+ please visit www.canon-europe.com/chromalife100

INTERFACE AND CONNECTIVITY	
Interface Type - PC	USB 2.0 Hi-Speed
Interface Type - Camera	N/A
Interface Type - Mobile Phone / PDA	None
DRIVERS AND SOFTWARE	
Supported Operating System	Windows® 7, Windows Vista, Vista SP1/SP2, Windows XP SP2/SP3 Mac OS X v.10.4.11 - v.10.6
Minimum System Requirements	Windows® 7, Windows Vista, Vista SP1/SP2, Windows XP SP2/SP3 / Internet Explorer 6 or higher / CD-ROM drive / SVGA 800x600 Display ^[6] Mac OS X v.10.4.11 - v.10.6 / Safari 3 or higher / CD-ROM drive / XGA Display 1024x768 ^[6]
Driver Features	Collate, multiple page per sheet print, poster print, scaled print, fit-to-page print, Photo Noise Reduction, photo effects
Software Included	Windows: Easy-PhotoPrint EX, Easy-WebPrint EX, Solution Menu EX Mac: Easy-PhotoPrint EX, Easy-WebPrint EX, Solution Menu EX
GENERAL FEATURES	
Power Source	AC 100-240V, 50/60Hz
Power Consumption	Standby: Approx. 1.3W Off: Approx. 0.5W Printing: Approx. 20W ^[8]
Temperature Range	Operating environment: 5° C- 35° C
Humidity	Operating humidity: 10 - 90%RH (no condensation)
Acoustic Noise Levels	Printing: Approx. 45.0 dB(A) with default settings
Dimensions (W x D x H)	approx. 549 x 299 x 159 mm
Weight	Approx. 7.6 kg

Footnotes

- Ink droplets can be placed with a minimum pitch of 1/9600 inch.
- 11x14" (28x35cm) image bordered onto A3+ size based on the default setting using ISO/JIS-SCID N2 on Photo Paper Plus Glossy II and does not take into account data processing time on host computer.
- Declared yield value in accordance with ISO/IEC 24711. Values obtained by continuous printing.
- When printing Canon standard patterns continuously with the default settings on 10x15cm Photo Paper Plus Glossy II using Windows 7 printer driver in borderless printing mode and Windows 7 Home Premium's Windows Photo Viewer. Declared yield value determined based on Canon standard method referring to ISO/IEC 24711.
- Paper types NOT supported for borderless printing are as follows: Envelope, High Resolution Paper, T-Shirt Transfer, Photo Stickers.
- Easy-WebPrint EX for Windows requires 32 bit version of Internet Explorer 7 or 8. Easy WebPrint EX for Mac requires Safari. Operation can only be guaranteed on a PC with Windows 7, Windows Vista or Windows XP pre-installed.
- Installation on Mac OS Extended (Journaled) or Mac OS format drives.
HD Movie Print for Windows requires 2.6 GHz or faster processor, 1GB RAM and Canon ZoomBrowser EX 6.5 or later.
HD Movie Print for Mac OS requires Intel processor and Canon ImageBrowser 6.5 or later software.
- When printing ISO/JIS-SCID N2 pattern on A4 size plain paper using default settings.