



## Cat6 Patch Panel

48-Port, UTP, 2U

Part No.: **560283**

### Lifetime Warranty

Strict manufacturing standards ensure the highest quality in all INTELLINET NETWORK SOLUTIONS products. All items carry a full Lifetime Warranty — the strongest quality commitment anyone can make.

### Features:

- Solid and reliable terminations for copper cabling featuring a minimum of 3 mm 50 micro-inch gold-plated jack contacts
- Compatible with both 110 and Krone punch-down tools
- Supports 22 to 26 AWG stranded and solid wire
- For use with unshielded twisted pair (UTP) Cat6 network cable
- Ideal for Ethernet, Fast Ethernet and Gigabit Ethernet network applications
- Connects 48 RJ-45 ports to a network
- Occupies 2U rack height
- Meets 19" rackmount standards
- Lifetime Warranty

### Specifications:

#### Standards

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3ab (1000Base-T Gigabit Ethernet)

#### Certifications

- UL listed
- RoHS compliant

#### Environmental

- Dimensions: 482 mm (W) x 88 mm (H) x 48 mm (D) (19 x 3.5 x 1.9 in.)
- Horizontal distance between left and right mounting holes: 465 mm (18.3 in.)
- Vertical distance between top and bottom mounting holes: 75.8 mm (3 in.)
- Weight: 1.27 kg (2.8 lbs.)
- Operating temperature: -40 – 80°C (-40 – 176°F)

#### Package Contents

- Cat6 Patch Panel

*For more information on Intellinet products, consult your local dealer or visit [www.intellinet-network.com](http://www.intellinet-network.com).*

*All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.*

- 4 mounting screws
- Quick start guide

