

# Compact Mono Laser All-in-One Printer with Automatic Double-sided Printing

## TIME SAVING

24ppm copy and print speed  
Less refilling with a 250 sheet paper capacity

## QUALITY

High resolution colour scanning  
plus scan to PDF feature

## PEACE OF MIND

With free 12-month warranty and  
lifetime technical support



## HI-SPEED

First page out time of less than  
8.5 seconds  
Hi-Speed USB 2.0 connection

## SPACE SAVING

Compact footprint makes this ideal  
for a small office where space is at  
a premium

## LOWER RUNNING COSTS

Save paper with double-sided printing  
as standard  
Separate drum and toner to help keep  
costs down – only replace the one  
that's run out  
Reduce cost with longer lasting high  
yield toners

DCP-7060D

## GREEN AND CLEAN TECHNOLOGY

That meets environmental standards



In a small office, efficiency is the key. So the DCP-7060D is space-efficient, doing the job of three machines – mono printer, copier and colour scanner – in the space of just one. It's super-efficient in other ways, too. Such as saving time with rapid 24 pages per minute printing and copying (the first in less than 10 seconds) and a 250 sheet paper capacity. You'll also save money with automatic double-sided printing halving paper costs, separate drum and toner meaning you only need replace the one that's run out and longer-lasting high yield toners to cut running costs. It's a real asset to any small business!

# DCP-7060D

## Technical specifications

### General

**Engine:** Electrophotographic laser  
**Processor:** ARM946E-S 200MHz  
**Interface:** Hi-Speed USB 2.0  
**LCD Display Size:** 2 lines x 16 characters  
**Memory Capacity:** 32MB (RAM)  
**On / Off Switch:** Yes

### Mono Printer

**Speed (simplex):** 24 pages per minute  
**Speed (duplex):** 5 sheets per minute  
**Resolution:** HQ1200 (2,400 x 600 dpi) quality  
**First Print Out Time [From Ready Mode]:** Less than 8.5 seconds  
**Warm Up Time [From Sleep Mode]:** Less than 7 seconds  
**Emulation:** GDI (host based)

### Mono Copier

**Speed:** Up to 24cpm (copies per minute)  
**First Copy Out Time [From Ready Mode]:** Less than 11 seconds  
**Resolution:** 600 x 600 dpi  
**Multi-Copying /Stack:** Makes up to 99 copies of each page  
**Enlargement /Reduction Ratio:** Easily copy documents to a required paper size (25% to 400% in 1% increments).  
**Save Paper:** Copy 2 or 4 pages to a single page (N-up copying)

### Colour Scanner

**Resolution (Optical):** Up to 600 x 2,400 dpi  
**Resolution (Interpolated):** Up to 19,200 x 19,200 dpi  
**Colour Depth:** 48bit internal / 24bit external colour scanner  
**Grey Scale:** 256 shades of grey are available for copying or scanning  
**TWAIN Scanner Compliance:** Windows® 7, Windows Vista®, Windows® XP, Windows® 2000 and OS X 10.3.9 or greater  
**WIA Scanner Compliance:** Windows® 7, Windows Vista®, Windows® XP  
**SANE Scanner Compliance:** Linux  
**Scan To:** E-mail, image, OCR, file (Requires the Brother Control Centre software)  
**Scan Key:** Enables user to scan a document to e-mail, image, OCR, file using the scan key (Requires the Brother Control Centre software)

### Printer Driver

**Windows®:** Windows 7® (32 & 64 bit editions), Windows Vista® (32 & 64 bit editions), Windows XP Home Edition, Windows XP Professional (32 & 64 bit editions), Windows® 2000 Professional, Windows® Terminal Services 2003 & 2008<sup>†††</sup>, Citrix Presentation Server<sup>††††</sup>, Citrix XenApp<sup>††††</sup>, Citrix Desktop<sup>††††</sup>  
**Apple Macintosh:** Mac OS X 10.4.11 or greater  
**Linux<sup>\*\*\*</sup>:** CUPS printing system(x86, x64 environment), Linux printer driver for LPD/LPRng printing system (x86, x64 environment)

### Printer Driver Installation Options

**Installation Wizard:** An easy to use wizard that will guide you through whole installation process  
**Printer Driver Only:** Install only the printer driver using your own installation method  
**Driver Deployment Wizard [DDW]<sup>\*\*\*</sup>:** Guides you through the printer driver install and creates an executable file that can be used to install the printer driver on other PC's (Windows® only).

### Printer Driver Functions

**N-up Printing (Windows® & Mac only):** Reduce up to 2, 4, 9, 16 or 25 A4 pages into just one A4 page  
**Poster Printing<sup>†</sup>:** Enlarge 1 A4 page into a poster using 4, 9, 16 or 25 A4 pages  
**Watermark Printing<sup>†</sup>:** Watermark your documents with predefined text or with your own user-defined messages  
**Automatic Duplex<sup>†</sup>:** Automatically print to both sides of a piece of paper  
**Booklet Printing<sup>†</sup>:** Print documents in A5 Booklet format using automatic duplex

### Remote Management Utilities

**E-mail reports:** Reports containing basic usage data sent to a nominated e-mail address on a cyclical basis. This feature requires the Brother BRPrint Auditor application<sup>\*\*\*</sup> to be installed onto the same computer as the DCP-7055 / 7057.  
**E-mail notifications:** Alerts sent to a nominated e-mail address when anything which can disrupt printing activity occurs. This feature requires the Brother BRPrint Auditor application<sup>\*\*\*</sup> to be installed onto the same computer as the DCP-7055 / 7057.

### Paper Handling

**Paper Input<sup>\*\*</sup>:** Standard Tray: 250 sheets  
Manual paper feed slot: 1 sheet  
**Paper Output<sup>\*\*</sup>:** Face Down (standard output): 100 sheets  
Face Up: 1 sheet (straight paper path) 1 sheet

### Media Specifications

**Media Types:** Standard Tray Plain paper, thin paper, recycled paper  
Manual paper feed slot: Plain paper, thin paper, thick paper, recycled paper, bond paper, labels and envelopes  
**Media Weights:** Standard Tray: 60 – 105g/m<sup>2</sup>  
Multi-Purpose Tray: 60 – 163g/m<sup>2</sup>  
**Media Sizes:** Standard Tray: A4, letter, B5(ISO/JIS), A5, A5 (long edge), B6(ISO), A6, executive  
Multi-Purpose Tray: Width (76.2 – 220mm) x length (116.0 x 406.4)  
**List / Report:** System Set-up List - A printed report that shows the current setting of your machine.

### Page Counters - Available to view in LCD & printed report

**Total Print Pages:** Informs the user of the total number of all pages produced from this machine  
**Copy Pages:** Informs the user of the total number of copies made on this machine in pages  
**PC Print Pages:** Informs the user of the total number of PC prints from this machine  
**Report Pages:** Informs the user of the total number of reports printed on this machine in pages

### Supplies

**Standard Toner:** (TN-2210) 1,200 pages\*  
**High yield toner:** (TN-2220) 2,600 pages\*  
**Drum:** (DR-2200) 12,000 pages

The frequency of replacement of consumables will vary depending on the complexity of the prints, the percentage of coverage, paper size, page per job, and the type of media.

### Dimensions & Weights

**With carton & consumables:** 527 (W) x 510(D) x 440(H) mm, 13.2Kg  
**Without carton, with consumables:** 405 (W) x 398.5 (D) x 268(H) mm, 10.1Kg

### Power Consumption

**Printing:** Average 445W at 25c  
**Ready:** Average 55W at 25c  
**Deep Sleep:** Average 0.9w at 25c

### Sound Pressure Level

**Printing:** Less than 53 dB  
**Ready:** Less than 30 dB

### Sound Power Level

**Printing:** Less than 6.40B  
**Ready:** Less than 4.27B

### Ecology

**Typical Electrical Consumption (TEC):** 0.968 kWh / week  
**Power Saving:** This enables the machine to consume less energy when not in use.  
**Toner Saving:** This reduces the toner usage and helps to reduce the total cost of printer ownership.  
**Energy Star:** Certified to the world-wide eco label for power consumption.

### Duty Cycles

**Recommended:** 250 – 2,000 pages monthly print volume  
**Maximum:** 10,000 pages monthly print volume

### Contents

**Toner cartridge:** up to 700 pages\*  
**Drum unit:** up to 12,000 pages  
**Power:** supply cord  
**Driver software:** for Windows® & Apple Macintosh  
**User Guide:** (CD-ROM)  
Quick Set-up Guide  
**PC interface:** cable NOT included

<sup>†</sup> For Windows only

<sup>††</sup> Requires the Brother Control Centre Software

<sup>†††</sup> For USB printing only.

\*Approx. yield is declared in accordance with ISO/IEC 19752

\*\*Calculated with 80g/m<sup>2</sup> paper

\*\*\* Downloaded free of charge from Brother's Solutions Centre <http://solutions.brother.com>

**brother**  
at your side

Brother UK Ltd, Audenshaw, Manchester M34 5JD  
Tel: +44(0)8444 999 444 Fax: +44(0)161 931 2218  
Web: [www.brother.co.uk](http://www.brother.co.uk)