

Cat5e Wall-mount Patch Panel

12-Port, UTP

Part No.: **162470**

Features:

- Solid and reliable terminations for copper cabling featuring a minimum of 3mm, 50 micro-inch, gold-plated jack contacts
- Compatible with both 110 and Krone punch-down tools
- Supports 22 to 26 AWG stranded and solid wire
- For use with unshielded twisted pair (UTP) Cat5e network cable
- Cat5e performance is in compliance with the ANSI/TIA/EIA 568 B.2 standard
- Ideal for Ethernet, Fast Ethernet and Gigabit Ethernet network applications
- Connects RJ45 ports to a network
- Lifetime Warranty

Specifications:

Standards

- IEEE 802.3 (10Base-T Ethernet)
- IEEE 802.3u (100Base-TX Fast Ethernet)
- IEEE 802.3ab (1000Base-T Gigabit Ethernet)

Certifications

- UL
- RoHS

Environmental

- Dimensions: 254 mm x 82 mm x 47 mm (W x H x D); 10 x 3.2 x 1.9 in.
- Weight: 0.337 kg (11.9 oz.)
- Operating temperature: -40°C – 80°C (-40°F – 176°F)

Package Contents

- Cat5e Mini Patch Panel
- 2 mounting screws
- Instructions

