



## Universal Notebook Power Adapter

Automatic Adjustable Voltage, 7 Output Levels, 90 W, USB

Part No.: **101646**

Provides a power solution for mobile computing needs.

Give mobile computing a boost with reliable, high-performance power when and where it's needed with this Universal Notebook Power Adapter by Manhattan. Eight DC output plug tips match popular Acer, Asus, Compaq, Dell, Fujitsu, Gateway, HP, Sony, Toshiba, IBM/Lenovo and more. Automatic voltage detection and adjustment removes the guesswork and reduces the risk of damage to sensitive mobile computers and other portable devices. There is also a convenient built-in USB charging port. Ideal for power supply replacement, upgrade or spare power needs.

### Features:

- Automatically selects among 7 voltage output levels to provide a broad mobile power solution — from 12 V to 24 V
- Convenient, single power source with USB port for notebook computers and other portable devices
- Compatible with most notebook computers from Acer, Asus, Compaq, Dell, HP, Lenovo, Toshiba and more
- Convertible (8) plug tips ensure proper polarization and fit
- Overload, overcurrent and overheat protection
- Lightweight and compact design easily stores for travel
- Three-Year Warranty

### Specifications:

#### Standards and Certifications

- FCC
- CE
- WEEE
- RoHS

#### Power Cable

- UL
- cUL

#### Input Characteristics

- AC rated voltage: 100 – 240 V
- AC voltage range: 90 – 264 V
- Frequency range: 50 – 60 Hz ( $\pm 3$  Hz)
- Current: 2.1 A max
- No-load power consumption:  $\approx 0.5$  W

#### Output Characteristics

- Rated voltage: 12 / 15 / 16 / 18.5 / 19 / 19.5 / 24 V (autoset by output tips)
- Peak load current: 6 A (constant current)
- Rated power: 90 watts maximum
- Ripple and noise:  $\approx 2\%$  of output voltage (peak-to-peak)
- USB output voltage: 5.0 V  $\pm 5\%$
- USB output current : 1.0 A
- USB output peak current : 2.1 A

#### Protection Characteristics

- Short circuit: auto recovery mode
- Primary current protection: an internal fuse on the AC input line
- Dielectric withstand voltage, primary (input AC short)-to-secondary (output DC short): 3000 VAC, 5 mA, 1 minute
- Leakage current  $\approx 0.25$  mA
- Insulation resistance, input to output: 10 M $\Omega$  at 500 VDC
- Reinforced insulation system, primary-to-ground and primary-to-secondary

#### Physical

- DC plug tips: 4.0 x 1.7 x 9.5 mm (19 V); 4.8 x 1.7 x 9.5 mm (18.5 V); 5.5 x 1.7 x 12 mm (19 V); 5.5 x 2.5 x 12 mm (19 V); 6.3 x 3.0 x 12 mm (15 V); 6.4 x 4.3 x 14 mm (16 V); 7.4 x 5.0 x 12 mm (18.5 V); 7.9 x 5.5 x 12 mm (20 V)
- Cable (combined length): 1.7 m (5.6 ft.)
- Dimensions: 122 x 64 x 19 mm (4.8 x 2.5 x 0.75 in.)
- Weight: 277.8 g (9.8 oz.)

#### Package Contents

- Universal Notebook Power Adapter
- 8 DC plug tips
- Instructions

#### Compatible with:

SONY (use 6.4 x 4.3 x 14, 19.5V DC plug tips)

Compatible with Models: Sony Vaio PCG-FR Series PCG-FR100, PCG-FR102, PCG-FR105, PCG-FR130, PCG-FR130U, PCG-FR150, PCG-FR215E, PCG-FR215H, PCG-FR215M, PCG-FR295MP, PCG-FR33/B, PCG-FR55/B, PCG-FR55E, PCG-FR55E/B, PCG-FR77/B, PCG-FR77E/B, PCG-FR780 Sony Vaio PCG-GRS Series PCG-GRS, PCG-GRS100, PCG-GRS150, PCG-GRS150K, PCG-GRS150P, PCG-GRS170, PCG-GRS170P, PCG-GRS175, PCG-GRS250, PCG-GRS515M, PCG-GRS515SP, PCG-GRS515SP/R, PCG-GRS515SPR, PCG-GRS55/B, PCG-GRS614MK, PCG-GRS614MP, PCG-GRS615SK, PCG-GRS615SP, PCG-GRS700K Sony Vaio

PCG-GRX Series PCG-GRX, PCG-GRX102/P, PCG-GRX315MK, PCG-GRX315MP, PCG-GRX316G, PCG-GRX316MK, PCG-GRX316MP, PCG-GRX316SK, PCG-GRX316SP, PCG-GRX415MK, PCG-GRX415MP, PCG-GRX416G, PCG-GRX416SK, PCG-GRX416SP, PCG-GRX500, PCG-GRX501, PCG-GRX51/BP, PCG-GRX510, PCG-GRX510K, PCG-GRX510P, PCG-GRX515G, PCG-GRX516MD, PCG-GRX516SP, PCG-GRX52/GB, PCG-GRX520, PCG-GRX520K, PCG-GRX520P, PCG-GRX530, PCG-GRX530K, PCG-GRX530P, PCG-GRX550, PCG-GRX550K, PCG-GRX550P, PCG-GRX560, PCG-GRX560K, PCG-GRX560P, PCG-GRX570, PCG-GRX570K, PCG-GRX570P, PCG-GRX580, PCG-GRX580K, PCG-GRX580P, PCG-GRX590, PCG-GRX590K, PCG-GRX590P, PCG-GRX590R, PCG-GRX590RP, PCG-GRX600, PCG-GRX606, PCG-GRX615G, PCG-GRX615S, PCG-GRX616MK, PCG-GRX616MP, PCG-GRX616SK, PCG-GRX616SP, PCG-GRX626, PCG-GRX626P, PCG-GRX650, PCG-GRX650P, PCG-GRX670, PCG-GRX670K, PCG-GRX670P, PCG-GRX690, PCG-GRX690K, PCG-GRX690P, PCG-GRX707, PCG-GRX72, PCG-GRX727, PCG-GRX81G/P, PCG-GRX90/P, PCG-GRX91G/P, PCG-GRX92G/P Sony Vaio PCG-NV Series PCG-NV, PCG-NV100, PCG-NV105, PCG-NV105/109, PCG-NV106, PCG-NV107, PCG-NV108, PCG-NV109, PCG-NV109M, PCG-NV170, PCG-NV170P, PCG-NV190, PCG-NV190P, PCG-NV200, PCG-NV205, PCG-NV205A, PCG-NV209, PCG-NV290, PCG-NV309, PCG-NV55E/B, PCG-NVR23 Sony Vaio PCG-R Series PCG-R505, PCG-R505BF, PCG-R505D, PCG-R505DCP, PCG-R505DF, PCG-R505DFK, PCG-R505DFP, PCG-R505DL, PCG-R505DLK, PCG-R505DLP, PCG-R505DMH, PCG-R505DS, PCG-R505DSK, PCG-R505DSP, PCG-R505Dx, PCG-R505E, PCG-R505EC, PCG-R505ECK, PCG-R505ECP, PCG-R505EL, PCG-R505ELK, PCG-R505ELP, PCG-R505ES, PCG-R505ESK, PCG-R505ESP, PCG-R505Ex, PCG-R505G, PCG-R505GC, PCG-R505GCK, PCG-R505GCP, PCG-R505GL, PCG-R505GLK, PCG-R505GLP, PCG-R505JL, PCG-R505MF, PCG-R505OM, PCG-R505TE, PCG-R505TEK, PCG-R505TF, PCG-R505TL, PCG-R505TS, PCG-R505TSK, PCG-R600, PCG-R600HEK, PCG-R600HEP, PCG-R600HEPD, PCG-R600HFK, PCG-R600HFP, PCG-R600HMK, PCG-R600HMKD, PCG-R600HMP, PCG-R600HMPD, PCG-R600MEP, PCG-R600MF, PCG-R600MX Sony Vaio VGN-A Series VGN-A100, VGN-A115B, VGN-A115M, VGN-A115S, VGN-A115Z, VGN-A130, VGN-A130P CTO, VGN-A140, VGN-A140B, VGN-A140P CTO, VGN-A150, VGN-A155, VGN-A160, VGN-A170, VGN-A170P CTO, VGN-A170P16C, VGN-A170P6C , VGN-A17SP, VGN-A190, VGN-A195, VGN-A195EP, VGN-A19SP, VGN-A230, VGN-A230P CTO, VGN-A240, VGN-A240P CTO, VGN-A250, VGN-A260, VGN-A270, VGN-A270P CTO, VGN-A270P2C , VGN-A290, VGN-A295, VGN-A29SP, VGN-A317M, VGN-A317S, VGN-A397XP, VGN-A39GP, VGN-A417M, VGN-A417S, VGN-A497XP, VGN-A49GP, VGN-A50B, VGN-A517B, VGN-A517M, VGN-A517S, VGN-A59GP, VGN-A600, VGN-A60091, VGN-A60B, VGN-A617B, VGN-A617M, VGN-A617S, VGN-A690, VGN-A790, VGN-A70P, Sony Vaio VGN-AX Series VGN-AX, VGN-AX570, VGN-AX570G, VGN-AX580, VGN-AX580G Sony Vaio VGN-BX Series VGN-BX, VGN-BX194VP, VGN-BX195EP, VGN-BX195VP, VGN-BX195XP, VGN-BX196VP, VGN-BX196XP, VGN-BX197XP, VGN-BX295VP, VGN-BX297XP, VGN-BX394VP, VGN-BX396VP, VGN-BX396XP, VGN-BX41VN, VGN-BX41XN, VGN-BX51VN, VGN-BX51XP, VGN-BX541, VGN-BX541B, VGN-BX543, VGN-BX543B, VGN-BX546, VGN-BX546B, VGN-BX670P, VGN-BX675P, VGN-BX740NW, VGN-BX740P, VGN-BX740PS, VGN-BX740PW, VGN-BX760NS, VGN-BX760P, VGN-BX760PS Sony Vaio VGN-C Series VGN-C1, VGN-C1/G, VGN-C1/P, VGN-C1/W, VGN-C140G/B,

VGN-C150P/B, VGN-C190P/H, VGN-C1S/G, VGN-C1S/P, VGN-C1S/W, VGN-C1Z/B, VGN-C220E/H, VGN-C240E/B, VGN-C250N/B, VGN-C291NW/H, VGN-C2S, VGN-C2S/G, VGN-C2S/H, VGN-C2S/L, VGN-C2S/P, VGN-C2S/W, VGN-C2Z, VGN-C2Z/B Sony Vaio VGN-CR Series VGN-CR11S, VGN-CR11S/L, VGN-CR11S/P, VGN-CR11S/W, VGN-CR11Z, VGN-CR11Z/R, VGN-CR120E, VGN-CR140E/B, VGN-CR140N/B, VGN-CR150E/B, VGN-CR190E, VGN-CR19VN/B, VGN-CR19XN/B, VGN-CR21E/L, VGN-CR21E/P, VGN-CR21E/W, VGN-CR21S, VGN-CR21S/L, VGN-CR21S/P, VGN-CR21S/W, VGN-CR21Z, VGN-CR21Z/N, VGN-CR21Z/R, VGN-CR29XN/B Sony Vaio VGN-E Series

VGN-E, VGN-E50B/B, VGN-E50B/D, VGN-E50B/S, VGN-E51B/D, VGN-E51B/S, VGN-E70B/B, VGN-E70B/S, VGN-E71B/S, VGN-E81B/B, VGN-E91B/B Sony Vaio VGN-FE Series VGN-FE, VGN-FE11H, VGN-FE31Z, VGN-FE550, VGN-FE550FM, VGN-FE550G, VGN-FE570, VGN-FE570G, VGN-FE590, VGN-FE590GC, VGN-FE590PA, VGN-FE590PB, VGN-FE660G, VGN-FE770G, VGN-FE790, VGN-FE880E/H, VGN-FE890 Sony Vaio VGN-FJ Series VGN-FJ, VGN-FJ170, VGN-FJ170/B, VGN-FJ180P, VGN-FJ180P/G, VGN-FJ180P/L, VGN-FJ180P/R, VGN-FJ180P/W, VGN-FJ1S, VGN-FJ1S/L, VGN-FJ1S/W, VGN-FJ1Z/W, VGN-FJ270, VGN-FJ270/B, VGN-FJ270P, VGN-FJ270P/B, VGN-FJ290, VGN-FJ290P1/B, VGN-FJ290P1/G, VGN-FJ290P1/L, VGN-FJ290P1/R, VGN-FJ290P1/V, VGN-FJ290P1/W, VGN-FJ57SP, VGN-FJ58SP Sony Vaio VGN-FS Series

VGN-FS, VGN-FS115B, VGN-FS115M, VGN-FS115Z, VGN-FS15GP, VGN-FS15SP, VGN-FS15TP, VGN-FS18GP, VGN-FS18SP, VGN-FS195VP, VGN-FS215M, VGN-FS25GP, VGN-FS25SP, VGN-FS28GP, VGN-FS28SP, VGN-FS35SP, VGN-FS38SP, VGN-FS415E, VGN-FS415W, VGN-FS485B, VGN-FS500, VGN-FS500P, VGN-FS500P12, VGN-FS515H, VGN-FS520, VGN-FS520B, VGN-FS530, VGN-FS530B, VGN-FS540, VGN-FS540P, VGN-FS550, VGN-FS550KIT1, VGN-FS570, VGN-FS620, VGN-FS620/W, VGN-FS625, VGN-FS625B, VGN-FS625B/W, VGN-FS630, VGN-FS630/W, VGN-FS635, VGN-FS635B, VGN-FS635B/W, VGN-FS640, VGN-FS640/W, VGN-FS645, VGN-FS645P, VGN-FS645P/H, VGN-FS660, VGN-FS660/W, VGN-FS675, VGN-FS675P, VGN-FS675P/H, VGN-FS680, VGN-FS680/W, VGN-FS690, VGN-FS715, VGN-FS730, VGN-FS730/W, VGN-FS730W, VGN-FS740, VGN-FS740/W, VGN-FS740W, VGN-FS742, VGN-FS742/W, VGN-FS742W, VGN-FS745P, VGN-FS745P/H, VGN-FS750, VGN-FS750P/W, VGN-FS755P/H, VGN-FS760/W, VGN-FS770, VGN-FS770/W, VGN-FS775, VGN-FS775P/H, VGN-FS780, VGN-FS780/W, VGN-FS780W, VGN-FS790, VGN-FS790BA/BZ, VGN-FS840, VGN-FS840/W, VGN-FS875, VGN-FS875P, VGN-FS875P/H, VGN-FS8900, VGN-FS8900P, VGN-FS8900P3, VGN-FS8900P4, VGN-FS8900P5, VGN-FS920, VGN-FS950 Sony Vaio VGN-FZ Series VGN-FZ11L, VGN-FZ11M, VGN-FZ11S, VGN-FZ11Z, VGN-FZ130, VGN-FZ130E, VGN-FZ130E/B, VGN-FZ140, VGN-FZ140E, VGN-FZ140E/B, VGN-FZ140N, VGN-FZ140N/B, VGN-FZ145, VGN-FZ145E, VGN-FZ145E/B, VGN-FZ150, VGN-FZ150E, VGN-FZ150E/B, VGN-FZ150E/BC, VGN-FZ160, VGN-FZ160E, VGN-FZ160E/B, VGN-FZ180, VGN-FZ180E, VGN-FZ180E/B, VGN-FZ18E, VGN-FZ18M, VGN-FZ190, VGN-FZ190E, VGN-FZ190E/B, VGN-FZ190N, VGN-FZ19VN, VGN-FZ21E, VGN-FZ21M, VGN-FZ21S, VGN-FZ21Z Sony Vaio VGN-N Series

VGN-N, VGN-N120, VGN-N120G, VGN-N120G/W, VGN-N130, VGN-N130G, VGN-N130G/B, VGN-N130G/W, VGN-N130P, VGN-N130P/B, VGN-N150, VGN-N150G, VGN-N150G/W, VGN-N150P, VGN-N150P/B, VGN-N160, VGN-N160G, VGN-N160G/W,

VGN-N170, VGN-N170G, VGN-N170G/T, VGN-N170G/W, VGN-N220, VGN-N220E, VGN-N220E/B, VGN-N220E/W, VGN-N230, VGN-N230E, VGN-N230E/B, VGN-N230E/T, VGN-N230E/W, VGN-N250, VGN-N250E, VGN-N250E/B, VGN-N250N, VGN-N250N/B, VGN-N270, VGN-N270E/T, VGN-N270E/W, VGN-N29VN/B, VGN-N31M, VGN-N31M/W, VGN-N31S/W, VGN-N31Z/W, VGN-N320, VGN-N320E, VGN-N320E/B, VGN-N320E/W, VGN-N330, VGN-N330E, VGN-N330E/B, VGN-N330N, VGN-N330N/B, VGN-N350, VGN-N350E/B, VGN-N350E/T, VGN-N350E/W, VGN-N350N, VGN-N350N/B, VGN-N370, VGN-N370E/B, VGN-N370E/T, VGN-N370E/W, VGN-N38E/W, VGN-N38Z/W Sony Vaio VGN-NR Series VGN-NR11M/S, VGN-NR11S/S, VGN-NR11Z/S, VGN-NR11Z/T Sony Vaio VGN-N-Series VGN-N11S/W, VGN-N19VP/B Sony Vaio VGN-S3 Series VGN-S380, VGN-S380B, VGN-S380B/P, VGN-S380P, VGN-S3HP, VGN-S3VP, VGN-S3XP Sony Vaio VGN-S4 Series VGN-S4, VGN-S430, VGN-S430P, VGN-S430P/S, VGN-S460, VGN-S460/B, VGN-S460P, VGN-S460P/B, VGN-S470, VGN-S470/B, VGN-S470P/B, VGN-S470P/S, VGN-S4HP/B, VGN-S4HRP/B, VGN-S4M/S, VGN-S4VP/B, VGN-S4XP/B, VGN-S4XRP/B Sony Vaio VGN-S5 Series VGN-S550, VGN-S550P/B, VGN-S55SP/S, VGN-S560, VGN-S560P/B, VGN-S570, VGN-S570P/S, VGN-S580, VGN-S580HA/RO, VGN-S5HP/B, VGN-S5M/S, VGN-S5VP/D, VGN-S5XP, VGN-S5XP/B Sony Vaio VGN-SZ Series VGN-SZ, VGN-SZ110/B, VGN-SZ120P/B, VGN-SZ140, VGN-SZ140PC, VGN-SZ140PD, VGN-SZ160, VGN-SZ160P, VGN-SZ160P/C, VGN-SZ170P, VGN-SZ170P/C, VGN-SZ1HP/B, VGN-SZ1M/B, VGN-SZ240, VGN-SZ240P12, VGN-SZ250P/C, VGN-SZ260P/C, VGN-SZ270, VGN-SZ270P, VGN-SZ270P/C, VGN-SZ281, VGN-SZ281P, VGN-SZ281P/X, VGN-SZ281P/XK1, VGN-SZ2VP/X, VGN-SZ2XP/C, VGN-SZ320P/B, VGN-SZ330P/B, VGN-SZ340, VGN-SZ360P/C, VGN-SZ370P/C, VGN-SZ381P/X, VGN-SZ390, VGN-SZ3VWP/X, VGN-SZ3XWP/C, VGN-SZ4, VGN-SZ430N/B, VGN-SZ440N23, VGN-SZ450N/C, VGN-SZ460N/C, VGN-SZ470N/C, VGN-SZ480, VGN-SZ491N/X, VGN-SZ4MN/B, VGN-SZ4VWN/X, VGN-SZ4XWN/C, VGN-SZ5MN/B, VGN-SZ5VWN/X, VGN-SZ5XWN/C, VGN-SZ61MN/B, VGN-SZ61VN/X, VGN-SZ61WN/C  
Compaq (use 4.0 x 1.7, 19V DC plug tips)

Compatible with laptop models: Compaq Mini 700ED Series: NF283EA, NF283EAR, Compaq Mini 700EF Series: NF291EA, NF291EAR, Compaq Mini 700EI Series: NG638EA, NG638EAR, Compaq Mini 700EK Series: NF289EA, Compaq Mini 700EL Series: NF288EA, NF288EAR, Compaq Mini 700EM Series: NF277EA, NF277EAR, Compaq Mini 700EN Series: NG621EA, NG621EAR, Compaq Mini 700ER Series: NF276EA, Compaq Mini 700ET Series: FT309EA, FT309EAR, Compaq Mini 700EW Series: NG622EA, NG622EAR, Compaq Mini 701ED Series: NG647EA, Compaq Mini 701EG Series: NG635EA, NG635EAR, Compaq Mini 701EI Series: NF293EA, Compaq Mini 701EM Series: NF279EA, Compaq Mini 701ER Series: NF278EA, Compaq Mini 701ES Series: NG643EA, NG643EAR, Compaq Mini 701ET Series: FT308EA, FT308EAR, Compaq Mini 702EA Series: NF280EA, NF280EAR, Compaq Mini 703EA Series: NF281EA, Compaq Mini 705EI Series: NG649EA, Compaq Mini 705ES Series: P770EA, Compaq Mini 730EJ Series: NP635EA, Compaq Mini 730EO Series: NP765EA, NP765EAR, Compaq Mini 730EQ Series: NG661EA, Compaq Mini 731EI Series: NU803EA, Compaq Mini 731ET Series: NP649EA, Compaq Mini 733EB Series: NT384EA, Compaq Mini 733EF Series: NP775EA, Compaq Mini 735EF Series: NS519EA, Compaq Mini 735EI Series: NT385EA, Compaq Mini 735EQ Series: NS522EA, Compaq Mini 735ES Series: NS518EA, NS518EAR,

HP (use 4.0 x 1.7, 19V DC plug tips)

HP Mini 1000 PCs: HP Mini 1001TU Series: NE570PA, NE570PAR, HP Mini 1001XX Series: NC953AS, HP Mini 1002TU Series: NE571PA, HP Mini 1002XX Series: NC954AS, HP Mini 1003TU Series: NE572PA, HP Mini 1004TU Series: NE573PA, HP Mini 1005TU Series: NE574PA, HP Mini 1006TU Series: NE575PA, HP Mini 1007TU Series: NE576PA, HP Mini 1008TU Series: NE577PA, HP Mini 1009TU Series: NE578PA, HP Mini 1010LA Series: FY348LA, HP Mini 1010NR Series: FT315UA, FT315UAR, HP Mini 1010TU, Series: NE579PA, HP Mini 1011TU Series: NE580PA, HP Mini 1012TU Series: NE581PA, NE581PAR, HP Mini 1013TU Series: NE582PA, HP Mini 1014TU Series: NE585PA, HP Mini 1015TU Series: NE590PA, HP Mini 1016TU Series: NE594PA, HP Mini 1020LA Series: NG837LA HP Mini 1021TU Series: NL100PA, HP Mini 1022TU Series: NL101PA, HP Mini 1023TU Series: NQ149PA, HP Mini 1024TU Series: NQ150PA, HP Mini 1025TU Series: NQ155PA, HP Mini 1030NR Series: FW376UA, FW376UAR, HP Mini 1033CL Series: FZ978UA, FZ978UAR, HP Mini 1035NR Series: FT313UA, FT313UAR, HP Mini 1050LA Series: NQ332LA, HP Mini 1090LA Series: NJ209LA, HP Mini 1000 CTO Series: FN819AV, FQ729AAR, FQ729AV, FR832AV, FV436AAR, FV436AV, NB914AV, NJ683AAR, NJ683AV, NP763AV, HP Mini 1000 Vivienne Tam Edition PC: HP Mini 1018TU Vivienne Tam Edition Series: NL037PA, NL037PAR, HP Mini 1019TU Vivienne Tam Edition Series: NL038PA, HP Mini 1020TU Vivienne Tam Edition Series: NL039PA, HP Mini 1097EI Vivienne Tam Edition Series: NG645EA, HP Mini 1098EI Vivienne Tam Edition Series: NG646EA, HP Mini 1099EA Vivienne Tam Edition Series: NG633EA, NG633EAR, HP Mini 1099ED Vivienne Tam Edition Series: NG624EA, NG624EAR, HP Mini 1099EE Vivienne Tam Edition Series: NG640EA, HP Mini 1099EF Vivienne Tam Edition Series: NG628EA, NG628EAR, HP Mini 1099EI Vivienne Tam Edition Series: NG652EA, HP Mini 1099EK Vivienne Tam Edition Series: NG644EA, HP Mini 1099EL Vivienne Tam Edition Series: NG630EA, NG630EAR, HP Mini 1099EM Vivienne Tam Edition Series: NG641EA, HP Mini 1099EN Vivienne Tam Edition Series: NG634EA, NG634EAR, HP Mini 1099EP Vivienne Tam Edition Series: NG626EA, HP Mini 1099ER Vivienne Tam Edition Series: NG631EA, HP Mini 1099ES Vivienne Tam Edition Series: NG627EA, NG627EAR, HP Mini 1099ET Vivienne Tam Edition Series: NG632EA, NG632EAR, HP Mini 1099EW Vivienne Tam Edition Series: NG625EA, NG625EAR, HP Mini 1100 PCs: HP Mini 1100CM Series: KS167UT, HP Mini 1101TU Series: NQ159PA, HP MINI 1101XX Series: NR200AS, HP Mini 1102TU Series: NQ160PA,

AMI: (use 4.0 x 1.7, 19V DC plug tips)

TF6720,TF6760,FT8850

HP (use 4.8 x 1.7, 18.5V DC plug tips)

Compatible with laptop models: Compatible P/N: 324816-003, 325112-001, PPP014S, 239427-003, 239704-001, HP-OK065B13, PPP009H, HP PAVILION / COMPAQ PRESARIO: HP/COMPAQ 710C HP/COMPAQ 712C HP/COMPAQ 720C HP/COMPAQ 722C, HP/COMPAQ 810C HP/COMPAQ 812C, HP/COMPAQ 815C, HP/COMPAQ 820, HP/COMPAQ 820CSE HP/COMPAQ 820, HP/COMPAQ 825C, HP/COMPAQ 830C, HP/COMPAQ 832C, HP/COMPAQ 840C,

HP/COMPAQ 841C, HP/COMPAQ 842C, HP/COMPAQ 843C, HP/COMPAQ 845C, HP/COMPAQ850C, HP/COMPAQ855C, HP/COMPAQ 855CSE, HP/COMPAQ 855CXI, HP/COMPAQ 870CSE, HP/COMPAQ 870CSI, HP/COMPAQ 880C, HP/COMPAQ 882C, HP/COMPAQ 890CSE, HP/COMPAQ 890CSI, HP/COMPAQ 895CSE, HP/COMPAQ 895CSI, HP/COMPAQ 920C, HP/COMPAQ 960C, HP/COMPAQ 960CXI, HP Compaq Tablet PC: tc1000, tc1100, tc4200, HP Compaq Business Notebook: nc4000, nc4010, nc6000, nc8000, nx5000, nx6100, nw8000, HP Pavilion DV1000 Series: DV1000 / DV1000 CTO / DV1001 / DV1001AP / DV1001XX MV IUR / DV1002 / DV1002AP / DV1002XX MV IUR / DV1003 / DV1004 / DV1004AP / DV1005 / DV1006 / DV1006AP / DV1007 / DV1008 / DV1009 / DV1009AP / DV1009XX MV / DV1010 / DV1010AP / DV1010US / DV1010CA / DV1011 / DV1011 / DV1012 / DV1012LA / DV1013 / DV1014 / DV1014AP / DV1014LA / DV1015 / DV1015AP / DV1015LA / DV1016 / DV1017 / DV1018 / DV1019 / DV1020 / DV1021 / DV1021AP / DV1022 / DV1022AP / DV1023 / DV1024 / DV1024AP / DV1024LA / DV1025 / DV1025AP / DV1025LA / DV1026 / DV1027 / DV1028 / DV1029 / DV1029AP / DV1030 / DV1030AP / DV1031 / DV1031AP / DV1032 / DV1033 / DV1034 / DV1034AP / DV1040 / DV1040US / DV1040CA / DV1042 / DV1044 / DV1045 / DV1045LA / DV1049 / DV1049CL / DV1050 / DV1050US / DV1060 / DV1060US / DV1061 / DV1063 / DV1064 / DV1065 / DV1065US / HP Pavilion DV1300 Series: DV1300 / DV1310 / DV1310US / DV1311 / DV1311SE / DV1315 / DV1315CL / DV1320 / DV1320US / DV1321us / DV1330 / DV1330CA / DV1330US / DV1340 / DV1340US / HP Pavilion DV1400 Series: DV1400 / DV1410 / DV1410US / DV1411 / DV1411SE / DV1420 / DV1420US / DV1427us / DV1430 / DV1430US / DV1432 / DV1432US / DV1435 / DV1439 / DV1439US / DV1440 / DV1440US / HP Pavilion DV1500 Series: DV1500 / DV1510 / DV1510US / DV1510CA / DV1515 / DV1515CL / DV1519 / DV1519US / DV1520 / DV1520US / DV1520CA / DV1530 / 1530US / DV1530CA / DV1532 / DV1532US / DV1540 / DV1540US / DV1540CA / DV1550 / DV1550SE / DV1580 / DV1580SE / HP Pavilion DV2000 series dv2000 , dv2000t, dv2000z, dv2001tu, dv2001tx, dv2001xx, dv2002tu, dv2002tx, dv2002xx, dv2003ea, dv2003tu, dv2003tx, dv2004ea, dv2004tu, dv2004tx, dv2004xx, dv2005ea, dv2005tu, dv2005tx, dv2005xx, dv2006ea, dv2006tu, dv2006tx, dv2006xx, dv2007ea, dv2007tu, dv2007tx, dv2008ea, dv2008tu, dv2008tx, dv2009ea, dv2009tu, dv2009tx, dv2009xx, dv2010ea, dv2010tu, dv2010tx, dv2011ea, dv2011tu, dv2011tx, dv2012ea, dv2012tu, dv2012tx, dv2013ea, dv2013tu, dv2013tx, dv2014ea, dv2014tu, dv2014tx, dv2015ea, dv2015nr, dv2015tu, dv2015tx, dv2016ea, dv2016tu, dv2016tx, dv2017ea, dv2017tu, dv2017tx, dv2018ea, dv2018tu, dv2018tx, dv2019ea, dv2019tu, dv2019tx, dv2020ca, dv2020ea, dv2020tu, dv2020tx, dv2020us, dv2021tu, dv2021tx, dv2022tu, dv2023tu, dv2024tu, dv2024tx, dv2025la, dv2025nr, dv2025tu, dv2025tx, dv2026tu, dv2026tx, dv2027tu, dv2027tx, dv2028ea, dv2028tu, dv2028tx, dv2029ea, dv2029tu, dv2029tx, dv2030ea, dv2030tu, dv2030tx, dv2031ea, dv2031tu, dv2031tx, dv2032ea, dv2032tu, dv2032tx, dv2033ea, dv2033tu, dv2033tx, dv2034ea, dv2034tu, dv2034tx, dv2035ea, dv2035la, dv2035tu, dv2035tx, dv2035us, dv2036ea, dv2036tu, dv2036tx, dv2037tu, dv2037tx, dv2037us, dv2038tu, dv2038tx, dv2039tu, dv2039tx, dv2040ca, dv2040tu, dv2040tx, dv2040us, dv2041tu, dv2041tx, dv2042tu, dv2042tx, dv2043tu, dv2043tx, dv2044tu, dv2044tx, dv2045ea, dv2045tu, dv2046tu, dv2046tx, dv2047cl, dv2047tx, dv2048tx, dv2049tx, dv2050tx, dv2050us, dv2053ea, dv2054ea, dv2055ea, dv2056ea, dv2057ea, dv2058ea, dv2064ea, dv2065ea, dv2080ea, dv2081ea, dv2082ea, dv2083ea, dv2084ea, dv2085ea, dv2088xx, dv2095ea, dv2097ea, dv2098ea, dv2099ea, dv2100, dv2101au, dv2101eu, dv2101tu, dv2101tx, dv2101xx, dv2102au, dv2102eu, dv2102tu, dv2102tx, dv2103au, dv2103ea, dv2103tu, dv2103tx, dv2104au, dv2104ea,

dv2104eu, dv2104tu, dv2104tx, dv2105ea, dv2105tu, dv2105tx, dv2106ea, dv2106eu, dv2106tu, dv2106tx, dv2107tu, dv2107tx, dv2108ea, dv2108tu, dv2108tx, dv2109tu, dv2109tx, dv2110eu, dv2110tu, dv2110tx, dv2111tu, dv2111tx, dv2112tu, dv2112tx, dv2113tu, dv2113tx, dv2114tx, dv2115ea, dv2115tu, dv2115tx, dv2116ea, dv2116tx, dv2116wm, dv2117tx, dv2118la, dv2118tx, dv2119tx, dv2120ca, dv2120la, dv2120tu, dv2120tx, dv2120us, dv2121tu, dv2121tx, dv2122tu, dv2122tx, dv2123tu, dv2123tx, dv2124tx, dv2125la, dv2125nr, dv2125tx, dv2126tx, dv2127tx, dv2128tx, dv2129ea, dv2129tx, dv2130br, dv2130ea, dv2130tx, dv2130us, dv2131ea, dv2131tx, dv2132ea, dv2132tx, dv2133ea, dv2133tx, dv2134ea, dv2134tx, dv2135la, dv2135tx, dv2136tx, dv2137tx, dv2138tx, dv2138xx, dv2139tx, dv2140br, dv2140eu, dv2140tx, dv2141eu, dv2141tx, dv2142tx, dv2143tx, dv2144tx, dv2145tx, dv2146tx, dv2147ea, dv2147tx, dv2148tx, dv2149ea, dv2149tx, dv2150ea, dv2150tx, dv2151ea, dv2151tx, dv2152ea, dv2152tx, dv2153tx, dv2154tx, dv2155tx, dv2160br, dv2164eu, dv2166eu, dv2171ca, dv2171cl, dv2171ea, dv2172ea, dv2173ea, dv2174cl, dv2174ea, dv2175ea, dv2180eu, dv2184ea, dv2185ea, dv2188ea, dv2190ea, dv2195eu, dv2196ea, dv2197ea, dv2200, dv2210us, HP Pavilion DV2500 Series dv2500, dv2500t, dv2501tu, dv2501tx, dv2501xx, dv2502tu, dv2502tx, dv2503tu, dv2503tx, dv2503xx, dv2504tu, dv2504tx, dv2505tu, dv2505tx, dv2506tu, dv2506tx, dv2506xx, dv2507tu, dv2507tx, dv2508tu, dv2508tx, dv2509tu, dv2509tx, dv2510tu, dv2510tx, dv2511tu, dv2511tx, dv2512tu, dv2512tx, dv2513tu, dv2513tx, dv2514tu, dv2514tx, dv2515ea, dv2515tu, dv2515tx, dv2516tu, dv2516tx, dv2517tu, dv2517tx, dv2518tu, dv2518tx, dv2519ea, dv2519tu, dv2519tx, dv2520ea, dv2520tu, dv2520tx, dv2521ea, dv2521tx, dv2522tx, dv2523tx, dv2524tx, dv2525ea, dv2527tx, dv2528ea, dv2528tx, dv2529ea, dv2529tx, dv2530ea, dv2530tx, dv2534tx, dv2535la, dv2535tx, dv2536tx, dv2550se, dv2554ea, dv2555ea, dv2560ea HP Pavilion DV4000 Series: DV4000 / DV4000 CTO / DV4005 / DV4005US / DV4010 / DV4015 / DV4015CL / DV4018 / DV4018CL / DV4020 / DV4020us / DV4030 / DV4030US / DV4030CA / DV4040 / DV4040CA / DV4040US / DV4100 / DV4100 CTO / DV4125 / DV4125US / DV4129 / DV4129US / DV4130 / DV4130US / DV4150 / DV4150CA / DV4150US / DV4155 / DV4155CL / DV4155US / DV4165 / DV4165CL / DV4170 / DV4170CA / DV4170US / DV4200 / DV4210 / DV4217 / DV4217CL / DV4220 / DV4223 / DV4223CL / DV4230 / DV4230us / DV4250 / DV4250US / DV4250CA / DV4253 / DV4253US / DV4257 / DV4257US / DV4269 / DV4269US / DV4270 / DV4270US / DV4270CA / DV4272 / DV4272US / DV4300 / DV4305 / DV4305US / DV4307 / DV4307CA / DV4307CL / DV4308 / DV4308WM / DV4310 / DV4310US / DV4320 / DV4320US / DV4330 / DV4330US / DV4330CA / DV4340 / DV4340US / DV4340CA / DV4400 / DV4401 / DV4420, HP Pavilion DV5000 Series: DV5000 / DV5001 / DV5003 / DV5003CL / DV5010 / DV5017 / DV5017CL / DV5020 / DV5020US / DV5020CA / DV5029 / DV5029US / DV5030 / DV5030US / DV5040 / DV5040US / DV5100 / DV5100CTO / DV5110 / DV5110US / DV5120 / DV5120US / DV5123 / DV5123CL, HP Pavilion DV6000 Series, HP Pavilion DV8000 Series: DV8000 / DV8000 CTO / DV8005 / DV8010 / DV8013 / DV8013CL / DV8026ea / DV8040 / DV8040CA / DV8040US / DV8045 / DV8080 / DV8088 / DV8088US / DV8100 / DV8110 / DV8110US / DV8113 / DV8113CL / DV8120 / DV8120US / DV8120CA / DV8123 / DV8123CL / DV8125 / DV8125NR / DV8130 / DV8130US / DV8135nr / DV8140 / DV8140US / DV8155 / DV8200 / DV8220 Series, HP Pavilion ZT3000 Series: HP Pavilion ZT3000 / ZT3001 / ZT3001US / ZT3010 / ZT3010US / ZT3015 / ZT3020 / ZT3020US / ZT3025 / ZT3030 / ZT3040 / ZT3050 / ZT3068 / ZT3068CL

/ ZT3101 / ZT3101US / ZT3110 / ZT3120 / ZT3130 / ZT3140 / ZT3140US / ZT3170 / ZT3170US / ZT3200 / ZT3201 / ZT3201US / ZT3205 / ZT3210 / ZT3215 / ZT3220 / ZT3225 / ZT3230 / ZT3235 / ZT3240 / ZT3241 / ZT3242 / ZT3250 / ZT3250US / ZT3260 / ZT3280 / ZT3280US / ZT3300 / ZT3301 / ZT3301US / ZT3302 / ZT3302US / ZT3305 / ZT3310 / ZT3340 / ZT3340US / ZT3349 / ZT3349CL / ZT3350 / ZT3350US / ZT3355 / ZT3355US / ZT3380 / ZT3380US / ZT3400, HP Pavilion ZE2000 Series: HP Pavilion ZE2000 / ZE2000 CTO / ZE2004 / ZE2004US / ZE2005 / ZE2005US / ZE2008 / ZE2008WM / ZE2010 / ZE2015 / ZE2015US / ZE2020 / ZE2020CA / ZE2100 / ZE2108 / ZE2108WM / ZE2109 / ZE2109US / ZE2110 / ZE2110US / ZE2113 / ZE2113US / ZE2114 / ZE2114US / ZE2115 / ZE2115US / ZE2117 / ZE2117US / ZE2120 / ZE2120CA / ZE2150 / ZE2150US / ZE2200 / ZE2200 CTO / ZE2300 / ZE2308 / ZE2308WM / ZE2309 / ZE2309NR / ZE2315 / ZE2315US / ZE2400 / ZE2401 / ZE2401XT, HP Pavilion ZE4900 Series: ZE4900 / ZE4901 / ZE4901us / ZE4902 / ZE4903 / ZE4904 / ZE4905 / ZE4906 / ZE4907 / ZE4908 / ZE4910 / ZE4910us / ZE4911 / ZE4913 / ZE4915 / ZE4916 / ZE4917 / ZE4918 / ZE4919 / ZE4920 / ZE4922 / ZE4923 / ZE4925 / ZE4926 / ZE4928 / ZE4929 / ZE4930 / ZE4935 / ZE4940 / ZE4950 / ZE4951 / ZE4960 / ZE4980, Compaq Presario M2000 Series: M2000 / M2001 / M2005 / M2005US / M2007 / M2007US / M2010 / M2010CA / M2010US / M2015 / M2015CL / M2070 / M2070US / M2099 / M2100 / M2100 / M2101 / M2101US / M2105 / M2105CA / M2105US / M2108 / M2108US / M2200 / M2300 / M2400 / M2401 / M2401XT, Compaq Presario 2200 Series: 2200 / 2200LA / 2201 / 2201AS / 2201US / 2202 / 2202US / 2203 / 2203AL / 2203AS / 2203US / 2204 / 2204AL / 2204AS / 2204US / 2205 / 2205AL / 2205AP / 2205AS / 2205LA / 2206 / 2206AL / 2206AP / 2206US / 2207 / 2207AL / 2207AP / 2207AS / 2208 / 2208AP / 2208AS / 2209 / 2209AP / 2209CL / 2210 / 2210AP / 2210CA / 2210US / 2211 / 2211AP / 2212CA / 2213 / 2214 / 2215 / 2216 / 2217 / 2218 / 2218AP / 2218RS / 2219 / 2220,2223 / 2223AP / 2223US / 2226 / 2226AP / 2226CL / 2227 / 2227AP / 2227US / 2231 / 2231AP / 2231US / 2232 / 2232AP / 2232US / 2233AP / 2234AP / 2236 / 2236AP / 2236CL / 2236US / 2237AP / 2238AP / 2242AP / 2243AP / 2254 / 2255 / 2256 / 2257 / 2258 / 2258AP / 2259 / 2260 / 2261 / 2261AP / 2262 / 2262AP / 2263 / 2263AP / 2265 / 2268AP / 2269AP / 2273AS, Compaq Presario 2800 Series: 2800 / 2800CA / 2800T / 2800US / 2801 / 2801CL / 2805 / 2805US / 2806 / 2806CL / 2810 / 2810CA / 2810EA / 2811 / 2811CA / 2811CL / 2811EA / 2815 / 2815EA / 2816 / 2816EA / 2878 / 2878CL / 2879 / 2879CL / 2880 / 2880CL / 2881 / 2881CL, Compaq Presario V2000 Series: V2000 / V2000t / V2000z / V2001 / V2002 / V2003 / V2004 / V2005 / V2006 / V2007 / V2008 / V2009 / V2010 / V2010US / V2016 / V2017 / V2018 / V2019 / V2020 / V2021 / V2022 / V2023 / V2024 / V2025 / V2026 / V2027 / V2028 / V2029 / V2030 / V2030US / V2031 / V2032 / V2033 / V2034 / V2035 / V2036 / V2037 / V2038 / V2039 / V2040 / V2040US / V2041 / V2069 / V2069CL, Compaq Presario V2100 Series: V2100 / V2110 / V2110US / V2110CA / V2130 / V2135 / V2135US / V2140 / V2140US / V2140CA / V2146 / V2146CL / V2150 / V2150US, Compaq Presario V2300 Series: V2300 / V2304 / V2304US / V2305 / V2305CA / V2305US / V2306 / V2306US / V2309 / V2309US / V2310 / V2310CA / V2310US / V2311 / V2311US / V2312 / V2312US / V2320 / V2321 / V2321US / V2330 / V2335 / V2335US, Compaq Presario V2400 Series: V2400 / V2400 CTO / V2401 / V2401CL / V2402 / V2402US / V2403 / V2403NR / V2403us / V2404 / V2404US / V2405 / V2405CA / V2405US / V2409 / V2409US / V2410 / V2410CA / V2410CL / V2410US / V2413 / V2413US / V2414 / V2414NR / V2419 / V2419US / V2424 / V2424NR, Compaq Presario V2500 Series: V2500 / V2508 / V2508WM / V2552 / V2552US / V2555 / V2555US / V2555CA / V2565 / V2565US / V2565CA / V2570 / V2570CA / V2570NR / V2575 / V2575US / V2575CA / V2582 / V2582US, Compaq

Presario V2600 Series: V2600 / V2610 / V2610US / V2630 / V2630US / V2640 / V2640NR / V2665 / V2665US / V2698 / V2699, Compaq Presario V4000 Series: V4000 / V4000z / V4001 / V4002 / V4003 / V4004 / V4005 / V4005CL / V4015 / V4015US / V4020 / V4020US / V4025 / V4025US / V4035 / V4035CA / V4035US / V4100 / V4120 / V4120US / V4125 / V4125CL / V4130 / V4135 / V4135US / V4200 / V4220 / V4220NR / V4220US / V4240 / V4240US / V4245 / V4245US / V4300 / V4400, Compaq Presario V5000 Series: V5000 / V5000Z / V5005 / V5005US / V5005CA / V5010 / V5015 / V5015US / V5015CA / V5100 CTO / V5100z CTO / V5101 / V5101US / V5102 / V5102NR / V5105 / V5105US / V5105CA / V5115 / V5115US / V5115CA / V5119 / V5119US / V5120 / V5120NR / V5160 / V5160US / V5189 / V5200 CTO / V5201 / V5201US / V5201CA / V5204 / V5204US / V5204NR / V5205 / V5205NR / V5206 / V5206OM / V5207 / V5207NR / V5208 / V5208CA / V5209 / V5209US / V5210 / V5210US / V5210CA / V5214EA / V5215EA / V5216EA / V5233EA / V5234EA / V5235EA / V5236EA / V5300 CTO / V5305 / V5305WM / V5306 / V5306US / V5307 / V5307US / V5308 / V5308CA, Compaq Presario V6000 Series: V6000 / V6000T / V6000Z / V6001XX / V6030US / V6048CL / V6101 / V6101US / V6105 / V6105NR / V6107 / V6107US / V6110 / V6110US / V6110CA / V6120 / V6120US / V6120CA / V6130 / V6130US / V6133 / V6133CA / V6133CL / V6137 / V6137US / V6143 / V6143CL / V6171 / V6171CL, Compaq Armada Series: 100 / 100s / 110 / 110s / E300 / E500 / E500s / E700 / M300 / M500 / M700 / V300 / N400c / N410c / N600c, Compaq EVO Series: EVO N1000 / N1000C / N1000V / N1005V / N110 / N150 / N200 / N400 / N400c / N410c / N600 / N600c / N610c / N620c / N800 / N800c / N800v / N800w / N8000, Compaq Presario X1000 Series: X1000 / X1001 / X1001US / X1002 / X1002US / X1005 / X1006 / X1007 / X1010 / X1010CA / X1010US / X1011 / X1012 / X1015 / X1015US / X1016 / X1018 / X1021 / X1022 / X1023 / X1026 / X1027 / X1028 / X1028CL / X1030 / X1030US / X1032 / X1033 / X1034 / X1035 / X1036 / X1036AP / X1037 / X1038 / X1039 / X1040 / X1040US / X1041 / X1042 / X1043 / X1044 / X1045 / X1046 / X1047 / X1048 / X1049 / X1050 / X1050CA / X1051 / X1052 / X1053 / X1054 / X1055 / X1056 / X1057 / X1058 / X1060 / X1061 / X1062 / X1063 / X1064 / X1065 / X1066 / X1067 / X1068 / X1069 / X1070 / X1071 / X1072 / X1073 / X1074 / X1075 / X1080 / X1081 / X1082 / X1083 / X1084 / X1085 / X1086 / X1087 / X1088 / X1089 / X1090 / X1091 / X1092 / X1093 / X1094 / X1095 / X1096 / X1097 / X1098 / X1099, Compaq Presario X1100 Series: X1100 / X1105 / X1110 / X1115 / X1140 / X1155, Compaq Presario X1200 Series: X1200 / X1201 / X1201US / X1210 / X1210CA / X1210US / X1220 / X1220US / X1230 / X1230US, Compaq Presario X1300 Series: X1300 / X1301 / X1301US / X1360 / X1360US / X1360CL / X1360CA / X1370 / X1370US / X1390 / X1390US / X1937 / X1937US

ACER: (use 5.5 x 1.7, 19V DC plug tips)

Travel Mate 200 Series: 200, 200DX, 200T, 201, 201T, 202, 202T, 210, 210T, 210TER, 210TXF, 211, 211T, 212, 212T, 212TE, 212TVX, 213, 213T, 213TX, 213TXV, 220, 222, 222X, 223, 223X, 223SC, 223XV, 225, 225X, 225XC, 225XV Pro, Travel Mate 300 Series: 310, 310T, 312, 312T, 313, 313T, 314, 314T, 330, 330T, 331, 332, 332T, 333, 333T, 340, 340T, 341, 341T, 342, 342T, 343, 343TV, 345, 345T, 347, 347T, 350, 350TE, 350TEN, 351, 351TE, 351TEV, 352, 352TE, 353, 353TE, 353TEV, 354, 354TE, 354TEV, 360, 361, 361EVi, 364, 364ECi, 365, Travel Mate 500 Series: 500, 505, 505DX, 506, 506DX, 506T, 507, 507DX, 507T, 508, 508T, 510, 512, 512DX, 512T, 512T-64, 512TE, 513, 513DX, 513T, 514, 514T, 514TXV, 515, 515TE, 516, 516TE, 517, 517TE, 518, 520, 520iT, 521, 521TE, 521TEV, 521TXV, 524, 524TE, 524TXV, 525, 525TE, 525TX, 525TXV, 527,

527TXV, 528, 528TE, 529, 529ATXV, 529TX, 529TXV, Travel Mate 600 Series: 600, 600TER, 602, 602TER, 603, 603TER, 604, 604TER, 610, 610TXC, 610TXV, 610TXVi, 611, 611TXC, 611TXCi, 611TXV, 612, 612TXC, 612TXCi, 612TXV, 613, 613TXC, 613TXV, 614, 614TXCi, 614TXV, Travel Mate 700 Series: 720, 720TX, 720TXV, 721, 721TX, 722, 722iTX, 722iTXV, 722TX, 723, 723TX, 723TXV, 730, 730TE, 730TX, 730TXV, 732, 732TLV, 732TX, 732TXV, 734, 734TL, 734TXV, 735, 735TLV, 735TXV, 736, 736TL, 736TLV, 737, 737TLV, 738, 738TLV, 739, 739TLV, 739GTLC, 740, 740LVF, 741, 741LVF, 744, 744LCF, Travel Mate 80x-Series: 800LC / 800LCi / 800LCib / 800LMi / 800LMib / 800XC / 800XCi / 801LC / 801LCi / 801LCib / 801LMi / 801LMib / 801XC / 801XCi / 801XVi / 802LCi / 802LCiB / 802LMi / 802LMib / 802XCi / 803LC / 803LCi / 803LCib / 803LM / 803LMi / 803LMib / 803XCi / 803XVi / 804LC / 804LCi / 804LCib / 804LM / 804LMi / 804LMib, Travel Mate 2300 Series: 2300, 2300LC, 2300LCi, 2300LM, 2301, 2301LC, 2301LCi, 2301LM, 2301LMi, 2301WLC, 2301WLCi, 2301WLM, 2301WLMi, 2301XC, 2301XCi, 2302, 2302LC, 2302LCi, 2302LM, 2302LMi, 2302WLM, 2302WLMi, 2310, 2310LCi, 2312, 2312LC, 2312LCi, 2312LM, 2312LMi, 2312NWLC, 2312NWLCi, 2312NWLM, 2312NWLMi, 2312WLCi, 2312WLMi, 2313, 2313LC, 2313LCi, 2313LM, 2313LMi, 2313NWLM, 2313NWLMi, 2313WLC, 2313WLCi, 2313WLM, 2313WLMi, 2314, 2314WLMi, 2318, 2318NWLMi, 2318WLM, 2318WLMi, 2319, 2319NCLi, 2350, 2352, 2352LC, 2352LCi, 2353, 2353LC, 2353LCi, 2353LM, 2353LMi, 2353WLMi, 2355, 2355LC, 2355LCi, Travel Mate 2400 Series: 2410, 2410WLMi, 2412, 2412LCi, 2412LMi, 2412NLC, 2412NLM, 2413, 2413LCi, 2413LMi, 2413NLCi, 2413NLMi, 2413NWLMi, 2413WLCi, 2413WLMi, 2414, 2414LMi, 2414WLM, 2414WLMi, 2419, 2419LCi, 2419NLCi, Travel Mate 3000 Series: 3000, 3002, 3002WTCi, 3002NLC, 3002NLCi, 3002NWLCi, 3003, 3003LC, 3003LCi, 3003LMi, Travel Mate 3200 Series: 3200, 3200XCi, 3200XMi, 3201, 3201XCi, 3201XMi, 3202, 3202XCi, 3202XMi, 3203, 3203XCi, 3203XMi, 3204, 3204XCi, 3204XMi, 3205, 3205XCi, 3205XMi, Travel Mate 4000 Series: 4000, 4000LCi, 4000LMi, 4000WLCi, 4000WLMi, 4001, 4001LC, 4001LCi, 4001LM, 4001LMi, 4001NLCi, 4001WLC, 4001WLCi, 4001WLM, 4001WLMi, 4001XCi, 4002, 4002LC, 4002LCi, 4002LM, 4002LMi, 4002NLCi, 4002WLCi, 4002WLM, 4002WLMi, 4009, 4009LC, 4009LCi, 4050, 4050LC, 4050LCi, 4050LM, 4050LMi, 4051, 4051LC, 4051LCi, 4051LMi, 4051WLCi, 4051WLMi, 4052, 4052LCi, 4052LMi, 4052NLCi, 4052WLCi, 4052WLMi, 4053, 4053LMi, 4060, 4060LCi, 4060LMi, 4061, 4061LCi, 4061LMi, 4061NLCi, 4061NLMi, 4061NWLCi, 4061WLCi, 4061WLMi, 4062, 4062LCi, 4062LMi, 4062WLCi, 4062WLMi, 4064, 4064LMi, 4064WLMi, Travel Mate 4100 Series: 4100, 4101, 4101WLMi, 4101LCi, 4101LMi, 4102, 4102LC, 4102LCi, 4102WLCi, 4102WLMi, 4103, 4103LCi, 4103LMi, 4103WLCi, 4104, 4104WLMi, 4106, 4106WLMi, 4150, 4150LC, 4150LCi, Travel Mate 4500 Series: 4500, 4500LCi, 4500LMi, 4500WLCi, 4500WLMi, 4501, 4501LC, 4501LCi, 4501LMi, 4501WLC, 4501WLCi, 4501WLM, 4501WLMi, 4502, 4502LC, 4502LCi, 4502LMi, 4502WLCi, 4502WLM, 4502WLMi, 4503, 4503LCi, 4503WLCi, 4503LMi, 4504, 4504LM, 4504LMi, Travel Mate 4600 Series: 4650, 4652, 4652LMi, 4654, 4654LMi, Travel Mate 5100, 5600, 5700, 5710, 5720

Travel Mate 6000 Series: 6000, Travel Mate 8000 (8002LCi, 8003LMi, 8006LMi), Travel Mate 8100 (8104WLMi, ZF1), Aspire 1200 Series, Aspire 1400 Series: 1410, 1411, 1411WLMi, 1412, 1412LC, 1412LCi, 1412LM, 1412LMi, 1413, 1413LC, 1413LM, 1413LMi, 1414, 1414LC, 1414LMi, 1414WL

Aspire 1600 Series: 1640, 1641, 1642, 1642WLMi, 1650, 1651, 1651WLCi, 1651WLMi, 1652, 1652WLMi, 1654, 1654WLMi, 1680, 1680WLCi, 1680WLMi, 1681, 1682, 1682LCi, 1682LMi, 1683, 1683LMi, 1683WLM, 1684, 1685, 1685WLCi, 1685WLi, 1690, 1690WLC,

1690WLCi, 1691, 1691WL, 1691WLCi

Aspire 2000 Series: 2000, 2000LCi, 2000LMi, 2000WLCi, 2000WLMi, 2001, 2001LC, 2001Lce, 2001LCi, 2001LMi, 2001WLCi, 2001WLMi, 2002, 2002LCi, 2002LMi, 2002WLCi, 2002WLMi, 2003, 2003LC, 2003LCi, 2003LM, 2003LMi, 2003WLCi, 2003WLMi, 2010, 2010LMi, 2010WLCi, 2010WLMi, 2012, 2012LC, 2012LCi, 2012LMi, 2012WLCi, 2012WLMi, 2013, 2013WLMi, 2014, 2014WLMi, 2016, 2016WLMi, 2020, 2020LC, 2020WLCi, 2021, 2021WLMi, 2023, 2023LMi, 2023WLCi, 2023WLMi, 2024, 2024WLCi, 2024WLMi, 2025, 2025LMi, 2025WLCi, 2025WLMi, 2026, 2026LMi, 2026WLMi, Aspire 3000 Series: 3000, 3000LC, 3000LCi, 3000LM, 3000LMi, 3000WLMi, 3002, 3002LC, 3002LCi, 3002LMi, 3003, 3004, 3004LMi, 3004WLMi, 3005, 3005LCi, AS3050-1594, 3050, Aspire 3100 Series: 3000, 3100-1352, 3100-1033, 3102WLMi, Aspire 3500 Series: 3500, 3500WLCi, 3500WLMi, 3502LC, 3503,

Aspire 3600 Series: 3600, 3602, 3602NWXM, 3603, 3603NWXM, 3603WLCi, 3603WXCi, 3603WXM, 3603XCi, 3608, 3608WXCi, 3608WXM, 3610, 3610WLCi, 3612, 3612LC, 3612LCi, 3613, 3613LC, 3613LCi, 3613WLCi, 3613WLMi, 3614, 3614WLCi, 3614WLMi, 3620, 3623, 3630, 3650, 3660, 3680, 3690-2196, Aspire 5000 Series: 5000, 5000WLMi, 5001, 5001LCi, 5001LM, 5001LMi, 5002, 5002LC, 5002LCi, 5002LM, 5002LMi, 5003, 5003WLMi, 5003WLMi, 5004, 5005 5030, Aspire 5100 Series: 5100, 5102, 5102WLMi, 5102WLMi-MCE, Aspire 5500 Series: 5500, 5501, 5502, 5503, 5504, 5510, 5512, 5513, 5514 5520 5570 5580 5600 5700 5720

Aspire 7100 7101 7102 7103 7104 9400 9402 9401 4900 4520 5315, Acer AcerNote 300 Series: 330t, 350 350c, 350E, 350P, 350PC, 352, 355, 356, 358, 361, 368d, 370, 370c, 374, Acer AcerNote 3600 Series: 3680, Acer AcerNote 500 Series: 500, 509, Acer AcerNote 800 Series: 850C, Acer AcerNote 900 Series: 950, 950C, 950CX, Acer AcerNote Light 300 Series: 350, 350c, 350p, 350pc, 352, 355, 356, 358, 359, 360, 360PC, 363, 370, 370C, 370P, 370PC, 371, 372, 373, 374, 380, 381, 382, 383, Acer AcerNote Light P100 Series: P100, Acer Aspire models: Acer Aspire 1200 series: 1200, 1200, 1200X, 1200XV, 1202, 1202X, 1203X, 1203XC, 1203XV, Acer Aspire 1400 series:

1400 1410 1411 1411WLMi 1412 1412LC 1412LCi 1412LM 1412LMI, 1412WLMi 1413 14131LC 1413LM 1413LMI 1413WLMi 1414 1414LC 1414LMI 1414WL 1414WLCi 1414WLMi, ACER ASPIRE 1500 SERIES:

1510, 1510LC, 1510LM, 1510LMI, 1511, 1511LC, 1511LCE, 1511LCi, 1511LM, 1511LMI, 1512, 1512LMI, 1513, 1513LM, 1513LMI, 1514, 1514LMI, ACER ASPIRE 1600 SERIES: 1640, 1640LC, 1640Z, 1641, 1641LCi, 1641LM, 1641LMi, 1641WLMi, 1642, 1642WLMi, 1642, 1642Z, 1642ZWLMi, 1640Z, 1644, 1644WLMi, 1650, 1651, 1651WLCi, 1651WLMi, 1652, 1652WLMi, 1654, 1654WLMi, 1680, 1680WLCi, 1680WLMi, 1681, 1681LC, 1681LCi, 1681LMi, 1681WLC, 1681WLCi, 1681WLM, 1681WLMi, 1682, 1682LCi, 1682LMI, 1682WLC, 1682WLCi, 1682WLM, 1682WLMi, 1683, 1683LMi, 1683WLM, 1683WLMi, 1684, 1684WLMi, 1685, 1685WLCi, 1685WLMi, 1690, 1690LCi, 1690WLC, 1690WLCi, 1690WLMi, 1691, 1691WL, 1691WLCi, 1691WLMi, 1692, 1692LMI, 1692WLCi, 1692WLMi, ACER ASPIRE 2000 SERIES:

2000, 2000LCi, 2000LMi, 2000WLCi, 2000WLMi, 2001, 2001LC, 2001Lce, 2001LCi, 2001LMi, 2001WLCi, 2001WLMi, 2002, 2002LCi, 2002LMi, 2002WLCi, 2002WLMi, 2003, 2003LC, 2003LCi, 2003LM, 2003LMi, 2003WLCi, 2003WLMi, 2010, 2010LMi, 2010WLCi, 2010WLMi, 2012, 2012LC, 2012LCi, 2012LCi, 2012LMi, 2012WLCi, 2012WLMi, 2013, 2013WLMi, 2014, 2014WLMi, 2016, 2016WLMi, 2020, 2020LC, 2020WLCi, 2021, 2021WLMi, 2023, 2023LMi, 2023WLCi, 2023WLMi, 2024, 2024WLCi, 2024WLMi, 2025, 2025LMi, 2025WLCi, 2025WLMi, 2026, 2026LMi, 2026WLMi, 2420-2355, ACER ASPIRE

2900 SERIES: 2920, 2920Z, 2930, ACER ASPIRE 3000 SERIES: 3000, 3000LC, 3000LCi, 3000LM, 3000LMi, 3000WLMi, 3002, 3002LC, 3002LCi, 3002LMi, 3002NLC, 3002NLCi, 3002NWLCi, 3002WLCi, 3002WLMi, 3003, 3003LC, 3003LCi, 3003LMi, 3003WLCi, 3003WLCi, 3003WLMi, 3003WLCi, 3003WLMi, 3004, 3004LCi, 3004LMi, 3004WLCi, 3004WLMi, 3005, 3005LCi, 3005WLCi, 3005WLMi, 3050, 3050-1594, 3050-1047, 3050-1066, 3050-1142, 3050-1150, 3050-1118, 3050-1270, 3050-1482, 3050-1494, 3050-1535, 3050-1547, 3050-1579, 3050-1594, 3050-1706, 3050-1710, 3050-1733, 3050-1776, 3050-1782, 3050-1787, 3050-1800, 3050-1825, 3050-1854, 3050-1894, 3050-1908, 3050-1946 ACER ASPIRE 3100 SERIES: 3100-1033, 3100-1052, 3100-1104, 3100-1352, 3100-1405, 3100-1458, 3100-1509, 3100-1709, 3100-1711, 3100-1868, 3100-1972, 3100-1974, 3102, 3102WLMi, 3102NWLMi, 3103, 3104NWLC, 3104WLMBiB, ACER ASPIRE 3500 SERIES: 3500, 3500WLCi, 3500WLMi, 3502, 3502LC, 3502LCi, 3502LMi, 3502NLCi, 3502WLC, 3502WLCi, 3503, 3503LCi, 3503NWLMi, 3503WLCi, 3503WLMi, 3505, 3505LMi, 3505WLMi, 3508, 3508WLMi, 3509, 3509WLMi, ACER ASPIRE 3600 SERIES: Acer Aspire 3600, 3602, 3602NWXM, 3603, 3603NWXM, 3603WLCi, 3603WXCi, 3603WXM, 3603XCi, 3608, 3608WXCi, 3608WXM, 3610, 3610WLCi, 3612, 3612LC, 3612LCi, 3613, 3613LC, 3613LCi, 3613WLCi, 3613WLMi, 3614, 3614WLCi, 3614WLMi, 3618, 3618AWLMi, 3620, 3623, 3623NWXM, 3623WLCi, 3623WLMi, 3623WXCi, 3623WXM, 3624, 3624WXCi, 3624WXM, 3630, 3634, 3634LMi, 3634WLMi, 3640, 3641, 3641WXM, 3650, 3651, 3651WLMi, 3660, 3660-2073, 3660-2209, 3660-2248, 3660-2314, 3660-2438, 3660-2501, 3660-2552, 3660-2662, 3660-2713, 3660-2728, 3661, 3661WLMi, 3680, 3680-2103, 3680-2108, 3680-2022, 3680-2233, 3680-2249, 3680-2301, 3680-2472, 3680-2513, 3680-2626, 3680-2633, 3680-2663, 3680-2682, 3680-2974, ACER ASPIRE 3800 SERIES: 3810 Timeline Series Aspire, 3810T-6415, 3810T-8503, 3810TZ-4880. ACER ASPIRE 3900 SERIES: 3935-6504. ACER ASPIRE 4000 Series: 4220, 4315-2004, 4315-2490, 4315-2843, 4315-2904, 4330-2403, 4520-5141, 4520-5235, 4520-5582, 4520-5803, 4520-5950, 4530-5267, 4530-5350, 4530-5487, 4530-5627, 4530-5889, 4530-6823, 4535-5015, 4710-2013, 4710G, 4710Z, 4715-4053, 4715Z, 4720-2013, 4720-4538, 4720-4721, 4720-4825, 4720-6336, 4730-4516, 4730-4758, 4730-4857, 4730-4947, 4730Z, 4736Z-4692, 4810 Timeline, 4810TZ-4011, 4810TZ-4439, 4810TZ-4696, 4810TZ-8480, 4930-6862, 4935. ACER ASPIRE 5000 Series: 5000, 5000WLMi, 5001, 5001LCi, 5001LM, 5001LMi, 5002, 5002LC, 5002LCi, 5002LM, 5002LMi, 5002WLCi, 5002WLM, 5002WLMi, 5003, 5003WLCi, 5003WLMi, 5004, 5004WLCi, 5004WLMi, 5005, 5005WLCi, 5005WLMi, 5030, 5050, 5050-3242, 5050-3336, 5050-3465, 5050-3564, 5050-3602, 5050-3785, 5050-4570, 5050-5172, 5050-5278, 5050-5374, 5050-5410, 5050-5430, 5050-5554, 5050-5555, 5050-5574, 5050-5827, 5050-5865, 5050-5951, 5050-5954 ACER ASPIRE 5100 Series: 5100-3010, 5100-3016, 5100-3087, 5100-3123, 5100-3139, 5100-3357, 5100-3372, 5100-3577, 5100-3530, 5100-3583, 5100-3748, 5100-3825, 5100-3886, 5100-3949, 5100-3959, 5100-4001, 5100-4306, 5100-4575, 5100-4720, 5100-4750, 5100-4800, 5100-5022, 5100-5023, 5100-5033, 5100-5095, 5100-5222, 5100-5232, 5100-5310, 5100-5328, 5100-5400, 5100-5474, 5100-5480, 5100-5538, 5100-5540, 5100-5697, 5100-5747, 5100-5778, 5100-5830, 5100-5840, 5101, 5101AWLMi, 5102, 5102WLMi, 5102WLMi-MCE, 5103, 5103WLMi, 5110 ACER ASPIRE 5200 Series: Acer Aspire 5220 (65W only) ACER ASPIRE 5300 Series: 5315-2001, 5315-2013, 5315-2077, 5315-2122, 5315-2142, 5315-2153, 5315-2187, 5315-2191, 5315-2203, 5315-2270, 5315-2290, 5315-2326, 5315-2373, 5315-2381, 5315-2580, 5315-2639, 5315-2651, 5315-2657, 5315-2698, 5315-2713,

5315-2721, 5315-2768, 5315-2808, 5315-2813, 5315-2826, 5315-2856, 5315-2895, 5315-2940, 5330-2339, 5335-2238, 5335-2257, 5335-2553 ACER ASPIRE 5500 Series: 5500, 5501, 5502, 5503, 5504, 5500Z, 5502Z, 5502ZWXCi, 5502ZWXM, 5510, 5512, 5513, 5514, 5515-5187, 5515-5831, 5515-5879, 5516-5063, 5516-5474, 5520-5043, 5520-5142, 5520-5147, 5520-5156, 5520-5281, 5520-5334, 5520-5377, 5520-5537, 5520-5579, 5520-5716, 5520-5806, 5520-5901, 5520-5908, 5520-5912, 5520-5928, 5520-7416, 5530-5824, 5535-5018, 5535-5050, 5535-5452, 5536, 5536-5165, 5570, 5570Z, 5570, 5570Z, 5570-2016, 5570-2018, 5570-2052, 5570-2067, 5570-2087, 5570-2094, 5570-2118, 5570-2163, 5570-2164, 5570-2197, 5570-2214, 5570-2219, 5570-2223, 5570-2364, 5570-2405, 5570-2429, 5570-2493, 5570-2504, 5570-2565, 5570-2569, 5570-2609, 5570-2609, 5570-2624, 5570-2656, 5570-2731, 5570-2746, 5570-2751, 5570-2758, 5570-2773, 5570-2792, 5570-2846, 5570-2852, 5570-2860, 5570-2935, 5570-2937, 5570-2941, 5570-2947, 5570-2948, 5570-2960, 5570-2961, 5570-2977, 5570-2985, 5570-2998, 5570-4011, 5570-4072, 5570-4174, 5570-4285, 5570-4285, 5570-4309, 5570-4421, 5570-4426, 5570-4523, 5570-4581, 5570-4765, 5570-4820, 5570-4940, 5570-4988, 5570-4998, 5580-6177, 5580-6432, 5580-6707, 5580-6856, 5580-6974, ACER ASPIRE 5600 Series: 5600, 5600AWLMi( 65W ), 5601, 5601AWLMi( 65W ), 5602, 5602WLMi( 65W ), 5610-2089, 5620, 5632, 5633, 5634, 5650, 5670, 5672, 5680, 5683, 5684. ACER ASPIRE 5700 Series: 5715-4190, 5715-4713, 5715-4740, 5715-4928, 5720-4126, 5720-4230, 5720-4353, 5720-4462, 5720-4516, 5720-4649, 5720-4662, 5720-4878, 5720-4984, 5720-6113, 5720-6183, 5720-6249, 5720-6279, 5720-6389, 5720-6497, 5720-6529, 5720-6683, 5730-4163, 5730-4899, 5735-4950, 5735-6041, 5735-6211, 5735-6285, 5735-6694, 5735-6957, 5738, 5738Z-4372, ACER ASPIRE 5800 Series: 5810 Timeline, 5810-4657, 5810TZ-4274 Timeline Series ACER ASPIRE 5900 Series: 5920-6750. Acer Aspire 6000 Series: 6920-6213, 6920-6422, 6920-6428, 6920-6441, 6920-6610, 6920-6621, 6920-6731, 6920-6853, 6920-6864, 6920-6886, 6920-6894, 6920-6875, 6920-6973, 6930-6067, 6930-6073, 6930-6082, 6930-6262, 6930-6455, 6930-6455, 6930-6560, 6930-6586, 6930-6723, 6930-6771, 6930-6809, 6930-6940, 6930-6941, 6930-6942, 6935-6194 Acer Aspire 7100 Series: 7100, 7103, 7103EWSMi, 7103WSMi, 7104, 7104WSMi, 7730-4126, 7730-4868, 7730-6542, Acer Aspire 9000 Series: 9100, 9100WLMi, 9101, 9100WLMi, 9103, 9103WLMi, 9104, 9104LM, 9104LMi, 9104WLMi, 9105, 9105WLMi, 9210, 9300, 9301, 9400, 9402, 9402WLMi, 9402WSMi, 9500 Acer Aspire One Series: 531h 10.1", 531h-1440, 531h-1766, 751h 11.6", 751h-1021, 751h-1080, 751h-1145, 751h-1153, 751h-1192, 751h-1196, 751h-1211, 751h-1259, 751h-1273, 751h-1279, 751h-1346, 751h-1351, 751h-1373, 751h-1378, 751h-1401, 751h-1442, 751h-1522, 751h-1545, 751h-1893, 751h-1948, A110-1041, A110-1113, A110-1137, A110-1178, A110-1295, A110-1545, A110-1588, A110-1626, A110-1662, A110-1691, A110-1698, A110-1722, A110-1812, A110-1831, A110-1834, A110-1888, A110-1948, A110-1955, A110-1995, A150-1001, A150-1006, A150-1029, A150-1035, A150-1049, A150-1068, A150-1083, A150-1126, A150-1137, A150-1141, A150-1172, A150-1178, A150-1220, A150-1249, A150-1316, A150-1329, A150-1347, A150-1348, A150-1359, A150-1382, A150-1400, A150-1405, A150-1423, A150-1435, A150-1444, A150-1447, A150-1457, A150-1485, A150-1493, A150-1504, A150-1505, A150-1532, A150-1546, A150-1553, A150-1555, A150-1570, A150-1572, A150-1576, A150-1577, A150-1588, A150-1622, A150-1635, A150-1649, A150-1662, A150-1672, A150-1679, A150-1690, A150-1706, A150-1742, A150-1777, A150-1784, A150-1786, A150-1798, A150-1834, A150-1864, A150-1887, A150-1890, A150-1905, A150-1949, A150-1983,

A150-1987, A150-1995, A150-1997, D150-1044, D150-1125, D150-1165, D150-1186, D150-1197, D150-1240, D150-1322, D150-1462, D150-1577, D150-1587, D150-1606, D150-1647, D150-1669, D150-1739, D150-1860, D150-1920, D250 10.1", D250-1026,e D250-1042, D250-1116, D250-1132, D250-1151, D250-1165, D250-1185, D250-1196, D250-1288, D250-1289, D250-1302, D250-1326, D250-1580, D250-1610, D250-1706, D250-1724, D250-1738, D250-1797, D250-1905, D250-1924, D250-1990, ZG5, ZG-5.

Acer Extensa Series: Acer Extensa 355 Series. Acer Extensa 365, 366, 366D, 367, 367D, 367T, 368, 368D, 368T Series. Acer Extensa 370 Series. Acer Extensa 390, 390C, 391, 391C, 391T, 392, 392C, 392T, 393, 393C, 393T, 394, 394T, 395, 395T. Acer Extensa 500, 500DX, 501, 501DX, 501T, 502, 502D, 502DX, 502T, 503, 503DX, 503T, 505, 505DX, 506, 506DX, 515 Series. Acer Extensa 600, 610, 610CD, 610CDT, 616, 620 Series. Acer Extensa 700, 700T, 710, 710DX, 710T, 710TE, 711, 711TE, 712, 712TE Series. Acer Extensa 900 Series. Acer Extensa 2000 Series. Acer Extensa 2300 Series: 2300, 2350, Acer Extensa 2500 Series: 2500, 2501FLC, 2501LC, 2501LM. Acer Extensa 2600 Series. Acer Extensa 2900 Series: 2900, 2950. Acer Extensa 3000 Series: 3000, 3001WLMI, 3002LMI. Acer Extensa 3100 Series: 3100, 3102. Acer Extensa 4000 Series: 4100, 4200, 4220, 4220-2148, 4220-2346, 4220-2555, 4230, 4230-2818, 4420-5237, 4420-5239, 4420-5963, 4620-4054, 4620-4431, 4620-4605, 4620-4648, 4620-4691, 4620-4908, 4620-6194, 4620-6402, 4620-6456, 4620-6736,a 4630-4485, 4630-4565, 4630-4658, 4630-4682 Series, 4630-4791,4630-4922 Acer Extensa 5000 Series: Acer Extensa 5220-2090, 5220-2385, 5300 SERIES, 5320-051G16MI, 5320-101G12MI 5420-5059, 5420-5232, 5420-5338, 5430-5720, 5500 SERIES, 5520,, 5620-4020, 5620-4025, 5620-4321, 5620-4382, 5620-4428, 5620-4469, 5620-4677, 5620-4792, 5620-4801, 5620-6030, 5620-6058, 5620-6119, 5620-6266, 5620-6396, 5620-6419, 5620-6635, 5620-6716, 5620-6832, 5620-6846, 5630-4239, 5630-4250, 5630-4666, 5630-4708, 5630-4928, 5630-4933,5630-6082, 5630-6395, 5630-6545, 5630-6806, 5630-6906, 5635,5635Z-4686. Acer Extensa 7500 Series: 7520, 7520G. Acer TravelMate Series: TravelMate C Tablet PC Series: C100, C102, C102T, C102TCI, C104, C104CTI, C104TI, C110, C110TCI, C110TI, C111, C111CTI, C111TCIB, C111TI, C112, C112TCi, C112Ti, C113, C113TCi, C113Ti, C200, C203, C203ETCi, C204, C204TMi, C210, C210TMi, C210-6169, C210-6733, C213, C213TMi, C215, C215TMi, C300, C300XCi, C300XCi\_11g, C300XMi, C301XCi Tablet PC, C301XCi-G, C302, C302XCi, C302XMi, C302XMi-G, C302XMi\_11g, C302XMib, C303, C303XCi, C303XMi, C310, C310XCi, C310XMi, C311, C311XCi, C311XMi, C312, C312XCi, C312XMi, C313, C313XCi, C313XMi, C314, C314XCi, C314XMi. Acer TravelMate 200 Series: Acer TravelMate 200, 200DX, 200T, 201T, 202T, 210, 210T, 210TER, 210TXF, 211T, 212T, 212TE, 212TVX, 213T, 213TX, 213TXV, 213, 213T, 213TX, 213TXV, 220, 222, 222X, 223, 223X, 223XC, 223XV, 225, 225X, 225XC, 225XV Pro 230, 230X, 230XC, 230XV, 230XV Pro, 233, 233LC, 233X, 233XCi, 233XV, 233XVi, 234, 234LC, 234LCi, 260, 261, 261X, 261XC, 261XV, 270, 270X, 270XV, 272, 272LC, 272X, 272XC, 272XV, 272XVi, 273, 273LC, 273LV, 273X, 273XC, 273XV, 274, 274XV, 275, 275LC, 280, 281, 281LC, 281X, 281XC, 281XV,e 283, 283LC, 283LCi, 283XC, 283XV, 283XVi, 284, 284LC, 284XC, 290, 290ATI, 290E, 290LCi, 290LCi Home, 290LCi Pro, 290LMi , 290XCi, 290Xi, 290XMi, 290Xvi, 291, 291ALCi, 291LCi, 291LCi Home, 291LCi-G, 291LMi, 291XCi, 291XCi\_11g, 292, 292LCi, 292LMi, 292ELCi, 292ELMi, 292EXCi, 292X, 292XCi, 293, 293LCi, 293LMi. Acer TravelMate 300 Series: 310, 310T, 311, 311T, 312, 312T, 313, 313T, 314, 314T, 330, 330T, 332, 332T, 333, 333T, 340, 340T, 341, 341T, 341TV, 342, 342T, 343, 343TV, 345, 345T, 347, 347T, 350, 350TE, 350TEN, 351, 351TE, 351TEV, 352, 352TE, 353, 353TE,

353TEV, 354, 354TE, 354TEV, 360, 361, 361EVi, 364, 364ECi, 365, 370, 370TCi, 370TMi, 371, 371LCi, 371Lmi, 371TCi, 371Ti, 371TMi, 372, 372TCi, 372TMi, 374, 374TCi, 374, 374TCi, 380, 380LCi, 380TC, 380TCi, 381, 381TC, 381TCi, 381Ti, 382, 382LCi, 382TC, 382TCi, 382Ti, 382TM, 382TMi, 383, 383TC, 383TCi Acer TravelMate 400 Series: 420, 420DLC, 420LC, 422, 422DLC, 422LC, 422XC, 422, 422DLC, 422LC, 422XC, 426, 426LC, 426LC-PRO, 430, 432, 432L, 432LC, 432LCi, 432, 432L, 432LC, 432LCi, 433, 433ELC, 433ELCi, 433ELM, 433LC, 433LCi, 433LM, 434, 434LC, 434LCi, 435, 435L, 435LC, 435LCi, 435LM, 435LMi. Acer TravelMate 500 series: 500, 505, 505DX, 506, 506DX, 506T, 507, 507DX, 507T, 508, 508T, 510, 512, 512DX, 512T, 512T-64, 512TE, 513, 513DX, 513T, 514, 514T, 514TXV, 515, 515TE, 516, 516TE, 517, 517TE, 550, A550, A551, K-550, 520, 520iT, 521, 521TE, 521TEV, 521TX, 524, 524TE, 524TXV, 525, 525TE, 525TX, 525TXV, 525, 525TE, 525TX, 525TXV, 527, 527TXV, 528, 528TE, 529, 529ATXV, 529TX, 529TXV, 528, 528TE, 529, 529ATXV, 529TX, 529TXV, 530, 530LC, 530LCi, 530XC, 530XCi, 530XV, 530XVi, 531, 531LC, 531LCi, 531XC, 531XCi, 531XV, 531XVi, 533, 533LC, 533LCi, 533XC, 533XCi, 533XV, 533XVi, 534, 534LC, 534LCi, 534TL, 534XC, 534XCi, 535, 535LC, 535LCi, 536, 536LCi, 550, 550LC, 550LV, 550XV, 551, 551XV, 551, 551XV. Acer TravelMate 600 series: Acer TravelMate 600, 600TER, 602, 602TER, 603, 603TER, 604, 604TER, 610, 610TXC, 610TXV, 610TXVi, 611, 611TXC, 611TXCi, 611TXV, 612, 612TXC, 612TXCi, 612TXV, 613, 613TXC, 613TXV, 614, 614TXC, 614TXV, 614TXVci, 620, 621, 621LV, 621XC, 621XV, 623, 623LC, 623LCi, 630, 630XCi, 630XV, 630XVi, 631, 631XC, 632, 632XCi, 633, 633LCi, 632, 632XCi, 633, 633LCi, 634, 634XCi, 636, 636LCi, 650, 650LC, 650XC, 650XCi, 653, 653LC, 653LCi, 653XC, 653XCi, 653XV, 654, 654LC, 654LCi, 654LMi, 654XC, 654XCi, 654XV, 655, 655LCi, 660, 660LCi, 660LMi, 661, 661LCi, 661LMi, 661XCi, 662, 662LCi, 662LMi, 663, 663LMi. Acer TravelMate 700 series: 720, 720TX, 720TXV, 721, 721TX, 721, 721TX, 722, 722iTX, 722iTXV, 722TX, 723, 723TX, 723TXV, 730, 730TE, 730TX, 730TXV, 732, 732TLV, 732TX, 732TXV, 734, 734TL, 734TX, 734TXV, 735, 735TLV, 735TXV, 735, 735TLV, 735TXV, 736, 736TL, 736TLV, 737, 737TLV, 737, 737TLV, 738, 738TLV, 739, 739TLV, 739GTLC, 739, 739TLV, 739GTLC, 740, 740LVF, 741, 741LVF, 744, 744LCF, 741, 741LVF, 744, 744LCF. Acer TravelMate 800 Series: 800, 800LCi, 800LCi-Home, 800LCi\_bt, 800LMi, 800XCi, 801, 801LCi, 801LCib, 801LMib, 802, 802LCi, 803, 803LCi, 803LCi\_bt, 803LCib, 803LMi, 803LMib, 804, 804LCi, 804LCib, 804LMi. Acer TravelMate 2300 Series: 2300, 2300LC, 2300LCi, 2300LM, 2301, 2301LC, 2301LCi, 2301LM, 2301LMi, 2301WLC, 2301WLCi, 2301WLM, 2301WLMi, 2301XC, 2301XCi, 2302, 2302LC, 2302LCi, 2302LM, 2302LMi, 2302WLM, 2302WLMi, 2303, 2303LC, 2303LCi, 2303LM, 2303LMi, 2303WLCi, 2303WLM, 2303WLMi, 2303XC, 2303XCi, 2304, 2304LC, 2304LCi, 2304WLCi, 2304WLM, 2304WLMi, 2310, 2310LCi, 2312, 2312LC, 2312LCi, 2312LM, 2312LMi, 2312NLC, 2312NLM, 2312NWLC, 2312NWLCi, 2312NWLM, 2312NWLMi, 2312WLCi, 2312WLMi, 2313, 2313LC, 2313LCi, 2313LM, 2313LMi, 2313NLC, 2313NLCi, 2313NLM, 2313NLMi, 2313NWLM, 2313NWLMi, 2313WLC, 2313WLCi, 2313WLM, 2313WLMi, 2314, 2314WLMi, 2318, 2318NWLMi, 2318WLM, 2318WLMi, 2319, 2319NCLi, 2350, 2352, 2352LC, 2352LCi, 2353, 2353LC, 2353LCi, 2353LM, 2353LMi, 2353WLMi, 2355, 2355LC, 2355LCi. Acer TravelMate 2400 series: 2400, 2403, 2403WXCi, 2403WXM, 2410, 2410WLMi, 2412, 2412LCi, 2412LMi, 2412NLC, 2412NLM, 2413, 2413LCi, 2413LMi, 2413NLCi, 2413NLMi, 2413NWLMi, 2413WLCi, 2413WLMi, 2414, 2414LMi, 2414WLM, 2414WLMi, 2418, 2418AWLMi, 2419, 2419LCi, 2419NLCi, 2420, 2423, 2423WXCi, 2423WXM, 2423WXi, 2424, 2424WXCi, 2430, 2434, 2434WLCi, 2434WLMi, 2440, 2441,

2441WXCi, 2450, 2451, 2451WLMi, 2451WLCi, 2470, 2480 Series, 2480-2022, 2480-2095, 2480-2106, 2480-2129, 2480-2153, 2480-2192, 2480-2196, 2480-2218, 2480-2228, 2480-2247, 2480-2282, 2480-2352, 2480-2405, 2480-2524, 2480-2551, 2480-2598, 2480-2645, 2480-2650, 2480-2698, 2480-2705, 2480-2735, 2480-2762, 2480-2766, 2480-2779, 2480-2835, 2480-2874, 2480-2876, 2480-2890, 2480-2915, 2480-2918, 2480-2923, 2480-2943, 2480-2967, 2480-2968, 2480-2991, 2481, 2481WXCi, 2490-2413, 2490-2442. Acer TravelMate 3000 Series: 3000, 3000WTCi, 3002, 3002WTCi Series, 3010, 3012, 3012WTMi. Acer TravelMate 3200 Series: 3200, 3200XCi, 3200XMi, 3201, 3201XCi, 3201XMi, 3202, 3202XCi, 3202XMi, 3203, 3203XCi, 3203XMi, 3204, 3204XCi, 3204XMi, 3205, 3205XCi, 3205XMi, 3210, 3210WXCi, 3210WXM, 3210XCi, 3210XMi, 3212, 3212WXCi, 3212WXM, 3212XCi, 3212XMi, 3213, 3213WXCi, 3213WXM, 3220, 3220WXCi, 3220WXM, 3222, 3222WXCi, 3222WXM, 3230, 3260, 3260-4192, 3260-4542, 3260-4653, 3260-4853, 3260-4874, 3270-6607, 3270-6637. Acer TravelMate 3300 Series: 3300, 3302, 3302WXM, 3304, 3304WXM. Acer TravelMate 4000 series: 4000, 4000LCi, 4000LMi, 4000WLCi, 4000WLMi, 4001, 4001LC, 4001LCi, 4001LM, 4001LMi, 4001NLCi, 4001WLC, 4001WLCi, 4001WLM, 4001WLMi, 4001XCi, 4002, 4002LC, 4002LCi, 4002LM, 4002LMi, 4002NLCi, 4002WLCi, 4002WLM, 4002WLMi, 4005, 4005LMi, 4005WLM, 4005WLMi, 4009, 4009LC, 4009LCi, 4010, 4010WLCi, 4011, 4011LCi, 4011LMi, 4011WLCi, 4011WLMi, 4012, 4012NLC, 4015, 4015LMi, 4020, 4020NWLCi, 4020WLCi, 4020WLMi, 4021, 4021LCi, 4021LMi, 4021NWLCi, 4021NWLMi, 4021WLCi, 4021WLMi, 4022, 4022NWLMi, 4022WLCi, 4024, 4024WLMi, 4025, 4025LCi, 4025LMi, 4050, 4050LC, 4050LCi, 4050LM, 4050LMi, 4051, 4051LC, 4051LCi, 4051LMi, 4051WLCi, 4051WLMi, 4052, 4052LCi, 4052LMi, 4052NLCi, 4052WLCi, 4052WLMi, 4053, 4053LMi, 4060, 4060LCi, 4060LMi, 4061, 4061LCi, 4061LMi, 4061NLCi, 4061NLMi, 4061NWLCi, 4061WLCi, 4061WLMi, 4062, 4062LCi, 4062LMi, 4062WLCi, 4062WLMi, 4064, 4064LMi, 4064WLMi, 4070, 4072, 4072LCi, 4072LMi, 4072WLCi, 4072WLMi, 4074, 4074, 4074WLMi. Acer TravelMate 4100 series: 4100, 4100LCi, 4100LMi, 4100WLM, 4100WLMi, 4101, 4101WLMi, 4101LCi, 4101LMi, 4102, 4102LC, 4102LCi, 4102WLCi, 4102WLMi, 4103, 4103LCi, 4103LMi, 4103WLCi, 4104, 4104WLMi, 4106, 4106WLMi, 4150, 4150LCi, 4150LMi, 4150NLCi, 4150WLMi, 4151, 4151LCi, 4151LMi, 4151NLCi, 4151WLCi, 4151WLMi. Acer TravelMate 4300 series: 4320-2451, 4320-2775. Acer TravelMate 4500 series: 4500, 4500LCi, 4500LMi, 4500WLCi, 4500WLMi, 4501, 4501WLMi, 4501WLC, 4501WLCi, 4501WLM, 4501WLMi, 4502, 4502LC, 4502LCi, 4502LMi, 4502WLCi, 4502WLM

HP (use 5.5 x 2.5, 19V DC plug tips)

Compatible with laptop models: HP Mini 1000 PC Series: 1000, 1010NR, 1030NR, 1033CL, 1035NR, FN819AV, FQ729AAR, FQ729AV, FR832AV, FT313UAR, FT313UA, FT315UAR, FT315UA, FW376UAR, FW376UA, FY348LA, FZ978UAR, FZ978UA, NB914AV, NC953AS, NC954AS, NE570PA, NE571PA, NE572PA, NE573PA, NE574PA, NE575PA, NE576PA, NE577PA, NE578PA, NE579PA, NE580PA, NE581PA, NE582PA, NE585PA, NE590PA, NE594PA, NG837LA, NJ209LA, NQ332LA, HP Mini 1000 Vivienne Tam Edition PC Series: NG624EA, NG625EA, NG626EA, NG627EA, NG628EA, NG630EA, NG631EA, NG632EA, NG633EA, NG634EA, NG640EA, NG641EA, NG644EA, NG646EA, NL037PA, HP Mini 1100 PC Series: 1110NR, 1111NR, 1120NR, 1125NR, 1130NR, 1136NR, 1141NR, NB133UAR, NB133UA, NB135UAR, NB135UA, NB137UAR, NB137UA, NB140UA, NB141UA, NB142UAR, NB142UA, NP994UAR, NP994UA, HP Mini

1100 Vivienne Tam Edition PC Series: 1140NR Vivienne Tam, NB134UAR, NB134UA, Compatible Part Number: 496813-001, NA374AA#ABA, PPP018H, A000001200 / A000001210 / A000007020 / A000007030 / ACC10 / ADP-65DB / ADP-65HB / ADP-75FB-A / ADT-W61 / API1AD43 / K000000550 / K000004120 / K000005050 / K000019570 / K000025320 / K000027270 / K000029300 / K000032420 / K000032580 / K000040250 / K000040270 / K000040290 / K000040460 / K000041670 / K000042840 / K000043680 / PA-1500-02 / PA-1600-01 / PA-1600-02 / PA-1650-01 / PA-1650-02 / PA-1700-02 / PA-1750-01 / PA-1750-04 / PA3165U-1ACA / PA3380E-1ACA / PA3380U-1ACA / PA3396E-1ACA / PA3396U-1ACA / PA3432E-1AC3 / PA3432E-1ACA / PA3432U-1AC3 / PA3432U-1ACA / PA3467 / PA3467E / PA3467E-1ACA / PA3467U / PA3467U-1ACA / PA3468E / PA3468E-1ACA / PA3468U / PA3468U-1ACA / SADP-65KB / SADP-65KBB / V000055210 / V000055400 / V000061300 / V000061310 / V000061690

ACER (use 5.5 x 2.5, 19V DC plug tips)

ACER TravelMate and Aspire Notebooks: TM211T, 212T, 213TX, TM340T, TM 341T, TM342, TM345T, TM347T, TM351TE, TM350TE, TM352TE, TM352TE-N, TM353TE, TM353TEV, TM354TE, TM354TEV, TM521TE, TM524TXV, TM525TE, TM525TXV, TM528TE, TM551XV, TM600TER, TM602TER, TM603TER, TM604TER, TM 610TXV, TM610TXVi, TM610TXC, TM611TXV, TM611TXC, TM612TXV, TM612TXC, TM613TXV, TM613TXC, TM730TX, TM732TX, TM734TL, TM735TLV, TM738TLV, TM739TLV, 1680(1681LCi, 1681WLCi, 1681WLMi, 1683WLMi, 1684WLMi, 1685WLMi), 2010, 2020, 3502WLC, 3502WLCi, 3502WLMi, 3603WXCi, 3603WXM, 3602NWXM, 3603WXCi, 3603WXM, 3603NWXM, 3603XCi, 3608NWXCi, 3608WXCi, 3608WXM, 5002LMi, 5002WLMi, 5004WLMi, Acer Aspire: 1200, 1410 (1414WLCi), 1640 (1642WLMi), 1650, 1690 (AS1690LCi, AS1690WLCi, AS1690WLMi, AS1691WLCi, AS1691WLMi, AS1692WLMi, AS1694WLMi), 3000 (3002LCi, 3002WLCi, 3002WLMi, 3003WLCi, 3003WLCi), 3030, 3500 (3502LCi, 3502NLCi, 3503LCi, 3503WLCi, ZL6), 3600 (3603NWXM), 3610, 5002LM, 5002LMi, 5002WLCi, 5030, 5510, 9100, Acer TravelMate: 2350, 2400, 2410, 3000, (3002WTCi), 3210 (3213WXCi, 3213WXM), 3220 (3220WXCi, 3220WXM, 3222WXCi, 3222WXM), 3230, 4020, 4050 (4052LCi), 4060, 4100 (4100LCi, 4100LMi), 4150, 8100 (8104WLMi, ZF1), 2300, 2700, 290, 290E, 3200, 4000, 4500, 6000, 8000, Acer TravelMate 200 Series: 200DX, 200T, 201, 201T, 202, 202T, 210, 210T, 210TER, 210TXF, 211, 211T, 212, 212T, 212TE, 212TXV, 213, 213T, 213TXV, 222X, 223X, 223XC, 223XV, 225X, 225XC, 225XV, 230XC, 230XV, 230XV-PRO, 233LC, 233X, 233XV, 233XVi, 234LCi, 261XC, 261XV, 260, 261, 261X, 261XC, 261XV, 270XV, 272LC, 272X, 272XV, 272XVi, 273X, 273XV, 275LC, 281XC, 281XV, 283LC, 283LCi, 283XV, 283XVi, 290LC, 290LCi, 290LMi, 290XCi, 290Xi, 290XMi, 290XVi, 291LCi, 291LCi-G, 291LMi, 291LMi-G, 291XCi, 291XCiH, 292LC, 292LCi, 292LM, 292LMi, 293LCi, 293LMi, Acer TravelMate 300 Series: 310, 311, 312, 313, 314, 310T, 311T, 312T, 313T, 314T, 320, 330T, 332T, 333T, 341TV, 342T, 343TV, 345, 347, 345T, 347T, 350TE, 350TE-N, 351TE, 351TEV, 352TE, 353TE, 353TEV, 354TE, 354TEV, 361EVi, 364ECi, 365, 371LCi, 371LMi, 371TCi, 371TCi XP, 371Ti, 371Tmi, 371LCi, 371LMi, 371TCi, 371TCi XP, 371Ti, 371Tmi, Acer TravelMate 500 Series: 512DX, 512T, 512TE, 512T-64, 513DX, 513T, 514T, 514TXV, 515TE, 516TE, 517TE, 530LC, 530LCi, 530XC, 530XCi, 530XV, 530XVi, 531LC, 531LCi, 531XC, 531XCi, 531XV, 531XVi, 533LC, 533LCi, 533XC, 533XCi, 533XV, 533XVi, 534LC, 534LCi, 534TL, 534XC, 534XCi, 534XV, 535LC, 535LCi, 536LCi, 540LCi, 540LMi, 541LC, 541LCi, 541LCib, 541LMi, 541XCi, 541XV, 542LCi, 542LMi, 543LCi, 543LMi, Acer

TravelMate 600 to 663 Series: 600, 602, 603, 604, 610, 611, 612, 613, 614, 610TXC, 610TXV, 610TXVi, 611TXC, 611TXCi, 611TXV, 612TXC, 612TXCi, 612TXV, 613TXC, 613TXV, 614TXVCi, 620, 621, 623, 621LV, 621XC, 621XV, 623LC, 623LCi, 630, 632, 633, 630XV, 630XCi, 632XCi, 633LCi, 650LC, 650XC, 650XCi, 653LC, 653LCi, 653XC, 653XCi, 653XV, 654LC, 654LCi, 654XC, 654XCi, 654XV, 655LCi, 660LCi, 660LMi, 661LC, 661LCi, 661LM, 661LMi, 661XC, 661XCi, 661XVi, 662LC, 662LCi, 662LM, 662LMi, 662XCi, 663LCi, 663LM, 663LMi, Acer TravelMate 720 to 740 Series: 720, 722, 723, 720TX, 720TXV, 721TX, 722iTX, 722iTXV, 722TX, 723TX, 723TXV, 730, 732, 734, 735, 730TX, 730TXV, 732TLV, 732TX, 732TXV, 734TL, 734TXV, 735TLV, 736, 737, 738, 739, 736TL, 736TLV, 737TLV, 738TLV, 739GTLV, 739TLV, 740, 741, 744, 740LVF, 741LVF, 744LCF, Acer TravelMate 800 Series: 800LC, 800LCi, 800LCib, 800LMi, 800LMib, 800XC, 800XCi, 801LC, 801LCi, 801LCib, 801LMi, 801LMib, 801XC, 801XCi, 801XVi, 802LCi, 802LCiB, 802LMi, 802LMib, 802XCi, 803LC, 803LCi, 803LCib, 803LM, 803LMi, 803LMib, 803XCi, 803XVi, 804LC, 804LCi, 804LCib, 804LM, 804LMi, 804LMib

Asus Laptop: (use 5.5 x 2.5, 19V DC plug tips)

Asus A6 Series: A6, A6JA, A6JC, A6Jm, A6K, A6KM, A6KT, A6M, A6T, A6Ta, A6Tc, A6R, A6VA, A6VM, Asus A7 Series: A7C, A7D, A7F, A7G, A7J, A7Jc, A7M, A7S, A7Tc, A7V, A7Vc, Asus A8 Series: A8F, A8Jc, A8Jp, A8Jr, A8Js, A8M, A8Sc, Asus F2 Series: F2J, F2Je, Asus F3 Series: F3Ja, F3Jc, F3Jm, F3Jp, F3Jr, F3M, F3P, F3Sc, F3T, F3Tc, Asus F9 Series: F9F, F9J, Asus G Series: G1, G1S, G2, G2S, Asus M2 Series: M2000, M2000N, ASUS M3, series: M3NP, Asus M6 Series: M6000N, M6700N, M6800N, M6B00N, M6N, M6V, M6VA, M6BN, Asus W2 Series: W2J, W2Pc, W2V, Asus W3 Series: W3N, W3V, Asus W5 Series: W5A, W5F, W5V, Asus U5 Series: U5A, U5F  
Asus V1 Series: V1J, V1Jp,

Fujitsu(use 5.5 x 2.5, 19V DC plug tips)

Siemens Amilo A Series A1600, A1640, A1645, A1645G, A1650, A1650G, A1667, A1667G, A1840, A2200+, A6600, A6660, A7600, A7620, A7640, A7645, A8600, A8620, A8625, Fujitsu Siemens Amilo L Series L1300, L1300G, L1310G, L6810, L6820, L6825, L7300, L7310, L7320, Fujitsu Siemens Amilo M Series: M1425, M7405, Fujitsu Siemens Amilo Pro V1Series: V1000, Fujitsu Siemens Amilo Pro V2 Series: V2000, V2010, V2020, V2030, V2035, V2040, V2045, V2055, V2060, V2065, V2085, Fujitsu Siemens Amilo Pro V3 Series: V3205, V3405, V3505, V3515, V3525, V3545, Fujitsu Siemens Amilo Pro V7 Series: V7010, Fujitsu Siemens Amilo Pro V8 Series: V8010, V8210  
Fujitsu Siemens Celcius H Series: H210, H230, H240, Fujitsu Siemens Celcius Mobile series: Mobile, Mobile 2, Mobile A, Mobile H, Mobile S, Fujitsu Siemens LifeBook C1000 Series: C1010, C1020, C1110, C1110D, C1211, C1211D, C1212, C1212D, C1320, C1320D, C1321, C1410, Fujitsu Siemens LifeBook C2000 Series: C2000, C2010, C2032, C2100, C2110, C2111, C2210, C2220, C2230, C2240, C2310, C2320, C2330, C2340, Fujitsu Siemens LifeBook C6000 Series: C6632, C6659, C6661, Fujitsu Siemens LifeBook E2000 series: E2000, E2010, Fujitsu Siemens LifeBook E4000 series: E4000D, E4010, E4010D, Fujitsu Siemens LifeBook E6000 Series: E6180, E6624, E6634, E6644, E6646, E6654, E6664, Fujitsu Siemens LifeBook E7000 Series: E7010, E7110, Fujitsu Siemens LifeBook E8000 Series: E8010, E8020, E8020D, E8110, Fujitsu Lifebook N Series: N3511, N3520, N3530, N6110, N6210, N6410, N6420, Fujitsu Lifebook S Series: S2210, S6310,

S6311, S6410, S7010, S7010D, S7020, S7020B, S7020D, S7020E, S7021, S7025, S7110, S7111, Fujitsu Lifebook T Series: T4020A, T4020B, T4020D  
DELL (use 5.5 x 2.5, 19V DC plug tips)

Dell Inspiron 1000 1300 1200 2200 B130 B120 Latitude 110L, 100L, 120L, LX Series and LXP Series. (PA-16), Dell Inspiron 3000, 3200, 3500, 3700, 7000 (PA-4 with Barrel Plug), Dell Inspiron D233XT, D266GT, D300GT, 300233XT  
Dell Inspiron 3500XT, 3500D233XT, Inspiron 3500D266GT, Inspiron 3500D300GT

GateWay (use 5.5 x 2.5, 19V DC plug tips)

GATEWAY SOLO 1100 Series GATEWAY SOLO 1100, GATEWAY SOLO 1150  
GATEWAY SOLO 1200/1400 Series: GATEWAY SOLO1200, GATEWAY SOLO 1400, GATEWAY SOLO 1450, GATEWAY SOLO 2100 Series GATEWAY 2100, GATEWAY 2150, GATEWAY 2200, GATEWAY SOLO 2300 Series GATEWAY 2300, GATEWAY 2300 Series, GATEWAY 2300LS, GATEWAY 2300XL, GATEWAY SOLO 2500 Series GATEWAY 2500, GATEWAY 2500 Series, GATEWAY 2500LS, GATEWAY 2500SE, GATEWAY 2500XL, GATEWAY 2550, GATEWAY SOLO 5100 Series GATEWAY 5100, GATEWAY 5100 Series, GATEWAY 5100XL, GATEWAY 5150LS, GATEWAY 5150SE, GATEWAY 5150XL, GATEWAY SOLO 9100 Series GATEWAY 9100, GATEWAY 9100 Series, GATEWAY 9100LS, GATEWAY 9100SE, GATEWAY 9100XL, GATEWAY 9150, GATEWAY SOLO 9300 Series GATEWAY 9300, GATEWAY 9300CX GATEWAY 9300XL

NEC (use 5.5 x 2.5, 19V DC plug tips)

Ready 440T, NEC Versa 2400, 2400CD, 2405, 2405CD, 2430, 2430CD, 2435C, 2435CD, 2500, 2500CD, 2505, 2530, 500, 5000, 5060, 5060X, 5080, 5080X, 550D, SXI

Acer (use 5.5 x 2.5, 19V DC plug tips)

TravelMate, 210, 210T, 210TER, 212T, 212TE, 212TXV, 213T, 213TXV, 220, 223X, 223XC, 225X, 225XC, 225XV-Pro, 230, 233XC, 260, 270, 270xv, 280, 290, 330, 330T, 340T, 350, 351TEV, 360, 500, 506, 506DX, 520, 521T, 521TE, 521TXV, 522, 525, 525TXV, 527TXV, 529TXV, 530, 600, 600TER, 602, 602TER, 603, 610, 620, 630, 730, 730TXV, 732, 732TLV, 735TLV, 735TXV, 738TLV, 739TLV, 740, a550, a551, Alpha 550, Alpha 551, Acer AcerNote 330T, 367D, 367T, 390, 390A, 391, 392, 393, 394, 395, Acer Acernote Light: 370, Acer Anywhere: 1100LX, 1120LX, Acer Extensa: 365, 366D, 367D, 368D, 390, 390C, 390CX, 393, 700 Series, 700T, 710, 711, 712 Series, 710DX, 710T, 710TE, 711TE, 712TE, 900, ESS3-391T

HP (use 5.5 x 2.5, 19V DC plug tips)

OmniBook 2100, 2103, 2104, 2105, 2106, 2120, 2121, 2122, 2123, 2124, 2125, 2126, 2127, 3000, 3000CTX, 3100, 3101, 3102, 3250, 4100, 4101, 4102, 4103, 4104, 4105, 4106, 4107, 4108, 4110, 4111, 4150, 4150B, 500, 500B, 6000, 6000 series, 6000B, 6000C, 6100, 7000, 7100, 7103T, 7150, 900, XE, XE 4100, XE 4500, XE-DA, XE2, XE2-DA, XE2-DB, XE2-DC, XE2-DD, XE2-DE, XE2-DI, XE3, XE3L, HP Pavilion 6000, N3000 series, N5000, N5100 series, N5200 series, N5300 series, N5400 series, N5500

series, N6000 series, XH series, XT118, XT155, XT236, XZ series, ZE4210, ZE4240, ZT series

Compaq Presario Series 1200 (i.e. 1220 , 1267 etc.) Series 1400 Series 1600 (i.e. 1624 etc.) Series 1700 Series 1800 Series 2900 (i.e. 2940 etc.) Series

Compaq CM2000 (i.e. CM2010 , CM2020 , CM2050 , CM2060 , CM2070 etc.) Series Prosignia 150 Series

Fujitsu (use 5.5 x 2.5, 19V DC plug tips)

LifeBook A4100 series: A4170, A4177, A4178, A4187, A4190. FutureTech 6200D

Toshiba (use 5.5 x 2.5, 19V DC plug tips)

Satellite: 1000, 1100, 1200, 1600, 1700, 3000 series

Micro Electronics (use 5.5 x 2.5, 19V DC plug tips)

Winbook: J1, N, X1, X2, X4, XLi, XP, Z, Si, Si 566/32, Si 566/64, Si 650 TFT, Si 700, Si 700M, Si 800 TFT, Si 800/128, Si 800CD, Si 800M, Si 850, Si 850DVD Winbook Si2 850, Si2 series, XL, XL 300TFT, XLI, XP, XP5, Z1, Z1 850

IBM / Lenovo (use 7.9 x 5.5, 20V DC plug tips)

T60, Z60 Series



