



VGA Monitor Cable

HD15M to HD15M, 1.8 m (6 ft.)

Part No.: **300735**

Reliable connections for superior signal quality.

Manhattan VGA Cables easily connect a monitor with a desktop or notebook computer. Ideal for use with video splitters, KVM switches and any HD15-equipped display, computer or device, Manhattan VGA Cables are engineered and constructed of quality materials to deliver dependable transmissions in video applications. Full foil shielding, molded boots with strain relief and mini-coax (RGB) with paired-video-wire construction help provide maximum conductivity and clear, crisp images with reduced EMI interference and distortion over extended distances.

Features:

- HD15 male to HD15 male
- Connects VGA source to VGA display
- Fully shielded to reduce EMI and other interference sources
- Molded PVC boot with strain relief
- Lifetime Warranty

Specifications:

Contacts

- 15-pin HD male connections (2)
- Nickel-plated contacts
- Molded PVC boot
- Built-in strain relief
- Mini-coax (RGB) and paired video wire

Cable

- 30 AWG cable
- Withstanding voltage: 300 VDC
- Thermal plastic casing

Dimensions

- Length: 1.8 m (6 ft.)
- Overall diameter: 5.0 mm (0.19 in.)

Package Contents

- VGA Monitor Cable, HD15 Male to HD15 Male

