

DCP-7060D Compact Mono Laser Multifunction Printer with Automatic 2-sided Printing

With fast print and copy speeds of up to 24 pages per minute and automatic 2-sided printing, the DCP-7060D will enable you to produce professional documents in no time. You'll get sharp, crisp text and accurate reproduction of even the finest details on the page thanks to its high print resolution.

This versatile all-in-one offers high quality prints, scans and copies in one compact multifunction unit. The high resolution flatbed scanner produces high quality colour images of scanned documents straight to your PC. The single sheet multi-purpose tray can be used to print on thicker media such as envelopes whilst the standard paper tray boasts an impressive 250 sheet capacity so you'll replenish it less frequently.



DCP-7060D Specifications

Duplex Mono Laser Printer	
Technology	Electrophotographic monochrome laser printer
Laser Notice	Class 1 Laser Product (IEC 60825-1:2007)
Print Speed A4 (Standard)	Up to 24ppm (pages per minute)
Print Speed A4 (Duplex)	Up to 10 sides per minute (5 sheets per minute)
Resolution	HQ1200 (2,400 x 600dpi), 600dpi, 300dpi
Processor	200MHz (ARM9)
Warm Up Time	Less than 7 seconds (from sleep mode)
First Print Out Time	Less than 8.5 seconds (from ready mode)
Emulation	GDI (host based)
Memory	32MB
Local Interface	Hi-Speed USB 2.0
Display	16 characters x 2 lines LCD
Mono Copier	
Copy Speed A4	Up to 24cpm (copies per minute)
Resolution	Up to 600 x 600dpi
First Copy Out Time	Less than 11 seconds (from ready mode)
Multi-Copying	Makes up to 99 copies of each page
Reduction / Enlargement Ratio	Reduce & enlarge documents from 25% to 400% using 1% increments
N in 1 Copying	Allows the user to compress 2 or 4 pages on to a single A4 sheet
Colour Scanner	
Resolution	Up to 600 x 2,400dpi
Resolution (Enhanced)	Up to 19,200 x 19,200dpi
Grey Scale	256 shades of grey are available for copying & scanning
Colour Depth	48 bit internal, 24 bit external
Pull Scan Functions	Scan documents to E-mail, Image, OCR or File**
Media Specifications	
Media Types	Standard Paper Tray - Plain Paper, Thin Paper & Recycled Paper Manual Feed Slot - Plain Paper, Thin Paper, Thick Paper, Recycled Paper, Bond Paper, Labels & Envelopes
Media Capacity & Weights	250 Sheet Standard Paper Tray - 60 - 105 g/m2 (16 - 28lb) 1 Sheet Manual Feed Slot - 60 - 163 g/m2 (16 - 43lb)
Media Sizes	Standard Paper Tray - A4, Letter, B5(ISO/JIS), A5, A5(Long Edge), B6(ISO), A6 & Executive Manual Feed Slot - Width 76.2 to 216mm, Length 116 to 406.4mm
Paper Output	100 Sheets (Face Down) 1 Sheet (Face up) Straight Paper Path

* Declared yield value in accordance with ISO/IEC 19752 ** Requires Brother Software † Windows® only †† Windows® & Apple Macintosh only

Contact:

The DCP-7060D has been designed with the budget conscious buyer in mind. Automatic 2-sided printing, N-in1 printing (where multi-page documents can be reduced to just one page) and toner save mode can reduce print costs considerably. All supplies, including the drum, can be replaced individually. This saves you money as you only pay for what you've used.

The DCP-7060D's ENERGY STAR certified energy efficiency means a reduced energy bill for you. Moreover, you can return your empty toner cartridges to Brother for recycling free of charge. The DCP-7060D also carries Germany's prestigious Blue Angel accreditation thanks to its exceedingly low impact on the environment.



Printer Driver Software	
Windows®	Windows® 7 (32 & 64 bit editions), Windows Vista® (32 & 64 bit editions), Windows® XP Home Edition, Windows® XP Professional (32 & 64 bit editions), Windows® 2000 Professional
Macintosh Linux***	Mac OS X 10.4.11, 10.5.x, 10.6.x CUPS & LPD/LPRng printing system (x86, x64 environment)
Printer Driver Functions	
N-up Printing†† Poster Printing†	Save paper reducing 2, 4, 9, 16 or 25 A4 pages to 1 A4 page Enlarge 1 A4 page into a poster using 4, 9, 16 or 25 A4 pages for a bigger impact
Watermark Printing†	Add predefined text or user-defined messages to your documents as a watermark
Booklet Printing†	Print easy-to-read, professional documents in A5 booklet format using automatic duplex
Header & Footer†	Print the time, date, user ID or customised message on your documents
Supplies	
Inbox Toner Standard Toner (TN-2210) High Yield Toner (TN-2220) Drum Unit (DR-2200)	700 pages* 1,200 pages* 2,600 pages* Approx. 12,000 pages (1 page / job)
Dimensions / Weight	
With Carton Without Carton	527 (W) x 510 (D) x 440 (H) mm / 13.2kg 405 (W) x 398.5(D) x 268 (H) mm / 10.1kg
Others	
Power Consumption	445W copying 55W ready 0.9W deep sleep
TEC (Typical Electrical Consumption) Noise Level	1.117kWh / week Sound Pressure - Less than 53dBA when printing, less than 30dBA in ready Sound Power - Less than 6.40B when printing, less than 4.27B in ready
Ecology	Power Save - Consume less energy when not in use Toner Save - Reduces toner usage
Recommended Monthly Print Volume	250 to 2,000 pages

DCP-7060D

brother
at your side



Compact Mono Laser Multifunction Printer with Automatic 2-sided (Duplex) Printing

The DCP-7060D offers print, scan and copy capabilities in one compact multifunction unit. Fast, high quality 2-sided prints, combined with low running costs make this the perfect solution for home and small offices.



- Versatile all-in-one mono laser printer, scanner and copier.
- Fast printing at speeds of up to 24 pages per minute (ppm).
- Save paper with automatic 2-sided (duplex) printing.
- HQ1200 (2,400 x 600 dpi) print resolution for high quality prints.
- Easy to use control panel with 2 line LCD screen.
- Optional high-yield toner cartridge to reduce print costs further.
- Low maintenance: large 250 sheet paper tray and manual feed slot to print on envelopes.



Versatile

With high speed printing and copying at up to 24 pages per minute, the DCP-7060D produces high quality documents fast. A 250 sheet built-in paper tray means you will be replenishing paper less frequently making you more efficient in your daily tasks and the single sheet multi-purpose tray allows you to print on thicker media such as envelopes. The high resolution colour scanner means you can create digital copies of hard copy documents quickly and easily.

Easy to Use

Although the DCP-7060D is equipped with a wealth of impressive functions, the intuitive control panel together with the 2 line LCD screen means you will be familiar with the most frequently used features in no time. An easy to follow menu structure means the machine is quick and easy to set-up and configure. Replacing the toner cartridge is simple thanks to the front operation.

Value for Money

The DCP-7060D is designed to keep print costs to a minimum. Significantly reduce paper consumption with automatic 2-sided printing or the N-in-1 function (printing multiple pages onto just one sheet). Using Toner Save Mode or the optional high-yield toner cartridge can further reduce your running costs. Energy Star approval adds to the DCP-7060D's impressive range of environmental features and credentials.

Environmentally Friendly

Thanks to its low power consumption, low noise levels and extremely low impact on the environment, the DCP-7060D has been awarded both ENERGY STAR accreditation and the prestigious Blue Angel environmental label. Brother's separate toner and drum system significantly reduces waste. Moreover, you can return your empty toner cartridge to Brother to be recycled free of charge.

Comprehensive Software

The DCP-7060D comes complete with a range of easy-to-use software utilities to improve your productivity. Bundled with the powerful Scansoft® Paperport™ document management software, hard copy documents such as invoices can be scanned in colour, stored and managed electronically for future retrieval.

Feature packed, this versatile all-in-one will help you cut costs and save time...



Scan colour documents direct to your PC



Automatic 2-sided printing to reduce print costs



Print on thicker media and envelopes using the manual feed slot

DCP-7060D