



HP OFFICEJET 6500A e-ALL-IN-ONE SERIES

PRINT, FAX, SCAN, COPY, WEB

Get professional colour and laser performance at a low cost per page. Print from mobile devices with HP ePrint¹. Stay productive with built-in networking and automatic two-sided printing options². (Wireless networking³ and two-sided printing is featured in HP Officejet 6500A Plus e-All-in-One only²).

Achieve laser performance at a low cost per page.

- Get a great value, using individual, high-capacity ink cartridges designed for the office⁴.
- Connect to your network with built-in Ethernet, or to your PC with Hi-speed USB 2.0. HP Officejet 6500A Plus e-All-in-One includes built-in wireless networking².
- Stay productive with a 250-page tray and a 35-page automatic document feeder. HP Officejet 6500A Plus e-All-in-One includes automatic two-sided printing.
- Do more, faster, with fax and scan solutions – quickly fax files or scan to a PC or e-mail⁵.

Print professional-quality colour documents – fast.

- Print borderless documents with vivid colour graphics and sharp text, using HP Officejet inks⁶.
- Print at up to 32 ppm black/31 ppm colour and at laser-comparable (ISO) speeds up to 10 ppm black/7 ppm colour⁷.
- Design high-impact marketing materials and print them affordably in-house.

Print from mobile devices¹.

- This HP ePrint-enabled printer has a dedicated email address so you can print from anywhere via email, from any mobile device¹.
- HP ePrint enabled printers – now with AirPrint™. Simply print wirelessly from your iPad®, iPhone® and iPod touch®.
- Use the 2.36" (5.99 cm) touchscreen to easily copy, fax, print, scan and more.
- Copy a two-sided identification card on one side of a page using the ID Copy feature.
- Use the memory card slots and 2.36" (5.99 cm) touchscreen to print without a PC.

Save energy and conserve resources.

- Use up to 40% less energy than comparable laser products, with an ENERGY STAR® qualified all-in-one⁸.
- Save Paper. PC Fax Send enables paperless fax sending and archiving⁹. A junk-fax blocker limits the amount of wasted paper¹⁰. Automatic two-sided printing on HP Officejet 6500A Plus e-All-in-One cuts paper usage by up to 50%².
- Get free and easy recycling – cartridges returned through HP Planet Partners are recycled responsibly¹¹.



HP Officejet 6500A e-All-inOne



HP Officejet 6500A Plus e-All-inOne

	Wired networking	Standard	Standard
	802.11g Wireless networking	Optional	Standard
	Duplex (Two-sided) printing	None	Automatic

¹May require an Internet connection to the printer. Feature works with any Internet- and e-mail-capable device. For details, www.hp.com/go/eprintcenter. ²Built-in wireless networking and automatic two-sided printing is available on the HP Officejet 6500A Plus e-All-in-One only. Product is available in selected countries only. ³Wireless performance depends upon physical environment and distance from access point.

⁴High-capacity cartridges and ColorLok® paper not included. Please purchase separately. ⁵Visit www.hp.com to download the latest software. ⁶On brochure and photo paper only. ⁷Based on ppm measured using ISO/IEC 24734. Standard applies to inkjet and laser products and excludes first set of new documents. For details, see www.hp.com/go/inkjetprinter. ⁸Supports iOS 4.2 devices with internet connection. Works with HP ePrint enabled printers and e-All-in-ones. Requires a wireless connection to the printer. Wireless performance is dependant upon physical environment and distance from access point. ⁹Most industry-leading color laser A4/C/LJ US\$600, March 2010. For details, www.hp.com/go/officejet. ENERGY STAR® is a registered trademark of the U.S. Environmental Protection Agency. ¹⁰Based on HP testing using the ENERGY STAR® program's TEC test method criteria. ¹¹Requires toll-free service, not included. Price and service are subject to contract. ¹²Program availability varies. HP print cartridge return and recycling is currently available in more than 49 countries, territories and regions in Asia, Europe, and North and South America through the HP Planet Partners program. For more information, visit www.hp.com/recycle.



Technical specification

Ordering information

HP Officejet 6500A e-All-in-One		HP Officejet 6500A Plus e-All-in-One	
Print			
Print Technology	HP Thermal Inkjet		
Print Speed	Document type	Maximum	Laser-comparable (ISO)*
Black	Up to 32 ppm	Up to 10 ppm	
Colour	Up to 31 ppm	Up to 7 ppm	
* Based on ISO/IEC 24734; see www.hp.com/go/inkjetprinter for details.			
Print Quality	Black: Up to 600 rendered dpi black (when printing from a computer); Colour: Up to 4800 x 1200 optimised dpi colour (when printing from a computer on selected HP photo papers and 1200 input dpi)		
Borderless Printing	Yes		
Printer Languages	HP PCL 3 GUI		
Fax			
Fax Speed	Up to 33.6 kbps, 3 sec per page		
Fax Resolution	Black and White: Up to 200 x 200 dpi; Colour: Up to 200 x 200 dpi		
Memory	Up to 100 pages		
Speed Dials	Up to 100 numbers		
Fax Features	Colour fax; auto reduction; auto redial; speed dial; group speed dial; junk barrier; poll to receive; forwarding (black only); distinctive ring; delayed send (black only); scan and fax; fax phone TAM interface; PC fax send and receive		
Scan			
Type	Flatbed, ADF		
Resolution	Up to 4800 x 4800 dpi		
Maximum Scanning Size	ADF: 216 x 356 mm; Flatbed: 216 x 297 mm		
Input Modes	Front-panel scan, HP Driver, EWS		
Copy			
Copy Speed	Black: Up to 32 cpm (draft); Colour: Up to 31 cpm (draft)		
Copy Resolution	Black: Up to 1200 optimised dpi (from 600 input dpi); Colour: Up to 4800 x 1200 optimised dpi (from 1200 input dpi on HP Photo Papers)		
Reduce/Enlarge	25 to 400%		
Maximum Copies	Up to 100 copies		
Copier Settings	Copies; Size; Quality; Lighter/Darker; Paper size; Paper Type; Two-sided; Collate; Margin shift; Enhancement; Crop; Copy preview		
Media Handling			
Automatic Document Feeder	Standard, Up to 35 sheets		
Paper Capacity	Input: Up to 250-sheet input tray, 35-sheet ADF; Output: Up to 50 sheets		
Duplex Printing	None	Automatic	
Media Sizes	Standard: ISO: A4; A5; A6; B5; B6; C6; JIS: B5; B6; B7; 76 x 127 to 216 x 355 mm Custom: Windows does not support custom paper size; Mac: Tray 1: 76.2 x 101.6 to 215.9 x 762 mm		
Media Weights	A4: 60 to 105 g/m ² ; envelopes: 75 to 90 g/m ² ; HP cards: Up to 200 g/m ² ; HP photo paper: up to 280 g/m ²		
Display	2.36" (5.99 cm) [diagonal], 480 x 234 CGD with RGB delta colour configuration		
Memory	64 MB		
Operating Systems Compatibility	Microsoft® Windows® 7, Windows Vista®, Windows® XP (SP2); Mac OS X v10.5, v10.6; Linux [For more information, see http://h2lpipopsource.com/h2lpip-web/index.html]		
Network/Connectivity	1 USB 2.0; 1 Ethernet; 2 memory card slots, 1 RJ-11 fax	1 USB 2.0; 1 Ethernet; 1 Wireless 802.11 b/g/n; 2 memory card slots, 1 RJ-11 fax	
Dimensions (w x d x h)	476 x 409 x 258 mm		
Weight	8.1 kg		
Operating Environment	Recommended: 15 to 32° C, 20 to 80% RH; Maximum: 5 to 40° C, 20 to 90% RH; Storage temperature: -40 to 60° C, 20 to 90% RH		
Power Specifications			
Power Consumption	Active: 36.621 watts; Sleep: 3.2 watts; Powersave: 5.0 watts	Active: 36.621 watts; Sleep: 3.9 watts; Powersave: 5.5 watts	
Input Voltage	Recommended*: 100 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3 Hz) * Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty.		
Warranty	One-year technical phone support; one-year limited hardware warranty; access to 24/7 award-winning support services through http://www.hp.com/support		

Number	Description
CN555A	HP Officejet 6500A e-All-In-One
CN557A	HP Officejet 6500A Plus e-All-In-One
Ink Cartridges	
CD971AA	HP 920 Black Officejet Ink Cartridge
CD972AA	HP 920XL Cyan Officejet Ink Cartridge
CD973AA	HP 920XL Magenta Officejet Ink Cartridge
CD974AA	HP 920XL Yellow Officejet Ink Cartridge
CD975AA	HP 920XL Black Officejet Ink Cartridge
For information on reference page output, visit www.hp.com/go/pageyield .	
Recommended Papers*	
Specialty	HP Professional Inkjet Paper
Plain	HP Papers with ColorLok® Technology**
For information on paper, visit www.hp.com/apac/paper .	
* Availability may vary by country and/or store. Please check with your retailer.	
** HP recommends ColorLok® papers for best printing results	
Hewlett-Packard Offices	
Australia	13 23 47
China	800 820 2255
Hong Kong	800 93 8833
India	3030 4499 1800 425 4999
Indonesia	0800 1111 222
Korea	080 703 0700
Malaysia	1800 88 9886
New Zealand	0800 733 547
Philippines	1800 1441 6688
Singapore	1800 278 0182
Taiwan	0800 236 686
Thailand	(66-2) 353 9000
Vietnam	(84-8) 3920 5564
For the following countries, please fax your queries to: (65) 6275 6707	
• Bangladesh • Bhutan • Brunei • Cambodia • Maldives • Nepal • Pakistan • Sri Lanka	
Visit us at www.hp.com/apac/homeandoffice .	
HP Total Care	
At HP, great technology comes with HP Total Care. HP's broad portfolio of services, solutions and provides expert help at every stage of your HP product experience.	
Discover how HP Total Care help you make IT hassle free, visit www.hp.com/apac/totalcare .	
For instant access to HP customer support online, visit www.hp.com/support .	
iPod, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries. AirPrint and the AirPrint logo are trademarks of Apple Inc.	
© Copyright Hewlett-Packard Development Company, L.P. 2010. All rights reserved. Reproduction, adaptation, or translation of this document in part or in whole without prior written permission is prohibited, except as allowed under the copyright laws. All brand and product names are trademarks or registered trademarks of their respective companies. The information contained in this document is subject to change without notice.	
Published in APJ 04/11, AAA2-4399EW, Ver 4	