



12.1 POS TFT LCD Monitor

Viewing Area	12.1" TFT
Resoluton	800 x 600 SVGA
Effective display area	246 x184.5(mm)
Color	262,144
Response time(tr/tf)	45ms
Contrast ratio	300:1
Brightness	160 cd/m ²
View angle	90°X(H) / 40°X(V)
VGA Signle	Analog VGA
Scan frequency	H:31.5~48 KHz / V:56~75 Hz
Composite Signle(VIDEO)	X
Control	Brightness, Contrast, H-Phase, V-Phase, Size....
Adaptor	Universal AC 100 ~ 240 V, 50 / 60 Hz / DC +12 V
Consumption(Max)	15W
Temperature	0°X ~ 50°XC
Humidity	10% ~ 85%
Dimension	302(w) X 287.5(H) X 160.3(D)
Weight	2.2 Kgs
Safety &EMI	FCCB,ETL.ETLC,CE,TUV/GS
Audio	X
Optional	Touch Panel,Card Reader Version