

ioSafe SoloPRO

Fireproof Waterproof External Hard Drives



ioSafe SoloPRO + Data Recovery Service

The world's only business-class fireproof, waterproof hard drive



Fireproof

Protects data from loss up to 1550°F for 1/2 hour per ASTM E119



Waterproof

Protects data from loss up to 10ft for 72 hours



Data Recovery Service

Up to \$2500 for forensic data recovery, Advanced Replacement included



Business-class Compatibility

eSATA provides full support for Windows Server and Linux



eSATA

eSATA/USB2.0

Data transfer up to 3Gb/s (for eSATA systems only)



USB 3.0 SuperSpeed

Data transfer up to 5Gb/s (for USB 3.0 systems only)



Active Airflow Cooling

Ensures optimum operating temperature



Theftproof

Built in Kensington security slot or bolt down with anti-theft tab



For more information please email sales@iosafe.com or visit us on the web

www.ioSafe.com

ioSafe SoloPRO External Hard Drive

Product Specifications

Operational Details

- Single 3.5 SATA disk: 1TB, 1.5TB, 2TB capacities available
- Quiet forced air cooling
- Multi-platform compatibility with Mac & PC/Windows
- Microsoft Windows Server & Linux (fully supported with eSATA)
- USB 3.0 or eSATA/USB 2.0 Interface

Disaster & Security Specifications

- Fire protection - 1550°F, 1/2 hour per ASTM E119
- Flood / Submersion protection - to 10 feet water depth, 72 hours
- Proven data protection and recovery
- Tested per UL, FCC and CE Standards
- Physical theft protection
- Cable lock or floor mount
- Kensington® Lock Compatible

Support

- 1 Year Data Recovery Service (DRS) Standard (3 and 5 year plans available)
- 3 Year manufacturer's warranty for defects Standard (5 year available with purchase of 5 year DRS upgrade)
- Up to \$2500 included for forensic recovery service
- Advanced Replacement included for warranty/DRS exchanges
- Expedited shipping for DRS support

Inside The Box

- ioSafe SoloPRO External Hard Drive
- USB Cable
- eSATA Cable (eSATA model only)
- Power Supply
- Owners Manual and Warranty

Electrical

- Electrical – AC input
- Voltage: 80 ~ 264 VAC at 50/60 HZ
- Typical Power Consumption: < 25W

System Requirements

- Intel Pentium II 350 Mhz-compatible or Mac G3 processor & greater
- USB for Microsoft Windows 7/Vista/XP, Mac OS 8.6 & greater or Linux based NAS devices
- eSATA for full support of Windows Server or Linux Server systems
- For USB 3.0 or eSATA/USB 2.0 speeds, the system must support applicable specifications

Operating Environment

- Operating: 0-35° C (95°F)
- Non-operating: 0-1550°F, 1/2 hr per ASTM E119
- Operating Humidity: 20% - 80% (non-condensing)
- Non-operating Humidity: 100%, Full water immersion, 10 feet, 3 days.

Physical

- Size: 5.0"W x 7.1"H x 11.0"L
- Weight: 15 lbs



For more information please email sales@iosafe.com or visit us on the web

www.ioSafe.com