



Superior performance with a low cost of ownership for enterprise workgroups

When productivity in the workplace really matters, if your team is taking on tight deadlines and demanding workloads, you need a network colour printer you can really depend on. The ultra-reliable digital LED technology, rapid throughput and a robust yet compact design deliver enterprise-class performance that just won't let you down.

And that's not all. With its superb print quality, exceptional media flexibility, superior energy efficiency and a genuinely low total cost of ownership, the C711 is a solid investment in the future of your business.

Print more, faster

- Enterprise-class colour print speeds of 34ppm and 36ppm black & white
- First colour page prints in just 9 seconds (8 seconds black & white)
- Generous 256MB RAM and 533MHz processor for rapid throughput
- Large paper supply, extendable to 1,690 sheets

Handle heavy workloads with ease

- Flat paper path copes more easily with high print volumes
- Industry-leading reliability built-in with OKI engineering
- Heavy-duty materials, rugged components and ultra-reliable digital LED technology
- User-replaceable, quick-change consumables for maximum uptime

Reduce and control your print costs

- Attractive price tag and low cost per page
- High-yield 11k mono and 11.5k colour toners and 20k long-life image drums
- Consumes just 1.2 watts in sleep mode, reducing energy bills
- Print Control software helps you manage print volumes by restricting usage
- PrintSuperVision software lets you track usage and monitor and manage your printers
- Colour Access Policy Manager lets you control and monitor the use of colour

Professional print quality

- ProQ2400 Multi-level output quality, 1200 x 600dpi print resolution
- Microfine High Definition toner ensures documents are sharper, crisper and glossier, even on ordinary office paper

First class media flexibility

- Paper sizes from A6 to A4, plus 210 x 1200mm banners
- Print on stock from 64 to 250gsm
- Print on specialist media including business cards, CD labels and polyester film

Impeccable security

Now you can remove the risk of sensitive information falling into the wrong hands with the Secure Print² utility. A print run can only start when you enter your private PIN at the printer, and data is encrypted before sending and securely erased after use.

A4	✓
Range of media handling	✓
Colour, Mono	✓
Print	✓
1 - 10+ users	✓

Variants available:

C711
networked
C711dn
duplex, networked
C711dtn
duplex, 2nd tray,
networked



C711 - Colour and Mono Printer

PRINTER		TYPEFACES	
A4 Print speed	34ppm colour, 36ppm mono	Printer fonts	Scalable: 87 PCL fonts and 136 PostScript fonts, PCL Bitmap fonts, OCR-A/B, USPS ZIP Barcode
Time to first print	9 seconds colour, 8 seconds mono	Barcode	Barcode with Checksum support
Warm up time	Up to 60 seconds from power on & up to 35 seconds from power save	GENERAL FEATURES	
Processor speed	533MHz	Memory	Standard RAM: 256MB; Maximum RAM: 768MB Optional SDHC Memory Card ⁴ : 16GB
PRINT QUALITY		Operating conditions	
Resolution	ProQ2400 Multi-level technology, 1200 x 600dpi, 600 x 600dpi	Temperature/Humidity: 10°C to 32°C (17°C to 27°C recommended) / 20% to 80% RH (50% to 70% RH recommended)	
Enhancements	Auto Colour Balance, Photo Enhance via driver (excludes Mac and PostScript drivers)	Storage: -10°C to 43°C, 10% to 90%RH	
INTERFACE AND SOFTWARE		Power supply	
Connectivity	Hi-Speed USB, 10/100-TX Ethernet, IEEE 1284 Bi-directional Parallel	Single phase 220 to 240VAC, frequency 50/60Hz +/- 2%	
Printer languages	PCL 6 (XL3.0) and PCL5c, PostScript 3 emulation, SIDM (IBM-PPR, EPSON-FX), PDF Direct Print v1.7, XPS	Typical: 600W; Max: 1300W; Idle: 100W (average); Power Save: <15W; Sleep: 1.2W	
Network & protocols	All major network protocols supported via ethernet card with internal web server for printer and network card set-up and management. TCP/IP: ARP, IPv4/v6, ICMPv4/v6, TCP, UDP, LPR, FTP, TELNET, HTTP(IPP), BOOTP, DHCP, SNMPv1/v3, DNS, DDNS, UPnP, Bonjour, WINS, SSL/TLS, SMTP, POP3, SNTP, WSDPrint, JetDirect protocols, NetBIOSoverTCP, NetWare 3.x, 4.x, 5.x and 6 with full NDNS and NDPS support: PServer, RPrinter, NDPS supported via dedicated OKI NDPS Gateway, AppleTalk: ELAP, AARP, DDP, AEP, NBP, ZIP, RTMP, ATP, PAP, NetBEUI: SMB, NetBIOS. Other: EAP	Noise level	
OS Compatibility ¹	Windows 2000 / XP Home / XP Professional / XP Professional x64 / Server 2003 / Server 2003 x64 / Server 2008 / Server 2008 x64 / Vista (32-bit & 64-bit); Mac OS X 10.3.9 - 10.6.1	Operating: 54dB(A); Standby: 37dB(A); Power save: Background level	
Advanced networking and security	IPv6, 802.1x authentication, SNMPv3, SSL/TLS HTTPS encryption, Secure Print ² , Secure Erase ² , Data encryption ² , MAC filtering, IP filtering, IPSec	Dimensions (HxWxD)	
Utility Suite ¹	Color Correct, OKI LPR ³ , PrintSuperVision.net ³ , Swatch Utility, Template Manager ³ , Web Driver Installer ³ , Print Control Server ³ , Print Control Client, Storage Device Manager ^{2,3} , Gamma Utility, Profile Assistant ² , Color Access Policy Manager ³	C711n: 389 x 435 x 546mm	
PAPER HANDLING		Weight ⁵	
Paper capacity	Tray 1: 530 sheets of 80gsm; Multi-purpose tray: 100 sheets of 80gsm	C711n: 28kg	
Paper capacity optional trays	Tray 2: 530 sheets of 80gsm (Standard on C711dtn) Tray 3: 530 sheets of 80gsm	Duplex	
Maximum paper capacity	1,690 sheets of 80gsm	Maximum: 100,000 pages/month; Average: 6,000 pages per month	
Paper sizes	Tray 1/2/3: A4, A5, B5; Multi-purpose tray: A4, A5, B5, A6, 10 Envelopes (Com-9, Com-10, DL, Monarch, C5); Labels (Avery 7162, 7664, 7666); Custom size (up to 1200mm length including Banner); Duplex: A4, A5, B5; Custom Size: Width 148-215.9mm Length 210-355.6mm	Warranty	
Paper weight	Tray 1/2/3: 64 to 220gsm; Multi-purpose tray: 64 to 250gsm; Duplex: 64 to 220gsm	1 year Next Business Day Onsite + 0800 support	
Duplex	Standard: C711dn, C711dtn; Optional: C711n	Product order numbers	
Paper output	350 sheets face down, 100 sheets face up (80gsm)	C711n: C711n; C711dn: C711dn; C711dtn: C711dtn	

¹Check www.oki.co.nz for latest driver releases and OS compatibility; ²SDHC Memory Card required; ³Windows only; ⁴Secure Digital High Capacity (SDHC) Memory Card supports up to 32GB. OKI is not responsible for any compatibility risk using non OKI genuine SDHC Memory Card; ⁵Including all consumables

Consumables Information: For the protection of your printer, and in order to ensure that you benefit from its full functionality, this model has been designed to operate only with genuine OKI Printing Solutions toner cartridges. These can be identified by the OKI trademark. Any other toner cartridge may not operate at all, even if it is described as "compatible", and if it does work, your printer's performance and print quality may be degraded.

AUCKLAND

8 Antares Place,
Rosedale
T (09) 477 0500
F (09) 477 0549

WWW.OKI.CO.NZ



WELLINGTON

Level 30, Grand Plimmer Tower,
2-6 Gilmer Terrace
T (04) 569 2940
F (04) 569 2968

CHRISTCHURCH

480B Moorhouse Avenue
T (03) 366 0876
F (03) 365 0167