

Planar Flat Panel Monitors - 15"-17"



SPECIFICATIONS		PL1500M-15"	
Planar Part Number		● PL1500M-BK	997-5905-00
Contrast Ratio (typical)	700:1		
Response Time (typical)	8 ms		
Viewing Angle	160° H, V		
Brightness (typical)	250 cd/m ²		
Pixel Pitch	0.297 mm		
Refresh Rate	75 Hz		
Power Consumption	25W (2W standby) 100/240 VAC (50/60 Hz)		
Input Options	Analog		
External Connections	D-sub 15-pin		
Audio - Built-in Speakers	Yes		
Features	Kensington® Security Slot, Anti-glare coating, Multi-language display, On screen display (OSD), 4:3 aspect ratio		
USB Hub	No		
Pivot	No		
Tilt Range	-5° to +20°		
Power Supply	Internal		
Display Active Area (WxH)	15" diagonal (11.97" x 8.98")		
Native Resolution	1024 x 768 XGA		
Dimensions (w/stand) (WxHxD)	13.18" x 13.47" x 7.86"		
Dimensions (w/o stand)(WxHxD)	13.18" x 11.68" x 2.39"		
Weight	5.95 lbs (net), 8.8 lbs (shipping)		
Weight (w/o stand)	-		
Approvals	FCC-B, CE, UL/cUL		
	*Black models TCO '95 certified		
Customer First™ Warranty	3-Year - featuring FREE 2-Day Advance Replacement		
VESA Compatible/Location	Built-in 75 mm VESA, back		
Planar® Versatility™ Mount	Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.		



Black		PL1700 / PL1700M / PL1702 - 17"		Black		PL1711M - 17"	
● PL1700-BK	997-2795-00	e		● PL1711M-BK	997-3111-00	v	
● PL1700M-BK	997-2796-00			● PL1711M-WH	997-5509-00		
● PL1700M-WH	997-2850-00						
● PL1702-BK	997-5562-00						
1000:1				1000:1			
5 ms				5 ms			
160° H, V				160° H, V			
300 cd/m ²				300 cd/m ²			
.264 mm				.264 mm			
56-75 Hz (75 Hz recommended)				56-75 Hz (60 Hz recommended)			
48W (2W standby)				48W (2W standby)			
100/240 VAC (50/60 Hz)				100/240 VAC +/- 10% (50/60 Hz)			
Analog				Analog, Digital (DVI-D)			
D-sub 15-pin				D-sub 15-pin			
1/8" audio jack (PL1700M Only)				24-pin DVI-D, 1/8" audio jack			
Yes, TrueMedia™, 1W/ch (PL1700M Only)				Yes, TrueMedia™, 1W/ch			
Multi-Mount Ready™, Kensington® Security Slot, Built-in power supply, 1/8 audio jack (PL1700M Only) Fast response time for excellent video performance, 4:3 aspect ratio, TrueMedia™ Sound (PL1700M Only)				Resistance-Free QuadStand™ with pivot, swivel and tilt - over 5" of height adjustment, Multi-Mount Ready™, Kensington® Security Slot, 90° Swivel, 4:3 aspect ratio, TrueMedia™ Sound			
No				No			
No				Yes			
-5° to +20° (PL1700, PL1700M) 360° (PL1702 Only)				-5° to ~+25°			
Internal				Internal			
17" diagonal (13.30" x 10.64")				17" diagonal (13.30" x 10.64")			
1280 x 1024 SXGA				1280 x 1024 SXGA			
14.4" x 15.1" x 7.8"				14.4" x 16.1" x 8.6" (height adjust to 23.2")			
14.4" x 13" x 2.46" (PL1700)				14.4" x 13.5" x 2.46"			
14.4" x 13.5" x 2.46" (PL1700M)							
8.6 lbs. (net), 13 lbs. (shipping)				14.8 lbs. (net), 19.2 lbs. (shipping)			
7.5 lbs.				7.5 lbs.			
UL/cUL, FCC-B, CE, RoHS				UL/cUL, FCC-B, CE, RoHS			
3-Year - featuring FREE 2-Day Advance Replacement				3-Year - featuring FREE 2-Day Advance Replacement			
Built-in 100 mm VESA, back				Built-in 100 mm VESA, back			
Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.				Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.			

Planar Flat Panel Monitors - 19"



SPECIFICATIONS	PL1900 - 19"	PL1910M - 19"	PL1920M - 19"	PL1911M - 19"
Planar Part Number	● PL1900-BK 997-3095-00 ● PL1900-WH 997-6374-00	● PL1910M 997-2797-00 ● PL1910M-WH 997-5510-00	● PL1920M 997-5956-00	● PL1911M 997-3113-00
Contrast Ratio (typical)	1000:1	1000:1	1000:1	1000:1
Response Time (typical)	5 ms	5 ms	5 ms	5 ms
Viewing Angle	150° H, 140° V	160° H, V	170° H, 160° V	150° H, 140° V
Brightness (typical)	300 cd/m ²	300 cd/m ²	300 cd/m ²	300 cd/m ²
Pixel Pitch	.294 mm	.294 mm	.294 mm	.294 mm
Refresh Rate	47-63 Hz (60 Hz recommended)	50-75 Hz (60 Hz recommended)	75 Hz max	56-75 Hz (60 Hz recommended)
Power Consumption	37W (2W standby) 100/240 VAC (47/63 Hz)	55W (2W standby) 100/240 VAC +/- 10% (50/60 Hz)	45W 100/240 VAC	50W (2W standby) 110/220 VAC +/- 10% (50/60 Hz)
Input Options	Analog	Analog, Digital (DVI-D)	Analog, Composite BNC (in/out), S-Video (in/out), Audio (in/out)	Analog, Digital (DVI-D)
External Connections	D-sub 15-pin	D-sub 15-pin 24-pin DVI-D, 1/8 audio jack	VGA input 15 pin, composite video input (BNC) x 1, composite video output (BNC) x 1, S-Video input x 1, S-Video output x 1	D-sub 15-pin 24-pin DVI-D, 1/8" audio jack
Audio - Built-in Speakers	No	Yes, 1W/ch	Yes, 1W/ch	Yes, TrueMedia™, 1W/ch
Features	Fast response time for excellent video performance, Kensington® Security Slot, 4:3 aspect ratio	Kensington® Security Slot, VESA DPMS compliant, DVI-D Digital Input, 4:3 aspect ratio	Kensington® Security Slot, Anti-glare coating, Multi-language display, On screen display (OSD), 4:3 aspect ratio	Resistance-Free QuadStand™ with pivot, swivel and tilt, Multi-Mount Ready™, Kensington® Security Slot, 4:3 aspect ratio, TrueMedia™ Sound
USB Hub	No	No	No	No
Pivot	No	No	No	Yes
Tilt Range	-5° to +20°	-5° to +20°	-5° to +20°	-5° to ~+25°
Power Supply	External	Internal	Internal	Internal
Display Active Area (WxH)	19" diagonal (14.82" x 11.85")	19" diagonal (14.82" x 11.85")	19" diagonal (11.97" x 8.98")	19" diagonal (14.82" x 11.85")
Native Resolution	1280 x 1024 SXGA	1280 x 1024 SXGA	1024 x 768 XGA	1280 x 1024 SXGA
Dimensions (w/stand) (WxHxD)	15.98" x 15.91" x 8.15"	16.2" x 16.46" x 8.7"	16.02" x 16.98" x 7.89"	16.2" x 17.2" x 8.6" (height adjust to 22.3")
Dimensions (w/o stand) (WxHxD)	15.98" x 13.11" x 1.93"	16.2" x 14.8" x 2.52"	16.02" x 14.15" x 2.77"	16.2" x 14.8" x 2.52"
Weight	9.04 lbs. (net), 13 lbs. (shipping)	9.9 lbs. (net), 15.2 lbs. (shipping)	10.08 lbs. (net), 12.35 lbs. (shipping)	17 lbs. (net), 22.3 lbs. (shipping)
Weight (w/o stand)	8.3 lbs.	8.3 lbs.	-	8.3 lbs.
Approvals *Black models TCO '95 certified	UL/cUL, FCC-B, CE, VESA DDC2B™ RoHS	UL/cUL, FCC-B, CE, RoHS	FCC-B, CE, cTUVus	UL/cUL, CE, FCC-B, RoHS
Customer First™ Warranty	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement
VESA Compatible/ Location	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back
Planar® Versatility™ Mount	Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall Mount, Extended Arm Mount, Dual/Quad Monitor Stands. No adapter required.

Planar Flat Panel Monitors - Widescreen



SPECIFICATIONS	PL1910W - 19" WIDE	PL1910MW - 19" WIDE	PL1911MW - 19" WIDE	PL2010MW - 20" WIDE
Planar Part Number	● PL1910W 997-6077-00	● PL1910MW 997-5260-00	● PL1911MW 997-5590-00	● PL2010MW 997-6011-00
Contrast Ratio (typical)	1000:1	1000:1	1000:1	1000:1
Response Time (typical)	5 ms	5 ms	5 ms	5 ms
Viewing Angle	170° H, 160° V	170° H, 160° V	170° H, 160° V	170° H, 160° V*
Brightness (typical)	250 cd/m ²	300 cd/m ²	300 cd/m ²	300 cd/m ²
Pixel Pitch	.3 mm	.243 mm	.243 mm	.276 mm
Refresh Rate	75 Hz	75 Hz	75 Hz	75 Hz
Power Consumption	23W (1W standby)	42W (max) (< 2 standby)	42W (max) (< 2 standby)	45W (1W standby)
Input Options	Analog (VGA), Digital (DVI-D)	Analog (VGA), Digital (DVI-D w/HDCP)	Analog (VGA), Digital (DVI-D w/HDCP)	Analog (VGA), Digital (DVI-D w/HDCP)
External Connections	D-sub 15-pin, 24-pin DVI-D	D-sub 15-pin, 24-pin DVI-D (w/HDCP) 1/8" audio jack	D-sub 15-pin, 24-pin DVI-D (w/HDCP) 1/8" audio jack	D-sub 15-pin, 24-pin DVI-D (w/HDCP) 1/8" audio jack
Audio - Built-in Speakers	No	Yes, TrueMedia™, 1W/ch	Yes, TrueMedia™, 1W/ch	Yes, TrueMedia™, 1W/ch
Features	Anti-glare coating; Multi-language display; On screen display (OSD) Kensington® Security Slot	Dual Analog and DVI-D video inputs 1680 x 1050 optimum resolution 100 mm VESA mount Extra wide viewing angle High contrast ratio of 1000:1 Exceptionally fast 5 ms response time	Dual Analog and DVI-D video inputs 1680 x 1050 optimum resolution 100 mm VESA mount Extra wide viewing angle High contrast ratio of 1000:1 Exceptionally fast 5 ms response time QuadStand™ w/tilt and height adjustment	Dual Analog and DVI-D video inputs Excellent 1600 x 900 Fast 5 ms response time 100 mm VESA mount
USB Hub	No	No	No	No
Pivot	No	No	No	No
Tilt Range	-5° to +20°	-5° to +20°	-5° to +20°	-5° to +20°
Power Supply	Internal	Internal	Internal	Internal
Display Active Area (WxH)	18.5" diagonal (16.14" x 9.07")	19" diagonal (16.07" x 10.05")	19" diagonal (16.07" x 10.05")	20" diagonal
Native Resolution	1366 x 768	1440 x 900 WSXGA+	1440 x 900 WXGA+	1600 x 900
Dimensions (w/stand) (WxHxD)	7.6" x 12.95" x 6.38"	17.26" x 13.62" x 7.8"	17.26" x 14.33" x 9.02" (height adjust to 19.45" or 494.1mm)	18.78" x 13.48" x 7.80"
Dimensions (w/o stand) (WxHxD)	7.6" x 12.95" x 2.56"	17.26" x 13.46" x 2.38"	17.26" x 13.46" x 2.38"	18.78" x 11.60" x 2.40"
Weight	7.05 lbs. (net), 9.92 lbs. (shipping)	9.2 lbs. (net), 11.9 lbs. (shipping)	9.2 lbs. (net), 11.9 lbs. (shipping)	9.5 lbs. (net), 12.5 lbs. (shipping)
Weight (w/o stand)	-	8.9 lbs.	8.9 lbs.	8.8 lbs.
Approvals *Black models TCO '95 certified	UL, CB, FCC-B, CE	UL/cUL, CE, FCC-B, RoHS	UL/cUL, CE, FCC-B, RoHS	FCC-B, cUL, UL, CE
Customer First™ Warranty	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement
VESA Compatible/Location	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back
Planar® Versatility™ Mount	-	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.

*Specified at CR≥5:1. All other LCDs specified at CR≥10:1.

Planar Flat Panel Monitors - Widescreen



SPECIFICATIONS	PX2210MW - 22" WIDE	PX2211MW - 22" WIDE	PX2230MW - 22" WIDE	PX2411MW - 24" WIDE	PX2491W - 24" WIDE	PX2710MW - 27" WIDE
Planar Part Number	● PX2210MW 997-5855-00	● PX2211MW 997-6125-00	● PX2230MW 997-5983-00	● PX2411MW 997-5788-00	PX2491W 997-6198-00LF	● PX2710MW 997-5984-00
Contrast Ratio (typical)	1000:1	1000:1	1000:1	1000:1	1000:1	1200:1
Response Time (typical)	5 ms	5 ms	5 ms	2 ms	6 ms	3.4ms (typical), <2ms (gray-to-gray)
Viewing Angle	170° H, 160° V*	170° H, 160° V	170° H, 160° V	170° H, 160° V	178° H, V	170° H, 160° V
Brightness (typical)	300 cd/m ²	300 cd/m ²	300 cd/m ²	300 cd/m ²	250 cd/m ²	300 cd/m ²
Pixel Pitch	.248 mm x .248 mm	.282 mm	.248 mm	.2715 mm	0.270 mm	.3114 mm
Refresh Rate	56-75 Hz	56-75 Hz (60 Hz recommended)	56-75 Hz	56-75 Hz	100-240 VAC, 50/60 Hz	55-76 Hz (60 Hz recommended)
Power Consumption	50W (< 2W standby)	50W (<2W standby) 100-240 VAC (50/60 Hz)	<48W 100-240 VAC (50/60 Hz)	43W (2W standby) 100-240 VAC (50/60 Hz)	65W (nominal)	60W (1W standby)
Input Options	Analog (VGA), HDMI, Digital (DVI-D w/HDCP)	HDMI, Digital (DVI w/HDCP), Analog (VGA)	Analog, Digital (DVI-D)	Analog, HDMI, Digital (DVI-D w/HDCP)	HDMI (1.3), DVI-D, DVI-I	Analog, HDMI, Digital (DVI-D w/HDCP)
External Connections	1- HDMI 19-pin connector, 1- VGA D-sub 15-pin, 1- 24-pin DVI-D (w/HDCP), 1- 1/8" audio jack, headset jack	1- HDMI input, 1- DVA/HDCP, 1- Analog VGA D-sub 15-pin video display, 1- Audio input, 1- headphone jack	D-sub 15-pin, DVI-D 24-pin, USB-B, Audio Port	1- HDMI 19-pin connector, 1- DVI 24-pin connector, 1- Analog VGA D-sub 15-pin video display, 1- 1/8" audio input jack, headset jack	-	HDMI 19-pin connector, D-sub 15-pin, 24-pin DVI-D
Audio - Built-in Speakers	Yes	Yes, TrueMedia™, 1W/ch	Yes, 2 x 1W	Yes, 2 x 2W	-	Yes, 2 x 2W
Features	Offers full HD 1080p resolution; HDMI input and integrated speakers; Fast 5 ms response time, 100 mm VESA mount	Height adjustable stand, swivel, tilt, pivot (also has 100mm VESA on back)	Optical Touch technology; multi-touch capability, compatible with Microsoft Windows® 7 operating system; HID compliant – no drivers needed for touch screen operation.	2 ms (gray-to-gray) response time, HMDI, Dual Analog (VGA) and Digital input; Height adjustable stand with tilt and pivot	-	Glossy finish, fast response time, anti-glare coating, 100 mm VESA mount, snap on base
USB Hub	No	No	No	No	-	Yes, 4+1 USB 2.0
Pivot	No	Yes	No	Yes, 90°	-	No
Tilt Range	-5° to +19°	-5° to +19°	0° to +20°	-5° to +21°	-5° to +22°	-0° to +20°
Power Supply	Internal	Internal	Internal	Internal	Internal	Internal
Display Active Area (WxH)	21.6" diagonal (18.75" x 11.75")	21.6" diagonal (18.79" x 10.57")	21.5" diagonal (11.77" x 10.56")	23.6" diagonal (20.60" x 11.75")	-	27" diagonal (23.54" x 13.24")
Native Resolution	1920 x 1080	1920 x 1080, full HD	1920 x 1080	1920 x 1080	1920 x 1200	1920 x 1080 full HD
Dimensions (w/stand) (WxHxD)	20.19" x 14.41" x 7.14"	20.19" x 15.67" x 7.14" (512.7 mm x 398.1 mm x 181.4 mm)	20.3" x 16.4" x 8.2"	22.1" x 16.5" x 9.8"	22" x 11" x 18" (558.8 mm x 279.4 mm x 457.2 mm)	25.47" x 17.92" x 9.67"
Dimensions (w/o stand) (WxHxD)	20.19" x 12.16" x 2.70"	20.19" x 12.16" x 2.70" (512.7 mm x 308.8 mm x 68.5 mm)	20.3" x 12.9" x 2.8"	22.1" x 13.2" x 2.7"	22" x 3.75" x 14.7" (558.8 mm x 95 mm x 373 mm)	25.47" x 15.72" x 2.60"
Weight	9.48 lbs. (net) 13.84 lbs. (shipping)	13.89 lbs. (6.3 kg)	12.1 lbs. (net) 15.9 lbs. (shipping)	11.7 lbs. (net) 14.9 lbs. (shipping)	23.7 lbs. (shipping)	13.87 lbs. (net) 17.64 lbs. (shipping)
Weight (w/o stand)	8.8 lbs.	8.8 lbs. (4 kg)	-	10.8 lbs.	-	13.07 lbs.
Approvals *Black models TCO '95 certified	CB, UL/CuL, CE, FCC	CB, UL/cUL, CE, FCC	cTUVus, FCC-B, CE, RoHS	UL/cUL, CE, FCC-B	UL, cUL, CE	FCC-B, CE, cTUVus, TUV/Baurat
Customer First™ Warranty	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement	3-Year - featuring FREE 2-Day Advance Replacement
VESA Compatible/Location	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm VESA, back	Built-in 100 mm x 100 mm VESA, back
Planar® Versatility™ Mount	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.	Fixed Wall/Extended Arm Mounts, Dual/Quad Monitor Stands. No adapter required.	-	-

*Specified at CR≥5:1. All other LCDs specified at CR≥10:1.