

EZH5040 NEW!

720p High Definition Outdoor IR Bullet Camera



HD CCTV


Features

- 1/3" Sony ExmorR Progressive Color CMOS
- 1280x720 resolution at 720p (30 FPS)
- HD-SDI (Serial Data Interface Type Video Output) BNC
- True mechanical Day/Night
- TV out (BNC) with NTSC/PAL selectable
- External megapixel lens controller for quick & easy lens zoom & focus (3-9mm vari-focal)
- OSD menu setting with built-in joystick controller
- Supports second video output for easy camera configuration
- 45 high illuminating IR LED lights
- IR distance up to 45 meters / 150 feet
- Weather resistant IP66 rated
- 12VDC/24VAC dual voltage

Specifications

Video Format	NTSC/PAL selectable (TV out)
Image Sensor	1/3" 1.3 Megapixel Sony ExmorR Progressive CMOS
Effective Pixels	1296x728 (30 FPS)
Unit Cell Size	3.75 um (H) x 3.75 um (V)
S/N Ratio	50 dB max.
Min. Illumination	0 Lux (IR LED on)
Day/Night	True mechanical day/night
IR LED	45 IR LEDs
IR Wavelength	850 nm
IR Distance	Up to 45 meters / 150 feet
IR LED Operation	1 Lux (On), 3 Lux (Off)
Min. Exposure Time	110.86us (1/9020 sec)
Video Output Mode	SDI: 720P, 60 FPS (frame conversion)
Lens	Megapixel vari-focal 3-9 mm lens (F1.6)
OSD Menu	Built-in with joystick controller
Flickerless	Off/50Hz/60Hz (selectable)
Backlight Comp.	On/Off
White Balance	Manual/Auto/Push (selectable)
Operating Temp.	-10°C ~ 50°C / 14°F ~ 122°F
Storage Temp.	-20°C ~ 70°C / -4°F ~ 158°F
Humidity	20~80% (operating), 20~95% (storage)
Power Source	12VDC/24VAC
Power Consumption	12VDC: 13.2W max. / 24VDC: 12W max.
Dimensions (L x W x H)	196 x 98.6 x 88.29 mm / 7.7" x 3.9" x 3.5" (with sunshield, w/out bracket)
Weight	1.37 kg / 3.02 lbs
Weather Resistant	Yes, IP66 rated
Certification	CE, FCC

Dimensions



Ordering Information**

**** Check with your EverFocus sales rep for release date and availability**

* Models vary in different countries. Visit www.everfocus.com and select your country for accurate ordering information