

Coax Cable Splitters

SKU: 859957, 859980, 859981

FEATURES

- 698~2700MHz Band
- Cellular mobile communication
- Low insertion loss, low VSWR
- High isolation, low ripple
- Microstrip Structure



859957 2-Way Splitter



859980 3-Way Splitter



859981 4-Way Splitter



Specifications

ELECTRICAL

Model	859957	859980	859981
Frequency Band (MHz)	698-2700		
VSWR	≥1.4		
Insertion Loss, dB	-3	-4.8	-6
Isolation, dB	≥20		
Power Capacity, W	50		

MECHANICAL & ENVIRONMENTAL

Model	859957	859980	859981
Connector	N-Female		
Dimensions(L×W×D), in	3.7×2.5×0.78	3.9×2.9×0.78	4.5×4.5×0.98
Weight, oz	4.23	6.34	11.64
Operating Temperature, °F	-40-140		

Support



2 Year Warranty

Email: support@wilsonelectronics.com

Website: <http://support.weboost.com>

Phone: +1 866 294 1660
Monday to Saturday