



DS-2CD752MF-FB(H) 2MP Vandal-proof Dome Camera



Key Features

- 1/3" Progressive Scan CMOS
- 2 mega-pixel (1600 × 1200) resolution
- HD720p real-time recording
- ePTZ support
- 3-axis adjustment
- IP66 rating
- Built-in heater optional

Dimensions



Accessories



DS-1217ZJ
(Wall Mount)

Specifications

DS-2CD752MF-FB(H)	
Camera	
Image sensor	1/3" Progressive Scan CMOS
Min. illumination	0.5 lux @ (F1.2, AGC ON), 0.1 lux @ (F1.2, AGC ON, sensitivity × 5)
Shutter time	1/25 s to 1/100,000 s
Lens	2.7 ~ 9 mm @ F1.2 Angle of view: 101° ~ 30.4°
Lens mount	Φ14
Angle Adjustment	Pan: 0 ~ 360°, Tilt: 0 ~ 75°, Rotation: 0 ~ 360°
Day / night	Electronic
Compression standard	
Video compression	H.264 (MPEG4 optional)
Bit rate	32 Kbps ~ 8 Mbps
Audio compression	OggVorbis
Dual stream	Yes
Image	
Max. image resolution	1600 × 1200
Frame rate	50 Hz: 12.5 fps (1600 × 1200), 12.5 fps (1600 × 912), 25 fps (1280 × 720) 60 Hz: 10 fps (1600 × 1200), 15 fps (1600 × 912), 15 fps (1280 × 720)
Image settings	Saturation, brightness, contrast adjustable through client software or web browser
Network	
Alarm trigger	Motion detection
Protocols	TCP/IP, HTTP, DHCP, DNS, RTP/RTSP, PPPoE (FTP, SMTP, NTP, SNMP optional)
Security	Password protection
Interface	
Audio input	1-ch, Line level (2.0 ~ 2.4 Vp-p, 1 kΩ)
Audio output	1-ch, Line level, 600 Ω
Communication interface	1 RJ45 10 M / 100 M Ethernet port and 1 RS-485 interface
Alarm input	1
Alarm output	1
Video output	1 Vp-p composite output (75 Ω/BNC)
Local storage	Built-in SD/SDHC slot, up to 32 GB
General	
Operating conditions	-10 °C ~ 60 °C (14 °F ~ 140 °F) Humidity 90% or less (non-condensing) -H: -40 °C ~ 60 °C (-40 °F ~ 140 °F) with heater and fan on
Power supply	24 VAC ± 10%, 12 VDC ± 10% -H: 24 VAC ± 10% PoE (802.3af)
Power consumption	Max. 3.5 W -H: Max. 13.5 W with heater and fan on
Impact protection	IEC60068-275Eh, 50J; EN50102, up to IK10
Weather proof rating	IP66
Dimensions	Φ 160 × 134.5 mm (Φ 6.30" × 5.30")
Weight	1400 g (3.09 lbs)

Available models

DS-2CD752MF-FB, DS-2CD752MF-FBH

* "H" series supports heater.