

In-Wall Switch, White

DRD3-W V2



The DRD3 switch can easily control any non-dimmable load or device. As part of the RF Lighting Control System, it can be controlled from other devices located anywhere in the home.

features & benefits

- Patented Top Dog™ RF communication protocol; 900MHz radio. Avoids interference with other 900MHz devices, such as cordless phones and baby monitors.
- Patented overload and short circuit protection.
- No control wiring necessary.
- Large surface-mounted antenna ensures maximum broadcast coverage.
- Stores room and house scenes.
- Compatible with Decorator wall plates.
- 5-year warranty.

Note: Wall plate sold separately from device. Product photographed with [Studio Wall Plate – WP5001](#).

specifications

General Info

Color: White

Connection Type: Screw Terminals

Type: RF Switch

Listing Agencies/Third Party Information

CSA Listing Info: CAN/CSA-C22.2 No. 14- 2005

CSA Standard: Yes

cUL Standard: Yes

FCC Standard: Yes
Fed Spec Number: FCC Part 15B
UL Listing No: UL 244A
UL Standard: Yes
UN SPS C: 39122226

Dimensions

Depth Metric: 4.8 cm
Depth U S: 1.88"
Height Metric: 10.8 cm
Height U S: 4.25"
Width Metric: 4.3 cm
Width U S: 1.69"

Technical Information

Frequency: 900 MHz
Humidity: 0-80% relative humidity, noncondensing
Material: High Impact Plastic
Mounting: Electrical Box
Operating Temperature Celsius: 0°C to 40°C
Operating Temperature Fahrenheit: 32°F to 104°F
Reset: Press and hold up and down buttons
Supported Standards: Topdog™ RF communication protocol
Volts A C: 120/277 VAC
Watts: 1500 W (120V), 3000W (277V)