

HSM® Classic

386.2 document shredder

Mobile, powerful model for IT departments and office floors destroys complete computer lists.



- Automatic start/stop control via electronic eye
- Automatically stops when container is full or door is open
- Hardened 100% solid steel cutters can handle occasional standard paper clips or staples
- Practical storage space with optional paper trays for paper stacks. (Paper trays available for purchase)
- Powerful, specially adjusted motor for longer periods of use - with thermal protection for high performance
- Cutting rollers with patented V-groove complete with a lifetime warranty
- Tried and tested closed-tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life
- Enclosed housing protects against the spread of paper dust
- Cross cut shredders should be oiled regularly to maintain top working condition
- Optional auto-oiler available for cross-cut model
- Uses a 58 gallon capacity shred bag; Part #HSM2117



HSM part#	HSM1276	HSM1278
Cutting type	Strip cut	Cross cut
Cutting size	1/8"	1/8" x 1 1/8"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-4 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	22 - 23	14 - 16
Cutting Speed	24 ft / min	27 ft / min
Throat opening	15"	15"
Motor at max. no. of sheets	670W	670W
Motor power (horsepower)	0.90	0.90
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	33 4/5" x 22 1/2" x 16 1/5"	33 4/5" x 22 1/2" x 16 1/5"
Weight	73 lbs	77 lbs
Shred-bin volume	31 gal	31 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.

*Anti-Jam Auto Reverse function available on the cross version model only.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®