

Stylish, desktop  
solution for  
personal use

**i-SENSYS**  
MF3010

you can



## Stylish, compact and easy-to-use desktop mono laser multifunctional.

Make quick prints, copies and scans at your convenience, straight from your desktop with this compact mono laser printer. Ideal for home and small offices it's easy to use and energy efficient.

### Key features

- Laser printer with copy and scan functions in a compact device
- 18 ppm mono laser printing
- First Print Out Time of 7.8 seconds
- Up to 1200 x 600 dpi print resolution
- No waiting with Quick First-Print technologies
- Easy to use colour scanning function
- Modern, eye-catching design
- Easy to use with simple vertical display
- Class leading energy efficiency
- Convenient, easy to use All-in-One cartridge

### What's in the Box

Main unit, Cartridge 725 starter, power cord, quick setup guide, user software and manual CDs

### Dimensions with trays (WxDxH)

372 mm x 276 mm x 254 mm

### Supported OS

**Windows** 7/2000/ XP/ Vista  
**Mac OS X** Version 10.4.9 - 10.7.x  
(Web distribution only)  
**Linux** (Web distribution only)



PRINT



COPY



SCAN



FAX

**Canon**

# Specifications



<p><b>PRINTER</b></p> <p>Print speed Printing method Print quality First Print Out Time Print resolution Printer languages Print margins Toner saver mode</p>	<p>Up to 18 ppm (A4) Monochrome laser beam printing Up to 1200 x 600 dpi with Automatic Image Refinement 7.8 secs 600 x 400 dpi UFR II-LT 5 mm-top, 6 mm-bottom, 5 mm-left and right Yes</p>
<p><b>COPIER</b></p> <p>Copy speed First Copy Output Time (FCOT) Copy resolution Copy modes Multiple copy Reduction / Enlargement Toner saver mode Other features</p>	<p>Up to 18 ppm (A4) Approx. 12 seconds or less Up to 600 x 600 dpi Text, Text/Photo, Text/Photo+, Photo Up to 9 copies 50-200% in 10% increments No 2 on 1, ID Card Copy</p>
<p><b>SCANNER</b></p> <p>Type Scan resolution Colour scanning depth Greyscales Compatibility Max. scan width</p>	<p>Colour Optical: Up to 600 x 600 dpi Enhanced: Up to 9600 x 9600 dpi 24 bit/24 bit (input/output) 256 levels TWAIN, WIA 216 mm</p>
<p><b>MEDIA HANDLING</b></p> <p>Scanner type Paper input (Standard) Paper output Media types Media sizes Media weights</p>	<p>Flatbed 150-sheet tray 100-sheet Plain paper, Heavy paper, Recycled paper, Transparency, Label, Envelope, Index Card Tray: A4, B5, A5, Executive, Envelope (COM10, Monarch, DL, B5, C5), LTR, LGL, Statement, Custom sizes: Width 76 x 216 mm; Length 127 x 356 mm. Tray: 60 to 163 g/m<sup>2</sup></p>
<p><b>INTERFACE &amp; SOFTWARE</b></p> <p>Interface type Operating System compatibility Software and printer management</p>	<p>USB 2.0 Hi-speed Windows 7/2000/ XP/ Vista Mac OS X Version 10.4.9 - 10.7.x<sup>1</sup> Linux<sup>2</sup> Presto! Page Manager, MF Toolbox</p>

<p><b>GENERAL FEATURES</b></p> <p>Duty cycle Warm-up Time Memory Control panel Dimensions with trays (W x D x H) Installation space (W x D x H) Weight Operating environment Power Source Power Consumption Noise Levels</p>	<p>Max. 8,000 pages per month Approx. 10 seconds from power on 64 MB 1 digit LED 372 mm x 276 mm x 254 mm 572 mm x 632 mm x 608 mm 8.2 Kg Temperature: 10 to 30°C (50 to 86°F) Humidity: 20 to 80% RH (no condensation) 220-240 V (±10%), 50/60 Hz (±2 Hz) Maximum: Approx. 960W Active: Approx. 450W Sleep mode: Approx. 1.4 W Typical Electricity Consumption (TEC): 0.6 kWh Sound Power Active: 65.3dB or less, Standby: 43.0dB or less Sound Pressure Active: 50.4dB, Standby: Inaudible</p>
<p><b>CONSUMABLES</b></p> <p>Cartridges</p>	<p>Cartridge 725 (1,600 pages<sup>3</sup>)<sup>4</sup></p>
<p><b>ACCESSORIES/OPTIONS</b></p>	<p>Standard disclaimer All specifications subject to change without notice [1] Web distribution only. Driver release November 2011 [2] Web distribution only. Linux support printing only. Driver release January 2012 [3] Ships with 700 pages starter cartridge [4] Based on ISO/IEC 19752</p>



Stylish, desktop  
solution for  
personal use

**i-SENSYS**  
MF3010

you can



Stylish, compact and easy-to-use  
desktop mono laser multifunctional

Sales Start Date: **October 2011**

**The whole range consists of:**

i-SENSYS MF3010, i-SENSYS MF4410, i-SENSYS MF4430,  
i-SENSYS MF4450, i-SENSYS MF4550d, i-SENSYS  
MF4570dn, i-SENSYS MF4580dn, i-SENSYS MF5940dn,  
i-SENSYS MF5980dw

**Box Dimensions (W x D x H)**

517x391x360 mm

**Box Weight**

9.8 kg

**Packet style**

Pallet

**Quantity of item**

16/12

**MERCURY CODES**

**PRODUCT**

Name	Mercury Code	EAN Code
i-SENSYS MF3010	5252B012AA	4960999783574

**OPTIONS**

Consumables	Mercury Code	EAN Code
Cartridge 725	3484B002AA	4960999665115



PRINT



COPY



SCAN



FAX

**Canon**