




DS-2CC5102/5172N Mini Dome Camera

- 1/3" SONY CCD
- Compact Design
- Day & Night Auto Switch
- 3-axis Adjustment
- Aux Video Output

Indoor



Unit: mm

Specifications

		DS-2CC5102N	DS-2CC5172N
Camera	Image Sensor	1/3" SONY Super HAD CCD II	
	Signal System	NTSC	
	Effective Pixels	510 (H) × 492 (V)	768 (H) × 494 (V)
	Min. Illumination	0.1 Lux @ (F1.2, AGC ON) 0.28 Lux @ (F2.0, AGC ON)	
	Shutter Time	1/60 s to 1/100,000 s	
	Lens	3.6 mm @ F2.0, Angle of view: 78°	
	Lens Mount	M12	
	Angle Adjustment	Pan: 0 - 355°, Tilt: 0 - 90°, Rotation: 0 - 355°	
	Day & Night	Electronic	
	Horizontal Resolution	420 TVL	540 TVL
	Synchronization	Internal synchronization	
General	Video Output	1Vp-p composite output (75 Ω / BNC); Test monitor out [1Vp-p composite output (75 Ω / BNC), device line]	
	S/N Ratio	More than 50 dB	
	Operating Conditions	-10 °C - 60 °C (14 °F - 140 °F) Humidity 90% or less (non-condensing)	
	Power Supply	12 V DC ± 10%	
	Power Consumption	Max. 2 W	
	Dimension (WxHxD)	Φ 97.8 × 64.4 mm (Φ 3.85" × 2.54")	
	Weight	300 g (0.66 lbs)	

Accessories



DS-1234ZJ
Single Gang Electrical Box Adapter