



Dell[™] Vostro[™] 260 MT/260s ST

Reliable, easy-to-use desktop solution for small business.

Easy setup for business that work hard.

The Vostor 260 desktops are designed to perform right out of the box. The Vostro 260 series has just the right essential features to keep your business moving.

- Power through daily tasks and enjoy seamless multitasking with powerful 2nd Generation Intel® Core i processors with Turbo Boost™ 2.0 Technology.
- With a 42% slimmer profile than the mini-tower, the Vostro 260s slim tower is designed to work hard even when space is at a premium.
- Create dynamic presentations with integrated Intel® HD graphics. Or, upgrade to 1GB¹ NVIDIA® or AMD discrete graphics for superb visual performance and support for two HD monitors.
- Connecting to your office is as easy as plug and play. Add a Dell printer or monitor, charge your smartphone, and transfer files with ease and flexible options: VGA, native HDMI, 8 easily accessible USB ports and a multi-media card reader.
- Presentations, programs and spreadsheets can add up quickly. With up to 3TB² of hard-disk space (260), you get plenty of room for saving all the work that matters.

Enjoy security that never sleeps.

Your data is your most valuable business asset. That's why Dell offers Vostro 260 desktops with a range of specialized options to help keep your critical data safe around the clock.

- Preinstalled Backup and Recovery Manager makes routine system backups a breeze. Choose Dell DataSafe Online Backup for a full-service, 24/7 backup and recovery solution — no extra hardware or IT staff required.
- With Roxio Creator Starter software preinstalled on your Vostro 260, you can simply drag and drop files to encrypt data onto a passwordprotected CD, DVD or Blu-ray disc.
- Threat protection comes standard on every Vostro 260 with free, preinstalled Trend Micro Worry-Free™ Business Security Services, securing against virus threats.

Vostro have your IT covered.

Running a small business is demanding enough without having to be your own IT staff. With a suite of specialized support options behind every Vostro desktop we sell, Dell has the resources to keep you up and running smoothly.

- Look to Dell ProSupport³ for the "how-to" help you need — from support with setting up office networks to expertise with virtualization, systems management and other complex IT areas.
- No need to wait on the phone for routine troubleshooting help. With the Dell Support Center application, you get a one-stop destination for keeping your Vostro 260 in top shape.
- Extend your Limited Hardware Warranty⁴up to 3 years, and choose Accidental Damage Service⁵ for protection against power surges, liquid spills and other hazards not covered under your Limited Hardware Warranty.⁴

Vostro 260 MT/260s ST A Perfect Fit

Features	Specifications	
Processor Options	Intel® Core™ i3, i5	
	Intel® Pentium®	
Chipset	Intel® 6 Series H61 Chipset	
Operating System	Genuine Windows® 7 SP1 Starter 32bit	
Options	Genuine Windows® 7 SP1 64 bit (Home Basic, Home Premium, Ultimate)	
	Genuine Windows® 7 SP1 Professional with Downgrade to Windows® XP Professional pre-installed, 32/64 b	
	Ubuntu Desktop Edition (APJ Only)	
	*All Windows OS's bundle Windows Live Search and Essentials	
System Memory ⁶	Up to 8GB 1333MHz Dual Channel DDR3 SDRAM	
	NOTE: Memory runs at maximum system supported speed of 1333 MHz	
	Two (2) user-accessible DIMM slots	
Graphics ¹	Integrated: Intel® HD Graphics	Integrated: Intel® HD Graphics
	Mini-Tower Discrete:	Slim-Tower Discrete:
	1GB Nvidia GT420	1GB AMD Radeon HD6450
Primary Storage	320GB - 1.0TB 7200RPM SATA Hard Drive	
Options ²	Maximum storage capacity on MT: 3TB (two drives at 1.5TB each)	
	All hard drives have 3.0Gb/s interface and utilize NCQ	
Optical Drive	16X DVD-ROM Drive	
Options	16X CD/DVD burner (DVD+/-RW) with double layer write capability	
	Blu-ray Combo	
I/O Ports	USB: 8 externally accessible USB Ports (2 front, 6 back	x); 2 internal USB ports
	Video: VGA, HDMI Audio: Three back-panel connectors for line-in, line-out, microphone-in, two front-panel connectors for headphone-output and microphone-in Other: Optional Serial, PS/2 for Keyboard and Mouse; RJ-45 (10/100/1000 Ethernet)	
Multimedia Options	19-in-1 media card reader (optional)	8-in-1 media card reader
Connectivity	•	
	Dell 1525 Wireless WLAN 11n PCIe Card – Optional	
Security Options	Trend Micro Worry Free for Small Business	
	Physical security – Cable lock chassis security slot and padlock loop	
Back-Up Options	Dell DataSafe Online Back-up	
	Dell Backup and Recovery Manager	
Bays	Mini-Tower:	Slim Tower:
-	3.5" Bays: 2 internal;	3.5" Bays: 1 internal bay
	5.25" Bays: 2 external bays	5.25" Bays: 1 external bay
Slots	PCIe x1: 3 Slots	
	PCIe x16 (Graphics): 1 Slot	
	Note: Slim Tower supports low profile cards	
Power Supply	Mini-Tower: 300W ATX, PFC or non-PFC (varies by	Slim Tower: 250W ATX, Auto-ranging Active-PFC or
	country) with 115/230VAC line switch, 50/60 Hz	non-PFC with 115/230VAC line switch (varies by
		country), 50/60 Hz
Starting Weight	Mini-Tower: 8.2 kg (18.08lb)	Slim Tower: 7.6 kg (16.76lb)
Dimensions	Mini-Tower:	Slim Tower:
(H x W x D)	360 x 175 x 436.3 mm	360 x 102 x 433.1mm
	14.17 x 6.89 x 17.18 inches	14.17 x 4.02 x 17.05 inches
Line Voltage	100 ~ 240 V A.C 50~60Hz	
Regulatory and	Dell Energy Smart settings	
Environmental	Carbon Off-set (Plant a Tree)	
Compliance Options	System Recycle (Asset Recovery Service)	

Important Information:

¹ Graphics & System Memory: Significant system memory may be used to support graphics, depending on system memory size and other factors. ² Hard Drives (GB and TB): GB means 1 billion bytes and TB equals 1 trillion bytes; actual capacity varies with preloaded material and operating environment and will be less

³ ProSupport: Availability and terms of Dell Services vary by region. For more information, visit <u>www.dell.com/servicedescriptions</u>.

⁴Ltd Hardware Warranty: For copy of Ltd Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see www.dell.com/warranty.

⁵ Accidental Damage Service: Service excludes theft, loss, and damage due to fire, flood or other acts of nature, or intentional damage. Customer may be required to return unit to Dell. For complete details, visit <u>www.dell.com/servicecontracts</u>.

⁶ 4GB or greater system memory capability: A 64-bit operating system is required to support 4GB or more of system memory.

Get Started at Dell.com/Vostro





Ad# G11001158, G11001412